

# DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4008Y** 



## Release | Revision: A/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker.

#### Page 1

Speaker Specification

## Page 2

Measuring Circuit

Typical Frequency Response Curve

## Page 3

Dimensions

Speaker Specification		
Item	Specification	Testing Condition
Dimensions	Ø40.0 x H7.7mm	
Voice Coil Impedance	4Ω ±15%	At 1,000Hz 1 V
Resonant Frequency	550±20%Hz	At 1.0 V
Output S.P.L.	90±2dB at 1.0, 1.2, 1.5, 2.0 KHz in average	At 0.1m/0.1W
Frequency Response	f0~10KHz	-10dB
Rated Input Power	2.0 W	
Max Input Power	3.0 W	
Operation	Must be normal	Program source 2.0 W
Noise	Must be normal	Sine wave 2.8 V
Heat Test	Meet items 8 & 9 after test	55±2°C 16 hours
Humidity Test	Meet items 8 & 9 after test	40±2°C 90~95%RH 48 hours
Load Test	Meet items 8 & 9 after test	2.0 W 100 hours white noise
Magnet	Ф12.5 x 1.5mm NdFeB	
Polarity	When a positive DC current is applied to the terminal marked(+), the diaphragm moves forward.	
Net Weight	14.5g	



# DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4008Y** 



Release | Revision: A/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker.

#### Page 1

**Speaker Specification** 


## Page 2

Measuring Circuit


Typical Frequency Response Curve

### Page 3

Dimensions



## **Typical Frequency Response Curve**





Tolerance: ±0.3mm



# DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-4008Y** 



## Release | Revision: A/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker.

#### Page 1

Speaker Specification

#### Page 2

Measuring Circuit

Typical Frequency Response Curve

## Page 3

Dimensions

