Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anticrime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majorityowned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



GaAs INTEGRATED CIRCUIT $\mu PG2158T5K$

L, S-BAND SPDT SWITCH

DESCRIPTION

The μ PG2158T5K is a GaAs MMIC for L, S-band SPDT (<u>Single Pole Double Throw</u>) switch which was developed for mobile phone and another L, S-band application.

This device can operate 2 control switching by control voltage 1.8 to 5.3 V. This device can operate frequency from 0.05 to 3.0 GHz, having the low insertion loss and high isolation.

This device is housed in a 6-pin plastic TSSON (<u>Thin Shrink Small Out-line Non-leaded</u>) package. And this package is able to high-density surface mounting.

FEATURES

•	Switch control voltage	: V _{cont (H)} = 1.8 to 5.3 V (2.7 V TYP.)
		: V _{cont (L)} = -0.2 to +0.2 V (0 V TYP.)
•	Low insertion loss	: LINS1 = 0.40 dB TYP. @ f = 0.05 to 1.0 GHz, V cont (H) = 2.7 V, V cont (L) = 0 V
		: LINS2 = 0.45 dB TYP. @ f = 1.0 to 2.0 GHz, V cont (H) = 2.7 V, V cont (L) = 0 V
		: LINS3 = 0.47 dB TYP. @ f = 2.0 to 2.5 GHz, V cont (H) = 2.7 V, V cont (L) = 0 V
		: LINS4 = 0.53 dB TYP. @ f = 2.5 to 3.0 GHz, V cont (H) = 2.7 V, V cont (L) = 0 V
٠	High isolation	: ISL1 = 27 dB TYP. @ f = 0.05 to 1.0 GHz, $V_{cont (H)} = 2.7 V$, $V_{cont (L)} = 0 V$
		: ISL2 = 19 dB TYP. @ f = 1.0 to 2.0 GHz, $V_{cont (H)} = 2.7 V$, $V_{cont (L)} = 0 V$
		: ISL3 = 17 dB TYP. @ f = 2.0 to 2.5 GHz, $V_{cont (H)} = 2.7 V$, $V_{cont (L)} = 0 V$
		: ISL4 = 17 dB TYP. @ f = 2.5 to 3.0 GHz, $V_{cont (H)} = 2.7 V$, $V_{cont (L)} = 0 V$
٠	Handling power	: Pin (0.1 dB) = +29.0 dBm TYP. @ f = 2.0/2.5 GHz, V cont (H) = 2.7 V, V cont (L) = 0 V
		: Pin (1 dB) = +30.5 dBm TYP. @ f = 2.0/2.5 GHz, V cont (H) = 2.7 V, V cont (L) = 0 V
٠	High-density surface mounting	: 6-pin plastic TSSON package (1.0 $ imes$ 1.0 $ imes$ 0.37 mm)

APPLICATIONS

- L, S-band digital cellular or cordless telephone
- W-LAN, WLL and Bluetooth[™] etc.

ORDERING INFORMATION

Part Number	Order Number	Package	Marking	Supplying Form
μPG2158T5K-E2	μPG2158T5K-E2-A	6-pin plastic TSSON (Pb-Free) ^{™te}	G2	 Embossed tape 8 mm wide Pin 1, 6 face the perforation side of the tape Qty 5 kpcs/reel


Note With regards to terminal solder (the solder contains lead) plated products (conventionally plated), contact your nearby sales office.

Remark To order evaluation samples, contact your nearby sales office. Part number for sample order: μ PG2158T5K

Caution Observe precautions when handling because these devices are sensitive to electrostatic discharge.

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version. Not all devices/types available in every country. Please check with local NEC Compound Semiconductor Devices representative for availability and additional information.

PIN CONNECTIONS AND INTERNAL BLOCK DIAGRAM



Pin No.	Pin Name
1	OUTPUT1
2	GND
3	OUTPUT2
4	V _{cont} 2
5	INPUT
6	Vcont1

TRUTH TABLE

Vcont1	V _{cont} 2	INPUT-OUTPUT1	INPUT-OUTPUT2
Low	High	OFF	ON
High	Low	ON	OFF

ABSOLUTE MAXIMUM RATINGS (TA = +25°C, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Switch Control Voltage	Vcont	+6.0 ^{Note}	V
Input Power	Pin	+31	dBm
Operating Ambient Temperature	TA	–45 to +85	°C
Storage Temperature	Tstg	–55 to +150	°C

Note $|V_{cont}1 - V_{cont}2| \le 6.0 V$

RECOMMENDED OPERATING RANGE (TA = +25°C, unless otherwise specified)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Switch Control Voltage (H)	Vcont (H)	1.8	2.7	5.3	V
Switch Control Voltage (L)	Vcont (L)	-0.2	0	+0.2	V

ELECTRICAL CHARACTERISTICS 1

(TA = +25°C, V_{cont} (H) = 2.7 V, V_{cont} (L) = 0 V, DC cut capacitors = 56 pF, unless otherwise specified)

Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Insertion Loss 1	Lins1	f = 0.05 to 1.0 GHz ^{Note 1}	-	0.40	0.45	dB
Insertion Loss 2	Lins2	f = 1.0 to 2.0 GHz	-	0.45	0.50	
Insertion Loss 3	Lins3	f = 2.0 to 2.5 GHz	-	0.47	0.55	
Insertion Loss 4	Lins4	f = 2.5 to 3.0 GHz	-	0.53	0.60	
Isolation 1	ISL1	f = 0.05 to 1.0 GHz ^{Note 1}	23	27	-	dB
Isolation 2	ISL2	f = 1.0 to 2.0 GHz	16	19	-	
Isolation 3	ISL3	f = 2.0 to 2.5 GHz	14	17	-	
Isolation 4	ISL4	f = 2.5 to 3.0 GHz	14	17	-	
Input Return Loss	RLin	f = 0.05 to 3.0 GHz ^{Note 1}	15	20	-	dB
Output Return Loss	RLout	f = 0.05 to 3.0 GHz ^{Note 1}	15	20	-	dB
0.1 dB Loss Compression	P in (0.1 dB)	f = 2.0/2.5 GHz	+26.0	+29.0	-	dBm
Input Power ^{Note 2}		f = 0.5 to 3.0 GHz	-	+29.0	-	
1 dB Loss Compression Input Power ^{Note 3}	Pin (1 dB)	f = 0.5 to 3.0 GHz	-	+30.5	-	dBm
2nd Harmonics	2fo	f = 2.0/2.5 GHz, Pin = +20 dBm	65	75	-	dBc
3rd Harmonics	3f o	f = 2.0/2.5 GHz, Pin = +20 dBm	65	75	-	dBc
Input 3rd Order Distortion Intercept Point	IIP₃	f = 0.5 to 3.0 GHz 2 tone 5 MHz spacing	-	+60	_	dBm
Switch Control Current	Icont	No signal	-	0.2	20	μA
Switch Control Speed	tsw	50% CTL to 90/10% RF	-	50	500	ns

Notes 1. DC cut capacitors = 1000 pF at f = 0.05 to 0.5 GHz

- 2. Pin (0.1 dB) is measured the input power level when the insertion loss increases more 0.1 dB than that of linear range.
- **3.** Pin (1 dB) is measured the input power level when the insertion loss increases more 1 dB than that of linear range.

Caution This device is used it is necessary to use DC cut capacitors.

The value of DC cut capacitors should be chosen to accommodate the frequency of operation, bandwidth, switching speed and the condition with actual board of your system. The range of recommended DC cut capacitor value is less than 100 pF.

ELECTRICAL CHARACTERISTICS 2

(TA = +25°C, V_{cont} (H) = 1.8 V, V_{cont} (L) = 0 V, DC cut capacitors = 56 pF, unless otherwise specified)

Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Insertion Loss 1	Lins1	f = 0.05 to 1.0 GHz ^{Note 1}	-	0.40	0.47	dB
Insertion Loss 2	Lins2	f = 1.0 to 2.0 GHz	-	0.46	0.52	
Insertion Loss 3	Lins3	f = 2.0 to 2.5 GHz	-	0.48	0.57	
Insertion Loss 4	Lins4	f = 2.5 to 3.0 GHz	_	0.54	0.62	
Isolation 1	ISL1	f = 0.05 to 1.0 GHz ^{Note 1}	23	27	-	dB
Isolation 2	ISL2	f = 1.0 to 2.0 GHz	16	19	-	
Isolation 3	ISL3	f = 2.0 to 2.5 GHz	14	17	-	
Isolation 4	ISL4	f = 2.5 to 3.0 GHz	14	17	-	
Input Return Loss	RLin	f = 0.05 to 3.0 GHz ^{Note 1}	15	20	-	dB
Output Return Loss	RLout	f = 0.05 to 3.0 GHz ^{Note 1}	15	20	-	dB
0.1 dB Loss Compression	Pin (0.1 dB)	f = 2.0/2.5 GHz	+19.0	+22.0	-	dBm
Input Power ^{Note 2}		f = 0.5 to 3.0 GHz	-	+22.0	-	
1 dB Loss Compression Input Power ^{Note 3}	Pin (1 dB)	f = 0.5 to 3.0 GHz	-	+25.0	-	dBm
Switch Control Current	Icont	No signal	-	0.2	20	μA
Switch Control Speed	tsw	50% CTL to 90/10% RF	_	50	500	ns


Notes 1. DC cut capacitors = 1 000 pF at f = 0.05 to 0.5 GHz

- 2. Pin (0.1 dB) is measured the input power level when the insertion loss increases more 0.1 dB than that of linear range.
- **3.** Pin (1 dB) is measured the input power level when the insertion loss increases more 1 dB than that of linear range.

Caution This device is used it is necessary to use DC cut capacitors.

The value of DC cut capacitors should be chosen to accommodate the frequency of operation, bandwidth, switching speed and the condition with actual board of your system. The range of recommended DC cut capacitor value is less than 100 pF.

EVALUATION CIRCUIT



 Remark
 Co
 : 0.05 to 0.5 GHz
 1 000 pF

 : 0.5 to 3.0 GHz
 56 pF

The application circuits and their parameters are for reference only and are not intended for use in actual design-ins.




ILLUSTRATION OF THE TEST CIRCUIT ASSEMBLED ON EVALUATION BOARD

 $V_{\text{cont}}\mathbf{1}$

USING THE NEC EVALUATION BOARD


Symbol	Values
C1, C2, C3	56 pF
C4, C5	1 000 pF

3.5

3.5


NEC

TYPICAL CHARACTERISTICS (TA = +25°C, Vcont (H) = 2.7 V, Vcont (L) = 0 V, DC cut capacitors = 56 pF, using test fixture, unless otherwise specified)




Remark The graphs indicate nominal characteristics.


3.5



INPUT-OUTPUT2 OUTPUT RETURN LOSS vs. FREQUENCY



OUTPUT POWER vs. INPUT POWER




Remark The graphs indicate nominal characteristics.


★ PACKAGE DIMENSIONS

6-PIN PLASTIC TSSON (UNIT: mm)

(Top View)







RECOMMENDED SOLDERING CONDITIONS

This product should be soldered and mounted under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your nearby sales office.

Soldering Method	Soldering Conditions	Condition Symbol	
Infrared Reflow	Peak temperature (package surface temperature) Time at peak temperature Time at temperature of 220°C or higher Preheating time at 120 to 180°C Maximum number of reflow processes Maximum chlorine content of rosin flux (% mass)	: 260°C or below : 10 seconds or less : 60 seconds or less : 120±30 seconds : 3 times : 0.2%(Wt.) or below	IR260
Wave Soldering	Peak temperature (molten solder temperature) Time at peak temperature Preheating temperature (package surface temperature) Maximum number of flow processes Maximum chlorine content of rosin flux (% mass)	: 260°C or below : 10 seconds or less : 120°C or below : 1 time : 0.2%(Wt.) or below	WS260
Partial Heating	Peak temperature (terminal temperature) Soldering time (per side of device) Maximum chlorine content of rosin flux (% mass)	: 350°C or below : 3 seconds or less : 0.2%(Wt.) or below	HS350

Caution Do not use different soldering methods together (except for partial heating).

Bluetooth is a trademark owned by Bluetooth SIG, Inc., U.S.A.

When the product(s) listed in this document is subject to any applicable import or export control laws and regulation of the authority having competent jurisdiction, such product(s) shall not be imported or exported without obtaining the import or export license.

- The information in this document is current as of December, 2005. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC semiconductor products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative
 purposes in semiconductor product operation and application examples. The incorporation of these
 circuits, software and information in the design of customer's equipment shall be done under the full
 responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third
 parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers
 agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize
 risks of damage to property or injury (including death) to persons arising from defects in NEC
 semiconductor products, customers must incorporate sufficient safety measures in their design, such as
 redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:
- "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.
 - "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
 - "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
 - "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.

(Note)

- (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd. and also includes its majority-owned subsidiaries.
- (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).

M8E 00.4-0110

Caution GaAs Products	This product uses gallium arsenide (GaAs). GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.
	• Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.
	 Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.
	Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.
	• Do not burn, destroy, cut, crush, or chemically dissolve the product.
	 Do not lick the product or in any way allow it to enter the mouth.

► For further information, please contact

NEC Compound Semiconductor Devices, Ltd. http://www.ncsd.necel.com/ E-mail: salesinfo@ml.ncsd.necel.com (sales and general) techinfo@ml.ncsd.necel.com (technical) Sales Division TEL: +81-44-435-1573 FAX: +81-44-435-1579

NEC Compound Semiconductor Devices Hong Kong Limited

E-mail: ncsd-hk@elhk.nec.com.hk (sales, technical and general)

 Hong Kong Head Office
 TEL: +852-3107-7303
 FAX: +852-3107-7309

 Taipei Branch Office
 TEL: +886-2-8712-0478
 FAX: +852-3107-7309

 Korea Branch Office
 TEL: +822-2558-2120
 FAX: +822-2545-3859

NEC Electronics (Europe) GmbH http://www.ee.nec.de/ TEL: +49-211-6503-0 FAX: +49-211-6503-1327

California Eastern Laboratories, Inc. http://www.cel.com/ TEL: +1-408-988-3500 FAX: +1-408-988-0279