

RUGGED TIGER EYE™ SYSTEMS

(0.80 mm) .0315" PITCH



FEATURES & BENEFITS

- High-reliability, multi-finger BeCu contact
- Micro pitch and slim body for space savings
- 6 mm, 7 mm and 10 mm stack heights
- · Locking clip, alignment pins and weld tab ruggedizing features
- Rugged latching system for increased withdrawal force
- Vertical and right-angle mating headers
- Discrete wire assembly available with 32 AWG *Teflon™ Fluoropolymer (See page 241).











*Teflon $^{\text{\tiny{TM}}}$ is a trademark of The Chemours Company FC, LLC used under license by Samtec



Locking for increased unmating force (Visit samtec.com?SEML for more information)



Components (ISDE/CC396) and tooling available: samtec.com/tooling


KEY SPECIFICATIONS (SEM/TEM)

	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	MAX. CYCLES	VOLTAGE RATING	LEAD-FREE SOLDERABLE
6 - 10 mm	Black LCP	BeCu (SEM) Phosphor Bronze (TEM)	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	2.9 A per pin (2 pins powered)	100 with 10 μ" (0.25 μm) Au	235 VAC/330 VDC	Yes





(0.80 mm) .0315" PITCH • MICRO TIGER EYE™ SOCKET AND HEADER



-07.0= 10 mmStack Height (TEM/TEMS only) Gold on contact, Gold Flash on tail -H $= 30 \mu$ " (0.76 µm) Gold on contact, Gold Flash on tail

Leave blank for SEMS/TEMS -A = Alignment Pin (Not available

with -LC or -WT)

OPTIONS

-LC = Locking Clip (Not available with –A or –WT) (Manual placement required)

-WT = Weld Tab (Not available with -A or -LC) OTHER OPTIONS

-K = (3.50 mm) .138" DIA Polyimide film Pick & Place Pad (Required for SEMS)

= (5.50 mm) .217" DIA Polyimide film Pick & Place Pad (Required for TEMS)

> -TR = Tape & Reel

-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)


SEM Board Mates: TEM


TEMS

Slim Header

SEMS Board Mates:








View complete specifications at: samtec.com?SEM & samtec.com?SEMS


TEM **Board Mates:** SEM, SEML

TEMS **Board Mates: SEMS**





MATED HEIGHTS						
STACK HEIGHT	A	MATED HEIGHT*				
-03.0	(5.610) .2209	6 mm				
-04.0	(6.610) .2602	7 mm				
-07.0	(9.610) .3783	10 mm				



Note: Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?TEM & samtec.com?TEMS

^{*}Processing conditions will affect mated height.