
Socket for PCBs; straight; 3-pole; Cod. B; pink

www.wago.com/770-883/081-000








 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

www.wago.com/770-883/081-000





Item description

Female connector/socket WINSTA® MIDI 3-pole

WAGO has various connection solutions for any challenge in building installation, for example, the WINSTA® MIDI female connector/socket. Our remarkable number of pluggable PCB connectors with various insertion directions and operating variants offers you the perfect solution for your application at all times.

The coding options reduce installation errors, allowing fast, secure wiring of all components. B coding enables the *WINSTA®* MIDI pcb connectors to be used for application control in automation, robotics, and mechanical engineering. This pcb connector can be employed for a voltage load of up to 25 A. As a result, pcb connector can also be used for high power loads. *WINSTA®* MIDI with Push-in CAGE CLAMP® spring pressure connection technology is found in can be found in a variety of projects you can use for quick, easy, flexible, and secure installation.

Push-in CAGE CLAMP® spring pressure connection technology – pluggable installation instead of laborious screw connections!

WINSTA® is the pluggable connection system that is optimally tailored to the strict requirements of electrical installation. It allows error-free installation of cables and components, quickly and reliably. Choose quality and durability – the WINSTA® MIDI pcb connector with protection against mismating from WAGO makes the installation of electrical components noticeably easier.

- pcb connectors with protection against mismating
- simple circuits
- with B coding for use in process automation, such as lighting technology
- fast, secure installation

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/770-883/081-000



Data Notes

Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/.

Other pole markings

Electrical data

Note on contact resistance	approx. 1 m Ω of contact resistance
	approx. $0.25~\text{m}\Omega$ contact transition plug/socket
Ratings per	IEC/EN 60664-1
Nominal voltage (III/3)	250 V
Rated surge voltage (III/3)	4 kV
Rated current	25 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3
Hinweis für den amerikanischen Markt	Application note for the U.S. market (USR): Some versions may also be used for current interruption in accordance with the UL certificate in select applications with currents below 16 A and voltages up to 600 V. For further information, please contact your local sales office.
Rated voltage UL 1977	600 V
Rated current UL 1977	23 A

Connection data

Total number of potentials	3	
Number of levels	1	
Pole No.	3	

Physical data

Pin spacing	10 mm / 0.394 inch
Width	27 mm / 1.063 inch
Height	29.5 mm / 1.161 inch
Height from the surface	26 mm / 1.024 inch
Depth	14.6 mm / 0.575 inch
Solder pin length	3.5 mm
Solder pin dimensions	1 x 0.8 mm
Drilled hole diameter with tolerance	1.5 ^{(-0.1} +0.1) mm

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/770-883/081-000



Mechanical data

Application	Measurement and regulation technology
Coding	В
Marking	125
Potentialkennzeichnung	125
Mating force of a plug-in connection	approx. 20 70 N (depending on pole number)
Retention force of a plug-in connection	Locked: > 80 N
Unmating force of a plug-in connection	Unlocked: approx. 20 70 N (depending on pole number)
Number of mating cycles	200, without resistive load
Design	straight

Plug-in connection

Contact type (pluggable connector)	Female connector/socket
Connector (connection type)	for PCB
Mismating protection	Yes
Note on mismating protection	All WINSTA® components are 100% protected against mismating when: a.) plugging different numbers of poles b.) plugging while rotated 180 c.) plugging while laterally staggered d.) plugging one pole
Mating direction to the PCB	90°
Locking lever	yes
Locking of plug-in connection	locking lever
Hinweis zur Verriegelung	All connectors for mounted installations (snap-in versions for lighting fixtures or devices, all types of PCB and distribution connectors) are factory-equipped with locking levers to ensure plugs and sockets are securely locked. Additional locking levers are only required for flying leads (plug/socket).

PCB contact

PCB Contact	тнт
Solder pin arrangement	2 in-line solder pins/pole
Number of solder pins per potential	2

Material data

Color pink

 $\label{lem:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/770-883/081-000



Insulation material	Polyamide (PA66)
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Copper or copper alloy (surface-treated)
Fire load	0.12MJ
Weight	6.4 g

Environmental requirements

Processing temperature	-5 +40 °C
Continuous operating temperature	-35 +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

PU (SPU)	100 Stück
Packaging type	box
Country of origin	PL
GTIN	4050821553519
Customs tariff number	85366990990

Approvals / Certificates

UL-Approvals

			Certificate
Logo	Approval	Additional Approval Text	name
	cURus	UL 1977	E45171
	Underwriters Laboratories Inc.		

c **T**us

Counterpart



Item no.770-293/081-000 Plug; 3-pole; 4,00 mm²; pink

www.wago.com/770-293/081-000

Required accessories

Cover

Cover

Item no.: 770-201

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/770-883/081-000





Lockout cap; 12-pole, separable; 12-pole; for sockets; black

www.wago.com/770-201



Item no.: 770-221

Lockout cap; for socket; 12-pole; separable; white

www.wago.com/770-221

Downloads CAD/CAE-Data

CAD data

2D/3D Models 770-883/081-000 **URL** Download

PCB Design

URL Symbol and Footprint 770-883/081-000 Download

CAx data for your PCB design, consisting of "schematic symbols and PCB footprints", allow easy integration of the WAGO component into your development environment.

Supported formats:

- Accel EDA 14 & 15
- Altium 6 to current version
- Cadence Allegro
- DesignSpark
- **Eagle Libraries**
- KiCad
- Mentor Graphics BoardStation
- Mentor Graphics Design Architect
- Mentor Graphics Design Expedition 99 and 2000
- OrCAD 9.X PCB and Capture
- PADS PowerPCB 3, 3.5, 4.X, and 5.X
- PADS PowerPCB and PowerLogic 3.0
- PCAD 2000, 2001, 2002, 2004, and 2006
- Pulsonix 8.5 or newer
- STL
- 3D STEP
- **TARGET 3001!**
- View Logic ViewDraw
- Quadcept
- Zuken CadStar 3 and 4

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Email: info.de@wago.com | Web: www.wago.com

Phone: +49571 887-0 | Fax: +49571 887-169

Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/770-883/081-000



Zuken CR-5000 and CR-8000

PCB Component Libraries (EDA), PCB CAD Library Ultra Librarian

CAE data

ZUKEN Portal 770-883/081-000 URL Download

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 770-883/081-000 URL Download

Socket for PCBs; straight; 3-pole; Cod. B; pink

Installation Notes

Product family

WINSTA® MIDI

Show all products from the family

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.