

Taiwan Semiconductor

15A, 600V - 800V Low V_F Standard Bridge Rectifier

FEATURES

- AEC-Q101 qualified available
- Low Forward drop enhance the efficiency
- Oxide Planar chip junction
- High surge current capability
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application


MECHANICAL DATA

- Case: TS-6P
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Mounting torque: 0.80 N·m maximum
- Polarity: As marked
- Weight: 7.15g (approximately)

KEY PARAMETERS					
PARAMETER	VALUE	UNIT			
I _F	15	А			
V _{RRM}	600 - 800	V			
I _{FSM}	200	А			
T _{J MAX}	150	°C			
Package	TS-6P				
Configuration	Quad				







ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)					
PARAMETER		SYMBOL	TS15PL05G	TS15PL06G	UNIT
Marking code on the device			TS15PL05G	TS15PL06G	
Repetitive peak reverse voltage		V _{RRM}	600	800	V
Reverse voltage, total rms value		V _{R(RMS)}	420	560	V
Forward current		I _F	15		А
Surge peak forward current, single half	t = 8.3ms	1	200		А
sine-wave superimposed on rated load	t = 1.0ms	I _{FSM}	630		А
Rating of fusing (t<8.3ms)		l ² t	166		A ² s
Junction temperature		TJ	- 55 to +150		°C
Storage temperature		T _{STG}	- 55 to +150		°C



Taiwan Semiconductor

THERMAL PERFORMANCE

PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-case thermal resistance	R _{eJC}	1	°C/W

Thermal Performance Note: Mounted on heat sink with 4" x 6" x 0.25" Al-Plate

ELECTRICAL SPECIFICATIONS ($T_A = 25^{\circ}C$ unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
Forward voltage per diode ⁽¹⁾	TS15PL05G	I _F = 7.5A, T _J = 25°C	V _F	-	0.90	V
	TS15PL06G			-	0.93	V
Reverse current @ rated V _R per diode ⁽²⁾		$T_J = 25^{\circ}C$	- I _R	-	5	μA
		T _J = 125°C		-	150	μA

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION					
ORDERING CODE ⁽¹⁾⁽²⁾	PACKAGE	PACKING			
TS15PLxG	TS-6P	15 / Tube			
TS15PLxGH	TS-6P	15 / Tube			

Notes:

1. "x" defines voltage from 600V(TS15PL05G) to 800V(TS15PL06G)

2. "H" means AEC-Q101 qualified



Taiwan Semiconductor

CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$





Fig.1 Forward Current Derating Curve

Fig.3 Typical Reverse Characteristics



1000

CAPACITANCE (pF)

100

10

0.1

225 200 PEAK FORWARD SURGE CURRENT (A) 8.3ms single half sine wave 175 150 125 100 75 50 25 0 10 100 1 NUMBER OF CYCLES AT 60 Hz

Fig.5 Maximum Non-Repetitive Forward Surge Current

Fig.2 Typical Junction Capacitance

1

10

REVERSE VOLTAGE (V)

Fig.4 Typical Forward Characteristics

100


f=1.0MHz Vsig=50mVp-p



TS15PL05G – TS15PL06G

Taiwan Semiconductor

PACKAGE OUTLINE DIMENSIONS



DIM.	Unit	(mm)	Unit (inch)		
Divi.	Min.	Max.	Min.	Max.	
A	4.40	4.80	0.173	0.189	
A1	3.40	3.80	0.134	0.150	
A2	2.50	2.90	0.098	0.114	
b	0.90	1.10	0.035	0.043	
b2	2.00	2.40	0.079	0.094	
с	0.65	0.75	0.026	0.030	
D	19.70	20.30	0.776	0.799	
D2	10.80	11.20	0.425	0.441	
D3	-	4.80	-	0.189	
E	29.70	30.30	1.169	1.193	
E2	2.30	2.70	0.091	0.106	
е	7.30	7.70	0.287	0.303	
e1	9.80	10.20	0.386	0.402	
L	17.00	18.00	0.669	0.709	
L4	3.80	4.20	0.150	0.165	
L5	0.45	0.65	0.018	0.026	
Р	3.10	3.40	0.122	0.134	

MARKING DIAGRAM



- P/N = Marking Code
- G = Green Compound
- YWW = Date Code
- F = Factory Code



TS15PL05G – TS15PL06G

Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.