#### **FEATURES:**

- Phase-Lock Loop Clock Distribution
- 10MHz to 133MHz operating frequency
- · Distributes one clock input to one bank of five outputs
- · Zero Input-Output Delay
- Output Skew < 250ps
- Low jitter <200 ps cycle-to-cycle</li>
- IDT2305-1 for Standard Drive
- IDT2305-1H for High Drive
- · No external RC network required
- Operates at 3.3V VDD
- · Power down mode
- · Available in SOIC/TSSOP packages


#### **DESCRIPTION:**

The IDT2305 is a high-speed phase-lock loop (PLL) clock buffer, designed to address high-speed clock distribution applications. The zero delay is achieved by aligning the phase between the incoming clock and the output clock, operable within the range of 10 to 133MHz.


The IDT2305 is an 8-pin version of the IDT2309. IDT2305 accepts one reference input, and drives out five low skew clocks. The -1H version of this device operates, up to 133MHz frequency and has a higher drive than the -1 device. All parts have on-chip PLLs which lock to an input clock on the REF pin. The PLL feedback is on-chip and is obtained from the CLKOUT pad. In the absence of an input clock, the IDT2305 enters power down. In this mode, the device will draw less than  $25\mu\text{A}$ , the outputs are tri-stated, and the PLL is not running, resulting in a significant reduction of power.

The IDT2305 is characterized for both Industrial and Commercial operation.

### **FUNCTIONAL BLOCK DIAGRAM**



#### **PINCONFIGURATION**



SOIC/TSSOP TOP VIEW

### **APPLICATIONS:**

- SDRAM
- Telecom
- Datacom
- PC Motherboards/Workstations
- Critical Path Delay Designs

# ABSOLUTE MAXIMUM RATINGS(1)

Symbol	Rating	Max.	Unit
VDD	Supply Voltage Range	-0.5 to +4.6	V
VI <sup>(2)</sup>	Input Voltage Range (REF)	-0.5 to +5.5	V
Vı	Input Voltage Range	-0.5 to	V
	(except REF)	VDD+0.5	
IIK (VI < 0)	Input Clamp Current	-50	mA
Io (Vo = 0 to VDD)	Continuous Output Current	±50	mA
VDD or GND	Continuous Current	±100	mA
TA = 55°C	Maximum Power Dissipation	0.7	W
(in still air)(3)			
Tstg	Storage Temperature Range	-65 to +150	°C
Operating	Commercial Temperature	0 to +70	°C
Temperature	Range		
Operating	Industrial Temperature	-40 to +85	°C
Temperature	Range		

#### NOTES:

- 1. Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.
- The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
- The maximum package power dissipation is calculated using a junction temperature of 150°C and a board trace length of 750 mils.

#### **PINDESCRIPTION**

Pin Name	Pin Number	Туре	Functional Description
REF	1	IN	Input reference clock, 5 Volt tolerant input
CLK2 <sup>(1)</sup>	2	Out	Output clock
CLK1 <sup>(1)</sup>	3	Out	Output clock
GND	4	Ground	Ground
CLK3 <sup>(1)</sup>	5	Out	Output clock
VDD	6	PWR	3.3V Supply
CLK4 <sup>(1)</sup>	7	Out	Output clock
CLKOUT <sup>(1)</sup>	8	Out	Output clock, internal feedback on this pin

#### NOTES:

1. Weak pull down on all outputs.

# **OPERATING CONDITIONS-COMMERCIAL**

Symbol	Parameter	Min.	Max.	Unit
VDD	Supply Voltage	3	3.6	V
TA	Operating Temperature (Ambient Temperature)	0	70	°C
CL	Load Capacitance < 100MHz	_	30	pF
	Load Capacitance 100MHz - 133MHz	_	10	
CIN	Input Capacitance	_	7	pF

## DC ELECTRICAL CHARACTERISTICS-COMMERCIAL

Symbol	Parameter	C	Conditions	Min.	Max.	Unit
VIL	Input LOW Voltage Level			_	0.8	V
Vih	Input HIGH Voltage Level			2	_	V
lıL	Input LOW Current	VIN = 0V		_	50	μΑ
Іін	Input HIGH Current	VIN = VDD	VIN = VDD		100	μΑ
Vol	Output LOW Voltage	Standard Drive	IOL = 8mA	_	0.4	V
		High Drive	IoL = 12mA (-1H)			
Vон	Output HIGH Voltage	Standard Drive	IOH = -8mA	2.4	_	V
		High Drive	Iон = -12mA (-1H)			
IDD_PD	Power Down Current	REF = 0MHz		_	12	μΑ
IDD	Supply Current	Unloaded Outputs at 66.	66MHz	_	32	mA

# SWITCHING CHARACTERISTICS (2305-1)-COMMERCIAL (1,2)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
tı	Output Frequency	10pF Load	10	_	133	MHz
		30pF Load	10	_	100	
	Duty Cycle = t2 ÷ t1	Measured at 1.4V, Fout = 66.66MHz	40	50	60	%
t3	RiseTime	Measured between 0.8V and 2V	_	_	2.5	ns
t4	FallTime	Measured between 0.8V and 2V	_	_	2.5	ns
t5	Output to Output Skew	All outputs equally loaded	-	_	250	ps
t6	Delay, REF Rising Edge to CLKOUT Rising Edge	Measured at VDD/2	_	0	±350	ps
t	Device-to-Device Skew	Measured at VDD/2 on the CLKOUT pins of devices	_	0	700	ps
tı	Cycle-to-Cycle Jitter, pk - pk	Measured at 66.66MHz, loaded outputs	_	_	200	ps
tlock	PLL Lock Time	Stable power supply, valid clock presented on REF pin	_	_	1	ms

- 1. REF Input has a threshold voltage of VDD/2.
- 2. All parameters specified with loaded outputs.

# SWITCHING CHARACTERISTICS (2305-1H)-COMMERCIAL (1,2)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
tı	Output Frequency	10pF Load	10	_	133	MHz
		30pF Load	10	_	100	
	Duty Cycle = t2 ÷ t1	Measured at 1.4V, Fout = 66.66MHz	40	50	60	%
	Duty Cycle = t2 ÷ t1	Measured at 1.4V, Fouт <50МHz	45	50	55	%
ts	RiseTime	Measured between 0.8V and 2V		_	1.5	ns
t4	Fall Time	Measured between 0.8V and 2V		_	1.5	ns
t5	Output to Output Skew	All outputs equally loaded	_	_	250	ps
t6	Delay, REF Rising Edge to CLKOUT Rising Edge	Measured at VDD/2	_	0	±350	ps
t	Device-to-Device Skew	Measured at VDD/2 on the CLKOUT pins of devices	_	0	700	ps
ts	Output Slew Rate	Measured between 0.8V and 2V using Test Circuit #2	1	_	_	V/ns
tı	Cycle-to-Cycle Jitter, pk - pk	Measured at 66.66MHz, loaded outputs	_	_	200	ps
tlock	PLL Lock Time	Stable power supply, valid clock presented on REF pin	_	_	1	ms

#### NOTES:

- 1. REF Input has a threshold voltage of VDD/2.
- 2. All parameters specified with loaded outputs.

## **OPERATING CONDITIONS-INDUSTRIAL**

Symbol	Parameter	Min.	Max.	Unit
Vdd	Supply Voltage	3	3.6	V
TA	Operating Temperature (Ambient Temperature)	-40	+85	°C
CL	Load Capacitance < 100MHz	_	30	pF
	Load Capacitance 100MHz - 133MHz	_	10	
Cin	InputCapacitance	_	7	pF

# DC ELECTRICAL CHARACTERISTICS-INDUSTRIAL

Symbol	Parameter	C	conditions	Min.	Max.	Unit
VIL	Input LOW Voltage Level			_	0.8	V
ViH	Input HIGH Voltage Level			2	_	V
lıL	Input LOW Current	VIN = 0V		_	50	μA
Іін	Input HIGH Current	VIN = VDD	VIN = VDD		100	μΑ
Vol	Output LOW Voltage	Standard Drive	IOL = 8mA	_	0.4	V
		High Drive	IOL = 12mA (-1H)			
Vон	Output HIGH Voltage	Standard Drive	IOH = -8mA	2.4	_	V
		High Drive	Iон = -12mA (-1H)			
IDD_PD	Power Down Current	REF = 0MHz		_	25	μA
ldd	Supply Current	Unloaded Outputs at 66.	66MHz	_	35	mA

# SWITCHING CHARACTERISTICS (2305-1) - INDUSTRIAL (1,2)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
tı	Output Frequency	10pF Load	10	_	133	MHz
		30pF Load	10	_	100	
	Duty Cycle = t2 ÷ t1	Measured at 1.4V, FOUT = 66.66MHz	40	50	60	%
ts	RiseTime	Measured between 0.8V and 2V	-	_	2.5	ns
t4	FallTime	Measured between 0.8V and 2V	_	_	2.5	ns
t5	Output to Output Skew	All outputs equally loaded		_	250	ps
t6	Delay, REF Rising Edge to CLKOUT Rising Edge	Measured at VDD/2	-	0	±350	ps
t7	Device-to-Device Skew	Measured at VDD/2 on the CLKOUT pins of devices	-	0	700	ps
tı	Cycle-to-Cycle Jitter, pk - pk	Measured at 66.66MHz, loaded outputs	_	_	200	ps
tLOCK	PLL Lock Time	Stable power supply, valid clock presented on REF pin	_	_	1	ms

#### NOTES:

- 1. REF Input has a threshold voltage of VDD/2.
- 2. All parameters specified with loaded outputs.

# SWITCHING CHARACTERISTICS (2305-1H)-INDUSTRIAL (1,2)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
tı	Output Frequency	10pF Load	10	_	133	MHz
		30pF Load	10	_	100	
	Duty Cycle = t2 ÷ t1	Measured at 1.4V, Fouт = 66.66MHz	40	50	60	%
	Duty Cycle = t2 ÷ t1	Measured at 1.4V, Fouт <50MHz	45	50	55	%
t3	RiseTime	Measured between 0.8V and 2V	-	_	1.5	ns
t4	Fall Time	Measured between 0.8V and 2V	1	-	1.5	ns
t5	Output to Output Skew	All outputs equally loaded	1	-	250	ps
t6	Delay, REF Rising Edge to CLKOUT Rising Edge	Measured at VDD/2		0	±350	ps
t7	Device-to-Device Skew	Measured at VDD/2 on the CLKOUT pins of devices	_	0	700	ps
ts	Output Slew Rate	Measured between 0.8V and 2V using Test Circuit #2	1	_	_	V/ns
tı	Cycle-to-Cycle Jitter, pk - pk	Measured at 66.66MHz, loaded outputs	_	_	200	ps
tlock	PLL Lock Time	Stable power supply, valid clock presented on REF pin	_	_	1	ms


- 1. REF Input has a threshold voltage of VDD/2.
- 2. All parameters specified with loaded outputs.

#### ZERO DELAYAND SKEW CONTROL

All outputs should be uniformly loaded in order to achieve Zero I/O Delay. Since the CLKOUT pin is the internal feedback for the PLL, its relative loading can affect and adjust the input/output delay. The Output Load Difference diagram illustrates the PLL's relative loading with respect to the other outputs that can adjust the Input-Output (I/O) Delay.


For designs utilizing zero I/O Delay, all outputs including CLKOUT must be equally loaded. Even if the output is not used, it must have a capacitive load equal to that on the other outputs in order to obtain true zero I/O Delay. If I/O Delay adjustments are needed, use the Output Load Difference diagram to calculate loading differences between the CLKOUT pin and other outputs. For zero output-to-output skew, all outputs must be loaded equally.


#### REF TO CLKA/CLKB RELAY vs. OUTPUT LOAD DIFFERENCE BETWEEN CLKOUT PIN AND CLKA/CLKB PINS




OUTPUT LOAD DIFFERENCE BETWEEN CLKOUT PIN AND CLKA/CLKB PINS (pF)

# **SWITCHING WAVEFORMS**







All Outputs Rise/Fall Time



Output to Output Skew




Input to Output Propagation Delay




Device to Device Skew

# **TESTCIRCUITS**




Test Circuit 1 (all Parameters Except t8)




Test Circuit 2 (t8, Output Slew Rate On -1H Devices)

# TYPICAL DUTY CYCLE<sup>(1)</sup> AND IDD TRENDS<sup>(2)</sup> FOR IDT2305-1




- 1. Duty Cycle is taken from typical chip measured at 1.4V.
- 2. IDD data is calculated from IDD = ICORE + nCVf, where ICORE is the unloaded current. (n = Number of outputs; C = Capacitance load per output (F); V = Supply Voltage (V); f = Frequency (Hz))


# TYPICAL DUTY CYCLE(1) AND IDD TRENDS(2) FOR IDT2305-1H



- 1. Duty Cycle is taken from typical chip measured at 1.4V.
- Ibb data is calculated from IDD = ICORE + nCVf, where ICORE is the unloaded current. (n = Number of outputs; C = Capacitance load per output (F); V = Supply Voltage (V); f = Frequency (Hz))

# PACKAGE OUTLINE AND PACKAGE DIMENSIONS-SOIC





150 mil (Narrow Body) SOIC

( =, ,						
SYMBOL		meters IMENSIONS	In Inches (1) COMMON DIMENSIONS			
	MIN	MAX	MIN	MAX		
Α	1.35	1.75	.0532	.0688		
A1	0.10	0.25	.0040	.0098		
В	0.33	0.51	.0130	.0200		
С	0.19	0.25	.0075	.0098		
D	SEE VARIATIONS		SEE VAF	RIATIONS		
E	3.80	4.00	.1497	.1574		
е	1.27 BASIC		0.050	BASIC		
Н	5.80	6.20	.2284	.2440		
h	0.25	0.50	.010	.020		
L	0.40	1.27	.016 .050			
N	SEE VAF	RIATIONS	SEE VARIATIONS			
	0°	8°	0°	8°		


# **VARIATIONS**

N	D (r	mm)	D (inch) (1)		
IN	MIN	MAX	MIN	MAX	
8	4.80	5.00	.1890	.1968	
14	8.55	8.75	.3367	.3444	
16	9.80	10.00	.3859	.3937	


NOTE:
1. For reference only. Controlling dimensions are in mm.

For reference only. Controlling dimensions are in mm.

## PACKAGE OUTLINE AND PACKAGE DIMENSIONS-TSSOP



# **ORDERING INFORMATION**



Ordering Code	Package Type	Operating Range
2305-1DCG8 (tape and reel)	8-Pin SOIC	Commercial
2305-1DCG	8-Pin SOIC	Commercial
2305-1DCGI8 (tape and reel)	8-Pin SOIC	Industrial
2305-1DCGI	8-Pin SOIC	Industrial
2305-1HDCG	8-Pin SOIC	Commercial
2305-1HDCG8 (tape and reel)	8-Pin SOIC	Commercial
2305-1HDCGI	8-Pin SOIC	Industrial
2305-1HDCGI8 (tape and reel)	8-Pin SOIC	Industrial
2305-1PGGI	8-Pin TSSOP	Industrial
2305-1PGG	8-Pin TSSOP	Commercial

(G=Lead-free, RoHS compliant)

#### **IMPORTANT NOTICE AND DISCLAIMER**

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

#### **Corporate Headquarters**

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

#### **Trademarks**

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

#### **Contact Information**

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit <a href="https://www.renesas.com/contact-us/">www.renesas.com/contact-us/</a>.