

5352269-1 ✓ ACTIVE



Z-PACK | Z-PACK 2mm HM

TE Internal #: 5352269-1

Hard Metric Backplane Connectors, PCB Mount Receptacle,  $\leq 1$  Gb


/s, 19 Column, 5 Row, Mezzanine, 95 Position, 2 mm [.078 in]

Centerline, Z-PACK 2mm HM

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Hard Metric Backplane Connectors >

Hard Metric Backplane Receptacle Connector: Mezzanine, 2mm



PCB Connector Assembly Type: **PCB Mount Receptacle**

Data Rate:  $\leq 1$  Gb/s

Number of Columns: **19**

Number of Rows: **5**

Backplane Architecture: **Mezzanine**

[All Hard Metric Backplane Receptacle Connector: Mezzanine, 2mm \(27\)](#)

## Features

### Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Backplane Interface Type          | 2mm HM                |
| PCB Connector Assembly Type       | PCB Mount Receptacle  |
| Connector System                  | Board-to-Board        |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |

### Configuration Features

|                                 |                         |
|---------------------------------|-------------------------|
| Mating & Unmating Configuration | Make First / Break Last |
| Rows Loaded                     | A, B, C, D, E           |
| Number of Signal Positions      | 95                      |
| Number of Columns               | 19                      |
| Number of Rows                  | 5                       |
| Backplane Architecture          | Mezzanine               |



|                     |    |
|---------------------|----|
| Number of Positions | 95 |
|---------------------|----|

|                       |          |
|-----------------------|----------|
| PCB Mount Orientation | Vertical |
|-----------------------|----------|

### Signal Characteristics

|                   |          |
|-------------------|----------|
| Crosstalk Version | Standard |
|-------------------|----------|

|           |         |
|-----------|---------|
| Data Rate | ≤1 Gb/s |
|-----------|---------|

### Body Features

|                       |      |
|-----------------------|------|
| Primary Product Color | Gray |
|-----------------------|------|

### Contact Features

|                         |        |
|-------------------------|--------|
| Feedthrough Post Length | 3.3 mm |
|-------------------------|--------|

|                        |      |
|------------------------|------|
| CompactPCI Designation | None |
|------------------------|------|

|              |        |
|--------------|--------|
| Contact Type | Socket |
|--------------|--------|

|                               |        |
|-------------------------------|--------|
| Contact Underplating Material | Nickel |
|-------------------------------|--------|

|   |     |
|---|-----|
| PCB Contact Termination Area Plating Material | Tin |
|---|-----|

|                       |                 |
|-----------------------|-----------------|
| Contact Base Material | Phosphor Bronze |
|-----------------------|-----------------|

|                                      |      |
|--------------------------------------|------|
| Contact Mating Area Plating Material | Gold |
|--------------------------------------|------|

|  |                 |
|--|-----------------|
| Contact Mating Area Plating Material Thickness | 1.27 μm[50 μin] |
|--|-----------------|

|                              |       |
|------------------------------|-------|
| Contact Current Rating (Max) | 1.5 A |
|------------------------------|-------|

### Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

### Housing Features

|                  |                |
|------------------|----------------|
| Housing Material | Polyester - GF |
|------------------|----------------|

|                    |               |
|--------------------|---------------|
| Centerline (Pitch) | 2 mm[.078 in] |
|--------------------|---------------|

### Dimensions

|                         |       |
|-------------------------|-------|
| Backplane Module Length | 38 mm |
|-------------------------|-------|

### Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |
|-----------------------------|----------------------------|

### Operation/Application

|          |    |
|----------|----|
| Shielded | No |
|----------|----|

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

### Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|



### Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 11   |
| Packaging Method   | Tube |

### Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not applicable for solder process capability  |


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Compatible Parts

|  |   |
|--|---|
|  <p>TE Part # 122561-1<br/>SUPPORT ANVIL 2MM H.M. 7 ROW</p> |  <p>TE Part # 6392175-1<br/>Z-PACK/B-19 M-HDR 95POS</p> |
|--|---|

### Also in the Series | Z-PACK 2mm HM



Backplane Connector Housings(4)



Backplane Power Connectors(6)




Connector Caps & Covers(62)




Connector Contacts(2)



Connector Hardware(97)



Hard Metric Backplane Connectors (267)



High Speed Backplane Connectors(1)



Insertion & Extraction Tools(2)



Rectangular Power Connectors(87)

## Customers Also Bought



TE Part #5787082-5  
50 50SR R/A RCPT ASSY,RDSN L/F



TE Part #2199119-5  
M.2 0.5PITCH 3.2H KEY B 30U" AU



TE Part #5787962-1  
.8MM CHAMP STACK RCPT ASSY



TE Part #1241050-4  
2x4P MOD II BREAK AWAY HDR,SMD, BLISTER



TE Part #5406526-1  
INV MJ ASSY,1X2



TE Part #1-1478979-0  
SMA STR PCB SKT GSS



TE Part #1-2176328-7  
CRGP 1206 220R 1%



TE Part #5-2176383-9  
RQ 1206 40R2 0.1% 10PPM 1K RL



## Documents

### Product Drawings

Z-PACK/B19 VF 95P

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5352269-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5352269-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5352269-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

Application Specification

English