



1N5400 THRU 1N5408 SILICON RECTIFIER

FEATURES

- High current capability
- Plastic package has Underwriters Laboratory Flammability Classification 94V-0 utilizing Flame Retardant Epoxy Molding Compound.
- Exceeds environmental standards of MIL-S-19500/228
- Low leakage.

MECHANICAL DATA

Case: Molded plastic, DO-201AD


Terminals: Plated axial leads, solderable per MIL-STD-202, method 208 guaranteed

Polarity: Color band denotes cathode end

Mounting position: Any

Weight: 0.04ounce, 1.1gram

DO-201AD(DO-27)



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

	Symbols	1N5400	1N5401	1N5402	1N5403	1N5404	1N5405	1N5406	1N5407	1N5408	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	300	400	500	600	800	1000	Volts
Maximum RMS Voltage	V_{RMS}	35	70	140	210	280	350	420	560	700	Volts
Maximum DC Blocking Voltage	V_{DC}	50	100	200	300	400	500	600	800	1000	Volts
Maximum Average Forward Rectified Current 0.375" (9.5mm) Lead Length at $T_A=75$	$I_{(AV)}$	3.0									Amp
Peak Forward Surge Current, 8.3ms single half-sine-wave superimposed on rated load (JEDEC method)	I_{FSM}	125									Amp
Maximum Forward Voltage at 3.0A DC and 25	V_F	1.1									Volts
Maximum Reverse Current at $T_A=25$ at Rated DC Blocking Voltage $T_A=100$	I_R	5.0 1000									uAmp
Typical Junction Capacitance (Note 1)	C_J	50									pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	18									/W
Operating Junction Temperature Range	T_J	-55 to +125									
Storage Temperature Range	T_{stg}	-55 to +125									

NOTES:

1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.

2- Thermal Resistance Junction to Ambient and form junction to lead at 0.375" (9.5mm) lead length P.C.B. Mounted with 0.8x0.8" (20x20mm) copper pads.



1N5400 THRU 1N5408 SILICON RECTIFIER

RATINGS AND CHARACTERISTIC CURVES





FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- TYPICAL REVERSE CHARACTERISTICS

