


# BASIC BLADE & BEAM HEADER & SOCKET

(0.635 mm) .025" PITCH • BTS/BSS SERIES



**BTS**  
Mates:  
BSS

**BSS**  
Mates:  
BTS

<b>BTS</b>	<b>NO. OF POSITIONS PER ROW</b>	<b>01</b>	<b>PLATING OPTION</b>	<b>D</b>	<b>A</b>	<b>OTHER OPTION</b>
------------	---------------------------------	-----------	-----------------------	----------	----------	---------------------

-025, -050,  
-075, -100

**-F**  
= Gold Flash on contact,  
Matte Tin on tail

**-L**  
= 10 μ" (0.25 μm)  
Gold on contact,  
Matte Tin on tail


**-K**  
= (7.00 mm)  
.275" DIA  
Polyimide Film  
Pick & Place Pad

**-TR**  
= Tape & Reel  
(-100 positions max.)

**-FR**  
= Full Reel  
Tape & Reel  
(must order max.  
quantity per reel;  
contact Samtec for  
quantity breaks)  
(-100 positions max.)


## SPECIFICATIONS

**Insulator Material:**  
Liquid Crystal Polymer  
**Terminal Material:**  
Phosphor Bronze  
**Contact Material:**  
Phosphor Bronze  
**Plating:**  
Au or Sn over 50 μ" (1.27 μm) Ni  
**Current Rating:**  
1.8 A per pin  
(2 pins powered)  
**Operating Temp Range:**  
-55 °C to +125 °C



## PROCESSING

**Lead-Free Solderable:**  
Yes  
**SMT Lead Coplanarity:**  
(0.10 mm) .004" max  
**Board Stacking:**  
For applications requiring more than two connectors per board or 100 positions or higher, contact ipg@samtec.com



## ALSO AVAILABLE

MOQ Required

30 μ" (0.76 μm) Gold  
Other platings  
Other positions

<b>BSS</b>	<b>NO. OF POSITIONS PER ROW</b>	<b>01</b>	<b>PLATING OPTION</b>	<b>D</b>	<b>A</b>	<b>OTHER OPTION</b>
------------	---------------------------------	-----------	-----------------------	----------	----------	---------------------

-025, -050,  
-075, -100

**-F**  
= Gold Flash on contact,  
Matte Tin on tail

**-L**  
= 10 μ" (0.25 μm)  
Gold on contact,  
Matte Tin on tail



**-TR**  
= Tape & Reel  
(-100 positions maximum)

**-FR**  
= Full Reel  
Tape & Reel  
(must order maximum  
quantity per reel;  
contact Samtec for  
quantity breaks)  
(-100 positions maximum)

## MATED HEIGHT

LEAD STYLE	MATED HEIGHT*
-01	(5.00 mm) .197"

\*Processing conditions will affect mated height.



**Note:**  
Some lengths, styles and options are non-standard, non-returnable.