






LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
D		REVISED PER ECO-13-010626	31JUL2013	KH	RP		
E		REVISED PER ECO-19-012987	26AUG2019	AP	SY		



- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE). COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT, TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA

○ = SIGNAL
 ⊗ = GROUND
 RECOMMENDED PCB BOARD LAYOUT BACKPLANE, COMPONENT SIDE SHOWN
 SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN S. MAGARO 07JUN2007	TE Connectivity NAME HEADER ASSEMBLY, DOUBLE ENDED, 3 PAIR, 6 COLUMN TinMan
DIMENSIONS: mm		CHK W. DAVIS 07JUN2007	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. PATTERSON 20AUG2008	SIZE CAGE CODE DRAWING NO. RESTRICTED TO
0 PLC ±	1 PLC ±	PRODUCT SPEC	A100779C=1934338
2 PLC ±	3 PLC ±	APPLICATION SPEC	SCALE 8:1 SHEET 1 OF 1 REV E
4 PLC ±	ANGLES ±	WEIGHT	CUSTOMER DRAWING
MATERIAL	FINISH		