

170354-1 ✓ ACTIVE

TE Internal #: 170354-1

Socket Contact, Tin, 26 – 22 AWG Wire Size, .12 – .4 mm² Wire Size,
Phosphor Bronze, Signal, -4 – 221 °F [-20 – 105 °C]

[View on TE.com >](#)



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Wire Size: **.12 – .4 mm²**

Features

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	750 VAC
Insulation Resistance	500 MΩ

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	2 A

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Compatible Insulation Diameter Range	1.09 – 1.91 mm[.043 – .075 in]
Wire Size	.12 – .4 mm ²

Usage Conditions

--	--



Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	7000
--------------------	------

Packaging Method	Strip
------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #5172625-3
DRAWER CONN. FEMALE ASSY 24P



TE Part #172211-6
EIS CAP HSG FREE HANG 6P
NATUTURAL




TE Part #172211-2
EIS CAP HSG FREE HANG 2P
NATUTURAL



TE Part #1-172211-0
10P CAP HSG F/H EI S CONN.



TE Part #172025-1
MIC PLUG HSG 7 POS



TE Part #172775-1
MIC MK-2 REC B TYPE



TE Part #178479-1
AMP UP CAP HSG F/H 5P NATURAL



TE Part #917636-1
MATE-N-LOK PIN CONT H-PRESSURE



TE Part #1-937188-2
CRIMPER,WIRE



TE Part #915415-1
PULL BACK

Documents

Product Drawings

LOW PROFILE E.I. CONNECTOR

Japanese

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_170354-1_B1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_170354-1_B1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_170354-1_B1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[1-1773972-5_EIS_Connectors_Brochure](#)

English

Product Specifications

[Application Specification](#)

English

[Crimping of Low Profile "EI" Series Connector](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese

[Low Profile "EI" Series Connector](#)

Japanese