

10A, 600V - 1000V Standard Bridge Rectifier

FEATURES

- AEC-Q101 qualified available
- Thin Single-in-line low profile package ideal for compact required circuit
- Glass passivated chip junction
- High surge current capability
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply
- Adapters
- Lighting application

MECHANICAL DATA

- Case: KBJL
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Mounting torque: 0.56 N·m maximum
- · Polarity: As marked
- Weight: 2.50g (approximately)


KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	10	Α		
V_{RRM}	600 - 1000	V		
I _{FSM}	180	Α		
T_{JMAX}	150	°C		
Package	KBJL			
Configuration	Quad			











ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)					
PARAMETER	SYMBOL	TS10KL60	TS10KL80	TS10KL100	UNIT
Marking code on the device		TS10KL60	TS10KL80	TS10KL100	
Repetitive peak reverse voltage	V_{RRM}	600	800	1000	V
Reverse voltage, total rms value	$V_{R(RMS)}$	420	560	700	V
Forward current	I _F	10			Α
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	180			А
Rating for fusing (t<8.3ms)	l ² t	134.46			A ² s
Junction temperature	TJ	- 55 to +150			°C
Storage temperature	T _{STG}	- 55 to +150			°C



Taiwan Semiconductor

THERMAL PERFORMANCE					
PARAMETER	SYMBOL	TYP	UNIT		
Junction-to-case thermal resistance	R _{eJC}	1.5	°C/W		

Thermal Performance Note: Units mounted on 4" x 6" x 0.25" Al-plate

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	I _F = 5A,T _J = 25°C	V _F	-	1	V
Reverse current @ rated V _R per diode ⁽²⁾	T _J = 25°C	1	-	5	μA
	T _J = 125°C	I _R	-	150	μΑ

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾⁽²⁾	PACKAGE	PACKING		
TS10KLx	KBJL	20 / Tube		
TS10KLxH	KBJL	20 / Tube		

Notes:

- 1. "x" defines voltage from 600V(TS10KL60) to 1000V(TS10KL100)
- 2. "H" means AEC-Q101 qualified



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.3 Typical Reverse Characteristics



Fig.2 Typical Junction Capacitance





Fig.4 Typical Forward Characteristics







Fig.5 Maximum Non-Repetitive Forward Surge Current






Taiwan Semiconductor

PACKAGE OUTLINE DIMENSIONS

KBJL



DIM.	Unit (mm)		Unit (inch)	
DIIVI.	Min.	Max.	Min.	Max.
Α	4.00	4.40	0.157	0.173
A2	2.50	2.90	0.098	0.114
b	0.90	1.10	0.035	0.043
b2	2.10	2.30	0.083	0.091
С	0.30	0.70	0.012	0.028
c2	3.00	3.40	0.118	0.134
D	10.00	10.60	0.394	0.417
D1	5.50	5.90	0.217	0.232
D2	6.90	7.30	0.272	0.287
E	24.70	25.30	0.972	0.996
е	7.30	7.70	0.287	0.303
Н	24.90	25.50	0.980	1.004
L	14.40	15.40	0.567	0.606
L4	1.20	1.60	0.047	0.063
Р	3.30	3.50	0.130	0.138
P1	3.10	3.30	0.122	0.130

MARKING DIAGRAM



P/N = Marking Code

G = Green Compound YWW = Date Code

F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.