## KBU801G – KBU807G Taiwan Semiconductor

ABSOLUTE MAXIMUM F	RATINGS	$(T_A = 25^{\circ}C)$	C unless	otherwis	e noted)				
PARAMETER	SYMBOL	KBU 801G	KBU 802G	KBU 803G	KBU 804G	KBU 805G	KBU 806G	KBU 807G	UNIT
Marking code on the device		KBU 801G	KBU 802G	KBU 803G	KBU 804G	KBU 805G	KBU 806G	KBU 807G	
Repetitive peak reverse voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V
Reverse voltage, total rms value	V <sub>R(RMS)</sub>	35	70	140	280	420	560	700	V
Forward current	I <sub>F</sub>				8				Α
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	200			А				
Rating for fusing (t<8.3ms)	l <sup>2</sup> t				166				A <sup>2</sup> s
Junction temperature	TJ	- 55 to +150		°C					
Storage temperature	T <sub>STG</sub>	- 55 to +150			°C				

1

# 8A, 50V - 1000V Standard Bridge Rectifier

#### FEATURES


- Glass passivated chip junction
- Ideal for printed circuit board
- High case dielectric strength
- Typical I<sub>R</sub> less than  $0.1\mu A$
- High surge current capability
- UL Recognized File # E-326243
- RoHS Compliant

### APPLICATIONS


- Switching mode power supply (SMPS)
- Adapters
- Lighting application

### **MECHANICAL DATA**

- Case: KBU
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Mounting torque: 0.56 N·m maximum
- Polarity: As marked
- Weight: 7.20g (approximately)











Taiwan Semiconductor

THERMAL PERFORMANCE			
PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-ambient thermal resistance	R <sub>eja</sub>	18	°C/W
Junction-to-case thermal resistance	R <sub>eJC</sub>	3	°C/W

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_A = 25^{\circ}C$ unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
Forward voltage per diode <sup>(1)</sup>	$I_F = 4A, T_J = 25^{\circ}C$	V <sub>F</sub>	-	1.0	V
	$I_F = 8A, T_J = 25^{\circ}C$		-	1.1	V
Reverse current @ rated $V_R$ per diode <sup>(2)</sup>	$T_J = 25^{\circ}C$	- I <sub>R</sub>	-	5	μA
	T <sub>J</sub> = 125°C		-	500	μA
Junction capacitance per diode	1MHz, V <sub>R</sub> = $4.0$ V	CJ	400	-	pF

#### Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

ORDERING INFORMATION		
ORDERING CODE <sup>(1)</sup>	PACKAGE	PACKING
KBU8xG	KBU	100 / Tray

Notes:

1. "x" defines voltage from 50V(KBU801G) to 1000V(KBU807G)



### **CHARACTERISTICS CURVES**

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 





Fig.1 Forward Current Derating Curve

#### Fig.3 Typical Reverse Characteristics



1000

100

10

0.1

f=1.0MHz Vsig=50mVp-p

1

CAPACITANCE (pF)

225 PEAK FORWARD SURGE CURRENT (A) 200 8.3ms single half sine wave 175 150 125 100 75 50 25 0 100 10 1 NUMBER OF CYCLES AT 60 Hz

#### Fig.5 Maximum Non-Repetitive Forward Surge Current

**Fig.2 Typical Junction Capacitance** 

10


**REVERSE VOLTAGE (V)** 

100



Taiwan Semiconductor

## **PACKAGE OUTLINE DIMENSIONS**



	DIM. Unit (m		Unit (inch)		
Divi.	Min.	Min. Max.		Max.	
A	6.8	7.1	0.268	0.280	
A2	4.6	5.0	0.181	0.197	
b	1.2	1.3	0.047	0.051	
D	18.8	19.8	0.740	0.780	
D1	8.2 (TYP)		0.322	(TYP)	
E	22.7	23.7	0.894	0.933	
е	4.6	5.6	0.181	0.220	
L	20.0	-	0.787	-	

#### **MARKING DIAGRAM**



P/N	= Marking Code
YWW	= Date Code

F = Factory Code



Taiwan Semiconductor

# Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.