Т

# TS10K40 – TS10K100

Taiwan Semiconductor

# 10A, 400V - 1000V Standard Bridge Rectifier

## FEATURES

- Ideal for printed circuit board
- High surge current capability
- Typical  $I_R$  less than 0.1µA
- UL Recognized File # E-326243
- AEC-Q101 available
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

## APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- TV
- Monitor

# **MECHANICAL DATA**

- Case: TS4K
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Mounting torque: 8.17 in-lbs maximum
- Weight: 4.00g (approximately)


PARAMETER		SYMBOL	TS10K	TS10K	TS10K	TS10K	רואט
PARAMETER		OTIMBOE	40	60	80	100	
Marking code on the device			TS10K40	TS10K60	TS10K80	TS10K100	
Repetitive peak reverse voltage		V <sub>RRM</sub>	400	600	800	1000	V
Reverse voltage, total rms value		V <sub>R(RMS)</sub>	280	420	560	700	V
Forward current		I <sub>F</sub>	10				Α
Surge peak forward current single half sine-wave superimposed on rated load per diode		I <sub>FSM</sub>	150				A
Rating of fusing (t<8.3ms)		l <sup>2</sup> t	93			A <sup>2</sup> s	
Junction temperature		TJ	- 55 to +150				°C
Storage temperature		T <sub>STG</sub>	- 55 to +150				°C

1

KEY PARAMETERS			
PARAMETER	VALUE	UNIT	
I <sub>F</sub>	10	А	
V <sub>RRM</sub>	400 - 1000	V	
I <sub>FSM</sub>	150	А	
T <sub>J MAX</sub>	150	°C	
Package	TS4K		
Configuration	Quad		



HALOGEN





THERMAL PERFORMANCE			
PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-case thermal resistance	R <sub>eJC</sub>	2.3	°C/W

ELECTRICAL SPECIFICATIONS (T <sub>A</sub> = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
	$I_F = 5A, T_J = 25^{\circ}C$	V <sub>F</sub>	-	1.0	V
Forward voltage per diode <sup>(1)</sup>	$I_F = 10A, T_J = 25^{\circ}C$		-	1.1	V
	$T_J = 25^{\circ}C$	- I <sub>R</sub>	-	10	μA
Reverse current @ rated V <sub>R</sub> per diode <sup>(2)</sup>	T <sub>J</sub> =125°C		-	500	μA

Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

ORDERING INFORMATION		
ORDERING CODE <sup>(1)(2)</sup>	PACKAGE	PACKING
TS10Kx	TS4K	20 / Tube
TS10KxH	TS4K	20 / Tube

Notes:

1. "x" defines voltage from 400V(TS10K40) to 1000V(TS10K100)


2. "H" means AEC-Q101 qualified



# **CHARACTERISTICS CURVES**

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 

Fig.1 Forward Current Derating Curve



#### **Fig.3 Typical Reverse Characteristics**






Fig.5 Maximum Non-repetitive Forward Surge Current



#### Fig.2 Typical Junction Capacitance

**Fig.4 Typical Forward Characteristics** 






# TS10K40 – TS10K100 Taiwan Semiconductor

# **PACKAGE OUTLINE DIMENSIONS**

TS4K



A1 -	
P	
†	D2
	A2
c —	    -  - <b></b>

DIM.	Unit (mm)		Unit (	(inch)
	Min.	Max.	Min.	Max.
A	4.40	4.80	0.173	0.189
A1	3.40	3.80	0.134	0.150
A2	3.10	3.40	0.122	0.134
b	0.90	1.10	0.035	0.043
b2	2.00	2.30	0.079	0.091
с	0.50	0.70	0.020	0.028
D	14.70	15.30	0.579	0.602
D2	9.30	9.60	0.366	0.378
D3	3.00	5.00	0.118	0.197
E	24.70	25.30	0.972	0.996
е	7.30	7.70	0.287	0.303
L	17.00	18.00	0.669	0.709
L4	3.30	3.70	0.130	0.146
Р	3.10	3.60	0.122	0.142

## **MARKING DIAGRAM**



P/N	= Marking Code
G	= Green Compound
YWW	= Date Code
F	= Factory Code



Taiwan Semiconductor

# Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.