

2A, 1000V Fast Recovery Bridge Rectifier

FEATURES


- AEC-Q101 qualified available
- Ideal for printed circuit board
- Reliable low cost construction utilizing molded plastic technique
- High surge current capability
- UL Recognized File # E-326854
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

ΛD	DI		TIC	NS
AP	PL	ILA	IIU	MO

- Switching mode power supply (SMPS)
- Adapters
- Lighting application

MECHANICAL DATA

- Case: DBLS
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 0.360g (approximately)













DBLS





ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)				
PARAMETER	SYMBOL	RDBLS207G	UNIT	
Marking code on the device		RDBLS207G		
Repetitive peak reverse voltage	V_{RRM}	1000	V	
Reverse voltage, total rms value	V _{R(RMS)}	700	V	
Forward current	I _F	2	А	
Peak forward surge current, 8.3ms single half sinewave superimposed on rated load	I _{FSM}	50	А	
Rating for fusing (t<8.3ms)	l ² t	10.3	A ² s	
Junction temperature	T _J	- 55 to +150	°C	
Storage temperature	T _{STG}	- 55 to +150	°C	

1





THERMAL PERFORMANCE				
PARAMETER	SYMBOL	TYP	UNIT	
Junction-to-lead thermal resistance	$R_{\Theta JL}$	22	°C/W	
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	62	°C/W	

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	I _F = 2A, T _J = 25°C	V _F	-	1.15	V
Deverse surrent @ reted // ner diede(2)	T _J = 25°C		-	2	μΑ
Reverse current @ rated V _R per diode ⁽²⁾	T _J = 125°C	l _R	-	500	μΑ
Reverse recovery time	$I_F = 0.5A, I_R = 1.0A,$ $I_{rr} = 0.25A$	t _{rr}	_	300	ns
Reverse recovery time	$I_{rr} = 0.25A$		-	300	115

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING		
RDBLS207G	DBLS	1,500 / Tape & Reel		
RDBLS207GH	DBLS	1,500 / Tape & Reel		

Notes:

1. "H" means AEC-Q101 qualified



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.3 Typical Reverse Characteristics





Fig.2 Typical Junction Capacitance

Fig.4 Typical Forward Characteristics








Fig.5 Maximum Non-Repetitive Forward Surge Current



3




PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
Dilvi.	Min.	Max.	Min.	Max.
Α	2.40	2.60	0.094	0.102
A1	0.076	0.330	0.003	0.013
b	1.02	1.20	0.040	0.047
С	0.22	0.33	0.009	0.013
D	8.13	8.51	0.320	0.335
D1	3.90	4.10	0.154	0.161
E	9.80	10.30	0.386	0.406
E1	6.20	6.50	0.244	0.256
е	5.00	5.20	0.197	0.205
L	1.02	1.53	0.040	0.060

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
Α	2.30	0.091
В	1.30	0.051
С	6.90	0.272
D	11.50	0.453
E	2.60	0.102
F	9.20	0.362

MARKING DIAGRAM



P/N = Marking Code

G = Green Compound

YW = Date CodeF = Factory Code





Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale..