

Wireless Charging Receiver Module

Scope

- The purpose of the document is to specify the functional requirement of a WPC V1.2.3 Qi Medium Power RX Module. (WPC V1.2.3 downward compatible WPC V1.1).
- The Wireless Power supply's RX Module shall meet the ROHS requirement.

Applications

- Smartphone, Notebooks, Tablets
- Wearable devices
- Game accessories
- Power bank, Charging case
- Computer peripheral devices
- Medical Care

Product Characteristic

QPR-0108 is a WPC V1.2.3 Qi Medium Power (15W) wireless charging RX Module: Its transmission efficiency is up to 76% and can provide up to 15W transmission capacity. It enables provide DC5V x 1.25A; DC9V x 1.25A; DC12 x 1.25A three output options, maximum output power of 15W. It adopts intelligent identification system while its transmitter and receiver unit adopts UART (Universal asynchronous receiver/ transmitter) encrypted transmission control signal which is stipulated by V1.2.3 The console will process the corresponding power adjustment based on the encoding of the receiving unit.

Input Characteristics

Input Voltage & Frequency

Item	Minimum	Normal	Maximum
Input Frequency	110kHz	145kHz	205kHz
Input Voltage	6.5VAC	12.5VAC	15.5VAC

Energy Consumption
 At 6.5VAC or 15.5VAC, Energy Consumption ≤ 0.01A.

Output Characteristics (Rx Module)

Static Output Characteristics (Vo & R+N)

Low Power TX (5W)

Output Voltage	Rated	Load	Peak	Output Range	R + N
	Min. Load	Max. Load		Output Kange	IX T IN
5V DC	0.05A	1A	1.2A	5V ± 5.0%	\leq 250m Vp-p

Medium Power TX (15W)

Output Valtage	Rated Load		Peak	Output Banga	R + N
Output Voltage	Min. Load	Max. Load	reak	Output Range	N T N
9V DC	0.05A	1.25A	1.4A	5V ± 4.5%	\leq 300m Vp-p
12V DC	0.05A	1.25A	1.5A	5V ± 4.0%	\leq 300m Vp-p

Note:

Ripple & Noise: Measurement is done by 20MHz bandwidth oscilloscope and the output end paralleled a 0.1uF ceramic capacitor and a 47uF electrolysis capacitor.



Wireless Charging Receiver Module

Line & Load Regulation

Output Voltage	Load Condition		Line Regulation	Load Regulation
Output voitage	Min. Load	Max. Load	Line Regulation	Load Regulation
5V DC	0.05A	1.25A	± 5.0%	± 5.0%
9V DC	0.03A	1.25A	± 4.5%	± 4.5%
12V DC	0.03A	1.25A	± 4.0%	± 4.0%

Protection Requirement

Short Circuit Protection

When the output is short circuit to ground, the input power should decrease, the power supply remains undamaged and automatically recover when fault condition is removed.

Over Current Protection

OCP Point Limited: 120%~130% auto restart.

The output will be blocked when output is over-current, and should automatically recover when fault condition is removed.

Reliability Requirements

Reliability Test

Test Items	Test Conditions		
Storage at high temperature test	+60°C, 16hours		
Storage at low temperature test	-20°C, 16hours		
Operating at high temperature test	+40°C, 8hours		
Operating at low temperature test	-20°C, 8hours		
High/Low temperature cycle test	+45°C (2Hrs) → -20°C (2Hrs) → +45°C (2Hrs) → -20°C (2Hrs) continually work 24hours		

Burn-in

2hours under 35°C (±5°C) environment, nominal input voltage, nominal load.

Environment Requirement

- Operating Temperature and Relative Humidity
 0°C to +40°C, 20%RH to 80%RH @ altitude should be below 10000 feet.
- Storage Temperature and Relative Humidity
 -20°C to +60°C, 10%RH to 90%RH (non-condensing) @ altitude should be below 30000 feet.

Execution Standards (Compatible with these specifications)

EMC Standards

GB9254	GB17625.1	GB13837	FCC-Part15
EN55022	EN55024	CISPR22	EN61000-4-4
EN61000-3-2	EN61000-3-3	EN61000-4-2	EN61000-4-3
EN61000-4-5	EN61000-4-6	EN61000-4-8	EN61000-4-11


WPC V1.2.3 Qi Standards



Wireless Charging Receiver Module

Photo of Product

Front Side








Module


- Product Design Proposal
 - According to the standardization of Qi, there are three principles need to be careful:
 - (1) The distance between Tx Coil with PCB and other metal components is Min: 5.0mm.
 - (2) The distance between the surface of Tx Coil and the surface of product (Working Face) is 2.0^{+0.25}_{-0.5} mm, which means the thickness of the working face plastic is not more than 2.5mm.
 - (3) The surface distance between Tx Coil and Rx Coil is 3.0~4.5mm.
- PCBA Port Functional Illustration



PCBA: 32 * 17 * 1.5±0.1 mm

Coil + Shielding : 50 * 40 * 1.0±0.1 mm

Amount of space between the PCBA to Coil+Shielding as follows: 5 ~ 50 mm






Wireless Charging Receiver Module

Port	Pin	Name	Туре	Description
CL1	1	AC1	I	AC input power from receiver resonant.
2		AC2	I	AC input power from receiver resonant.
	1	GND	GND	Power and logic ground
	2	SDA	I	MCU_MSTR_I2C_SDA
	3	SCL	I	MCU_MSTR_I2C_SCL
	4	WHG_THERM_P	0	Connect to thermal sensor positive
	5	WHG_THERM_N	I	Connect to thermal sensor negative
CN1	6 DET_N		0	Open drain output that allows user to sense when receiver is on transmitter
	7	WPG_N	0	Open-drain output that allows user to sense when power is transferred to load
8		TS	I	Temperature sense. Can be pulled high to send end power transfer (EPT) or end of charge (EOC) to TX
		Out	0	Output pin, used to deliver power to the load (5V / 9V / 12V)

Rx Coil Spec

CN2



GND

0

Power and logic ground

(5V / 9V / 12V)

Output pin, used to deliver power to the load

Electrical specification @25°C

GND

Out

1

2

Parameters	Unit	Limit
Inductance, LS @100kHz, 1.0V, 0.26mm*2 → 10Turns	uH	8.5 ± 10%
Q		> 20
DCR	mΩ	130 ± 10%

Others

- Weight: 8 ± 1 g
- Major Test Equipment
 - (1) DC Supply
 - (2) Qi Tx_Module
 - (3) Electronic Load
 - (4) DPO3014 Digital Phosphor Oscilloscope
 - (5) Logical Analyzer
 - (6) CATS II BST