

## 5-V/100mA Low Power Low-Drop Fixed-Voltage Regulator with low current consumption

**ILE4264-2G**

The ILE 4264-2G is a Monolithic Integrated Low Power Low-Drop Fixed Voltage Regulator 5-V/100mA with low current consumption. The ILE 4264-2G is specially designed to create power source with 5V output voltage, loads up to 100 mA and drop voltage less than 0.5V. The regulator is designed to supply electronic device in automotive applications and some another applications. The ILE 4264-2G is equipped with additional protection against overvoltage of both polarities, load current limitation, short-circuit and over temperature shutdown of output voltage.




### ORDERING INFORMATION

Device	Operating Temperature Range	Package	Packing
ILE4264-2G	T <sub>J</sub> = -40° to 125° C	SOT-223	T&R

### Features

- Output voltage tolerance 5V ±3% (±2% up to 50 mA)
- Low-drop voltage
- Current capability up to 150 mA
- Very low current consumption
- Over temperature protection
- Reverse polarity proof
- Suitable for use in automotive electronics
- Short-circuit proof
- AEC-Q100 Qualified
- ESD Protection : HBM ±8.000V / MM ±400V / CDM ±2.000V

### Block Diagram



**Pin Description (for SOT-223 package)**

Pin	Symbol	Function
01	I	Input voltage; block to ground directly with a ceramic capacitor
03	Q	5-V output voltage; block to ground with a capacitor ( $C_a \geq 10 \mu F$ , $ESR \leq 4\Omega$ )
02, 04	GND	Ground

**Absolute Maximum Ratings**

Parameter	Symbol	Min	Max	Unit	Note
Input voltage	$V_I$	-42	45	V	
Input current	$I_i$				limited internally
Ground pin current	$I_{GND}$	50	-	mA	
Output voltage	$V_Q$	-0.3	32	V	
Output current	$I_Q$				limited internally
Junction temperature	$T_J$	-40	150	°C	
Storage temperature	$T_{stg}$	-50	150	°C	

\* Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

**Operating Range**

Parameter	Symbol	Min	Max	Unit
Input voltage	$V_I$	6	28	V
Junction temperature	$T_J$	-40	125	°C

**Thermal Resistances**

Parameter	Symbol	Min	Max	Unit
Thermal Resistances Junction-case , for conventional case P-SOT223-4-1	$R_{th\ jc}$	-	25*	°C/W
Thermal Resistances Junction-ambient, for conventional case P-SOT223-4-1, - without heat sink	$R_{th\ ja}$	-	220*	°C/W

\*  $R_{th\ ja}$  - Thermal Resistances Junction-ambient

Thermal resistance junction ambient for IC with heat dissipater is calculated by formula:

$$R_{th\ ja} = R_{th\ jc} + R_{th\ ca} \tag{1}$$

$R_{th\ jc}$  - thermal resistance junction case, °C /W.

Application circuit and heat dissipater have to provide  $T_J \leq 125 \text{ °C}$ .

Maximum power  $P_{tot}$ , BT, dissipated by IC for  $T_A$ , is calculated by formula:

$$P_{tot} = (125 - T_A) / R_{th\ ja} \tag{2}$$

125 – maximum permitable operating junction temperature, °C

### Electrical Characteristics

( $V_I=13.5\text{ V}$ ,  $-40\text{ °C} \leq T_J \leq 125\text{ °C}$ , unless specified otherwise)

Parameter	Symbol	Test Conditions	Limit Value			Unit	Note
			Min	Typ	Max		
Output voltage	$V_Q$	$9\text{ V} \leq V_I \leq 16\text{ V}$ $5\text{ mA} \leq I_Q \leq 50\text{ mA}$	4.9	5.0	5.1	V	
		$6\text{ V} \leq V_I \leq 21\text{ V}$ $5\text{ mA} \leq I_Q \leq 100\text{ mA}$	4.85	5.0	5.15		
Maximum output current	$I_{Qmax}$	$4.8\text{ V} \leq V_Q \leq 5.2\text{ V}$	150		500	mA	
Consumption current $I_q = I_I - I_Q$	$I_q$	$I_Q=0.1\text{ mA}$ , ( $T_J \leq 85\text{ °C}$ )	-		0.06	mA	
		$I_Q = 0.1\text{ mA}$	-		0.07		
		$I_Q = 50\text{ mA}$	-		4		
Drop-out voltage	$V_{Dr}$	$I_Q = 100\text{ mA}$	-	0.25	0.5	V	1
Load regulation	$\Delta V_{Q(I)}$	$1\text{ mA} \leq I_Q \leq 100\text{ mA}$ $V_I = 13.5\text{ V}$	-		90	mV	
Line regulation	$\Delta V_{Q(V)}$	$6\text{ V} \leq V_I \leq 28\text{ V}$ $I_Q = 1\text{ mA}$	-		30	mV	

Note:


<sup>1</sup> Drop voltage  $V_{Dr} = V_I - V_Q$  (measured when the output voltage  $V_Q$  has dropped 100 mV from the nominal value obtained at  $V_I = 13.5\text{ V}$ ).

### Typical Performance Parameters

( $V_I=13.5\text{ V}$ ,  $-40\text{ °C} \leq T_J \leq 125\text{ °C}$ , unless specified otherwise)

Parameter	Symbol	Test Condition	Typical Value	Unit
Power Supply Ripple Rejection	PSRR	$f_r = 100\text{ Hz}$ , $V_r = 3\text{ V}$ (peek-to-peek)	68	dB

### Application Circuit



In the ILE4264-2G the output voltage is divided and compared to an internal reference of 2.5 V typical. The regulation loop controls the output to achieve an output voltage of 5V with an accuracy of  $\pm 3\%$  at an input voltage range of  $5.5\text{ V} < V_i < 45\text{ V}$ .

Figure shows a typical application circuit. For stability of the control loop the ILE4264-2G output requires an output capacitor  $C_o$  of at least  $10\text{ }\mu\text{F}$  with a maximum permissible ESR of  $4\Omega$ . Tantalum as well as multi layer ceramic capacitors are suitable.


At the input of the regulator an input capacitor is necessary for compensating line influences ( $100\text{ nF}$  ceramic capacitor recommended). A resistor of approx.  $1\Omega$  in series with  $C_i$ , can damp any oscillation occurring due the input inductivity and the input capacitor.

In the application circuit shown in Figure an additional electrolytic input capacitor of  $470\text{ }\mu\text{F}$  is added in order to buffer supply line influences. This capacitor is recommended, if the device is sourced via long supply lines of several meters.


The ILE4264-2G can supply up to 150 mA. However for protection for high input voltage above 25 V, the output current is reduced (SOA protection).

Typical Performance Characteristics


Output Voltage  $V_O$  versus Temperature  $T_j$





Drop Voltage  $V_{dr}$  versus Output Current  $I_O$



Output Voltage  $V_O$  versus Input Voltage  $V_I$



Typical Performance Characteristics  
(continue)



Package Dimensions

