

3-1939755-6 ✓ ACTIVE




Free Height

TE Internal #: 3-1939755-6

PCB Mount Receptacle, Vertical, Board-to-Board, 220 Position, .5 mm [.02 in] Centerline, Gold, Surface Mount, Signal, Black, Free Height

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **220**

Centerline (Pitch): **.5 mm [.02 in]**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Ground Feature Type | Grounding Contact |
| PCB Connector Assembly Type | PCB Mount Receptacle |
| Connector System | Board-to-Board |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|------------------------------|----------|
| Stackable | Yes |
| PCB Mount Orientation | Vertical |
| Number of Positions | 220 |
| Board-to-Board Configuration | Parallel |

Electrical Characteristics

| | |
|---------------------------------------|---------|
| Dielectric Withstanding Voltage (Max) | 200 VAC |
| Insulation Resistance | 2 MΩ |
| Operating Voltage | 50 VAC |

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

| | |
|---------------------------------------------------------|-----------------|
| Contact Mating Area Length | 1 mm, 1.3 mm |
| PCB Contact Termination Area Plating Material Thickness | 1 μm[39.37 μin] |



| | |
|-----------------------------------------------|------------------|
| Contact Layout | Inline |
| Mating Tab Width | .33 mm[.013 in] |
| Mating Tab Thickness | .15 mm[.006 in] |
| PCB Contact Termination Area Plating Material | Tin |
| Contact Base Material | Copper Alloy |
| Contact Mating Area Plating Material | Gold |
| | 29.9212 μ in |
| Contact Type | Socket |
| Contact Current Rating (Max) | .5 A |

Termination Features

| | |
|-----------------------------------------------|-----------------|
| Rectangular Termination Post & Tail Thickness | .15 mm[.006 in] |
| Rectangular Termination Post & Tail Width | .9 mm[.035 in] |
| Termination Method to Printed Circuit Board | Surface Mount |

Mechanical Attachment

| | |
|--------------------------|----------------|
| PCB Mount Alignment Type | Locating Posts |
| PCB Mount Retention Type | Solder Peg |
| Mating Alignment | With |
| Mating Alignment Type | Polarized |
| PCB Mount Retention | With |
| PCB Mount Alignment | With |

Housing Features

| | |
|--------------------|--------------------------------|
| Centerline (Pitch) | .5 mm[.02 in] |
| Housing Material | High Temperature Thermoplastic |

Dimensions

| | |
|------------------|---------------------------|
| Connector Height | 3.25 mm[.128 in] |
| Stack Height | 4 mm, 5 mm, 8 mm[.315 in] |

Usage Conditions

| | |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F] |
|-----------------------------|---------------------------|

Operation/Application

| | |
|--------------------------|--------|
| Assembly Process Feature | None |
| Circuit Application | Signal |

Industry Standards



| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 30 |
| Packaging Type | Tray |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Reflow solder capable to 245°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 3-1827253-6 .5FHP05H,220,S,GIG,08/Sn,HT,NSYes</p> |  <p>TE Part # 8-6318491-6 .5FHP08H,220,S,GIG,08/Sn,HT,SEYes</p> |  <p>TE Part # 3-6318491-6 .5FHP08H,220,S,GIG,08/Sn,HT,NSYes</p> |  <p>TE Part # 3-1939756-6 .5FHP08H,220,S,GIG,30/Sn,HT,NS</p> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|




TE Part # 9-6318491-6
.5FHP08H,220,S,GIG,08/Sn,HT,NSYes,W/C



TE Part # 3-2040713-6
.5FHP08H,220,S,GIG,30/Sn,TR,NS



TE Part # 9-1939756-6
.5FHP08H,220,S,GIG,30/Sn,HT,NS,WC



TE Part # 4-1827253-6
.5FHP05H,220,S,GIG,08/Sn,TR,NSYes



TE Part # 9-1827253-6
.5FHP05H,220,S,GIG,30/Sn,HT,NSYes

Also in the Series | Free Height



PCB Headers & Receptacles(759)

Customers Also Bought



TE Part #5499922-9
A/L UNIV HDR 40P VERT LG LAT



TE Part #4525DO-TP3AJ030APF
PRESS XDCR,DIGITAL,PSI RANGE



TE Part #5767005-8
MICT,495PLUG,038,ASSY,.025,REC



TE Part #34856
TERMINAL,PG R 12-10 5/16



TE Part #5747877-3
FEMALE SCREWLOCK ZINC CLEAR




TE Part #1676203-2
RN 0805 16K2 0.1% 10PPM 1KRL



TE Part #1-2176244-3
CRGS0805 5% 10R



TE Part #5070022021
RNF-100-1/16-X-STK



TE Part #5677562009
RNF-3000-3/1-0-STK

Documents

Product Drawings

[.5FHR04H,220,S,GIG,30/Sn,HT,NS](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1939755-6_A_c-3-1939755-6-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1939755-6_A_c-3-1939755-6-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1939755-6_A_c-3-1939755-6-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[COM Connectors Brochure \(English\)](#)

English

Product Specifications

[Product Specification](#)

English

[0.5mm Pitch Board to Board Connector, Free Height Type](#)

English