


◆FEATURES

1. Temperature range : -55 to +150°C
2. Temperature characteristic : X8L
3. Small in size and wide capacitance range.
Max. 15 μ F is available.
4. Epoxy resin(UL94 V-0)used for coating.
5. Automotive grade(AEC-Q200)

◆APPLICATIONS

1. Noise filter for automotive equipment(ECU etc.)
2. Equipment used in a high temperature environment

◆CONSTRUCTION



◆RATINGS

1. Category Temperature Range	-55~+150°C
2. Rated Voltage Range	25, 50, 100 Vdc
3. Rated Capacitance Range	0.1~15 μ F
4. Rated Capacitance Tolerance	M(\pm 20%), K(\pm 10%)
5. Temperature Characteristics	X8L
6. Rated Ripple Current	See No.5 on the following table

◆SPECIFICATIONS

No.	Items		Specification	Test Condition		
1	Withstand Voltage	Between Terminals	No abnormality.	250% of rated voltage shall be applied for 5 seconds. (Only 250Vdc products : 475V)		
		Terminals to Coating Resin				
2	Insulation Resistance		100/C _R (M Ω) or 4000(M Ω) whichever is less.	Rated voltage shall be applied for 60 \pm 5 seconds at temperature 25 \pm 2°C.		
3	Rated Capacitance		Within specified tolerance.		C _R \leq 10 μ F	C _R >10 μ F
				Temperature	25 \pm 2°C	
4	Dissipation Factor		5.0% maximum.	Frequency	1 \pm 0.1kHz	120 \pm 12Hz
				Voltage	1 \pm 0.2Vrms	0.5 \pm 0.2Vrms

As customer requirement, Chemi-Con has submits the test results according to AEC-Q200 for Multilayer ceramic capacitors. Please contact us for more information.



DIPPED RADIAL LEAD MULTILAYER CERAMIC CAPACITORS

KVD Series

◆ SPECIFICATIONS

No.	Items	Specification	Test Condition															
5	Rated Ripple Current	<table border="1"> <tr> <td>Size code</td> <td>32</td> <td>43</td> <td>55</td> </tr> <tr> <td>Arms</td> <td>0.3</td> <td>0.8</td> <td>1.0</td> </tr> </table>	Size code	32	43	55	Arms	0.3	0.8	1.0	10kHz to 1MHz (sine curve) Ripple voltage V_p shall be less than the rated voltage. The surface temperature of MLCC must not exceed the maximum category temperature when the ripple current is applied.							
Size code	32	43	55															
Arms	0.3	0.8	1.0															
6	High Temperature Exposure(Storage)	Appearance : No structural damage such as cracks $\Delta C/C : \pm 20\%$ D.F. : 10% maximum I.R. : $50/C_R(M\Omega)$ or $1000(M\Omega)$ whichever is less.	Temperature : Max. category temperature $\pm 3^\circ C$ Time : 1000 ± 48 hours															
7	Temperature Cycle	Appearance : No visible damage. $\Delta C/C : \pm 15\%$ D.F. : To meet the initial specification. I.R. : To meet the initial specification.	<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature($^\circ C$)</th> <th>(min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Min Category temperature ± 3</td> <td>30 ± 3</td> </tr> <tr> <td>2</td> <td>Room temperature</td> <td>3 max.</td> </tr> <tr> <td>3</td> <td>Max. Category temperature ± 3</td> <td>30 ± 3</td> </tr> <tr> <td>4</td> <td>Room temperature</td> <td>3 max.</td> </tr> </tbody> </table> For 1000 cycles	Step	Temperature($^\circ C$)	(min)	1	Min Category temperature ± 3	30 ± 3	2	Room temperature	3 max.	3	Max. Category temperature ± 3	30 ± 3	4	Room temperature	3 max.
Step	Temperature($^\circ C$)	(min)																
1	Min Category temperature ± 3	30 ± 3																
2	Room temperature	3 max.																
3	Max. Category temperature ± 3	30 ± 3																
4	Room temperature	3 max.																
8	Biased Humidity	Appearance : No abnormality. $\Delta C/C : \pm 20\%$ D.F. : 10% maximum I.R. : $25/C_R(M\Omega)$ or $1000(M\Omega)$ whichever is less.	Temperature : $85^\circ C \pm 3^\circ C$ Humidity : $80 \sim 85\%RH$ Voltage : Rated voltage Time : 1000 ± 48 hours															
9	Operational Life	Appearance : No structural damage such as cracks $\Delta C/C : \pm 20\%$ D.F. : 10% maximum I.R. : $50/C_R(M\Omega)$ or $1000(M\Omega)$ whichever is less.	Temperature : Max. category temperature $\pm 3^\circ C$ Voltage : Rated voltage Time : 1000 ± 48 hours															
10	Terminal Strength (Leaded)	<table border="1"> <tr> <td>Tension</td> <td rowspan="2">No visible damage.</td> </tr> <tr> <td>Bending</td> </tr> </table>	Tension	No visible damage.	Bending	The force applied shall be : <table border="1"> <tr> <td>Lead ϕ (mm)</td> <td>Tensile(N)</td> <td>(sec.)</td> </tr> <tr> <td>0.5 max.</td> <td>5</td> <td>10 ± 1</td> </tr> </table> <table border="1"> <tr> <td>Lead ϕ (mm)</td> <td>Bending(N)</td> <td>(kg)</td> </tr> <tr> <td>0.5 max.</td> <td>2.5</td> <td>0.25</td> </tr> </table> Time : 2times.	Lead ϕ (mm)	Tensile(N)	(sec.)	0.5 max.	5	10 ± 1	Lead ϕ (mm)	Bending(N)	(kg)	0.5 max.	2.5	0.25
Tension	No visible damage.																	
Bending																		
Lead ϕ (mm)	Tensile(N)	(sec.)																
0.5 max.	5	10 ± 1																
Lead ϕ (mm)	Bending(N)	(kg)																
0.5 max.	2.5	0.25																
11	Mechanical Shock	Appearance : No abnormality. $\Delta C/C : \pm 20\%$ D.F. : To meet the initial specification.	MIL-STD-202 Method 213 Condition C Peak value : 100G Normal duration : 6 ms Velocity change : 12.3 ft/sec(3.8m/s) Direction and time : 3 times each in X,Y, Z axis. Total 18 times															
12	Vibration	Appearance : No abnormality. $\Delta C/C : \pm 20\%$ D.F. : To meet the initial specification.	MIL-STD-202 Method 204 Test condition : 5G peak Amplitude : 1.5mm max. Frequency : 10-2000-10Hz(20 minute) Direction and time : 12 times each in X,Y, Z axis. Total 36 times															
13	Resistance to Soldering Heat	Appearance : No visible damage. $\Delta C/C : \pm 15\%$ D.F. : To meet the initial specification. I.R. : To meet the initial specification.	Solder temp. : $260 \pm 5^\circ C$ Dipping Time : $10 \pm 1s$ Depth : 1.5 to 2mm															
14	ESD	Appearance : No abnormality. $\Delta C/C : \pm 20\%$ D.F. : To meet the initial specification. I.R. : To meet the initial specification.	AEC-Q200-002 Connection : Between terminals Direct Contact : 8kV(150pF 2000 Ω) Times : ± 1 time															
15	Solderability	Min. 75% of surface of the termination shall be covered with new solder.	<table border="1"> <tr> <td>Solder</td> <td>Pb Free</td> </tr> <tr> <td>Solder Temperature</td> <td>$245 \pm 5^\circ C$</td> </tr> <tr> <td>Dipping Time</td> <td>$2 \pm 0.5s$</td> </tr> </table>	Solder	Pb Free	Solder Temperature	$245 \pm 5^\circ C$	Dipping Time	$2 \pm 0.5s$									
Solder	Pb Free																	
Solder Temperature	$245 \pm 5^\circ C$																	
Dipping Time	$2 \pm 0.5s$																	


*CR : Rated Capacitance(μF)

◆ STANDARD RATINGS


Rated voltage (Vdc)	Rated Capacitance (μF)	Electrostatic Capacitance Temperature Characteristics	Dimensions(mm)					Maximum ripple current (Arms)	Part Number	Taping Quantity per reel (pcs. / reel)
			L max.	W max.	T max.	F±0.8	φd±0.05			
25	1.0	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD250L105□32A0T00	2,000
	1.5	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD250L155□32A0T00	2,000
	2.2	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD250L225□32A0T00	2,000
	3.3	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD250L335□32A0T00	2,000
	4.7	X8L	6.5	6.5	4.0	5.0	0.5	0.8	KVD250L475□43A0T00	2,000
	6.8	X8L	6.5	6.5	4.0	5.0	0.5	0.8	KVD250L685□43A0T00	2,000
	10	X8L	7.5	9.0	4.5	5.0	0.5	1.0	KVD250L106□55A0T00	2,000
50	0.33	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD500L334□32A0T00	2,000
	0.47	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD500L474□32A0T00	2,000
	0.68	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD500L684□32A0T00	2,000
	1.0	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD500L105□32A0T00	2,000
	1.5	X8L	6.5	6.5	4.0	5.0	0.5	0.8	KVD500L155□43A0T00	2,000
	2.2	X8L	6.5	6.5	4.0	5.0	0.5	0.8	KVD500L225□43A0T00	2,000
	3.3	X8L	7.5	9.0	4.5	5.0	0.5	1.0	KVD500L335□55A0T00	2,000
	4.7	X8L	7.5	9.0	4.5	5.0	0.5	1.0	KVD500L475□55A0T00	2,000
100	0.10	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD101L104□32A0T00	2,000
	0.15	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD101L154□32A0T00	2,000
	0.22	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD101L224□32A0T00	2,000
	0.33	X8L	5.0	6.0	3.5	5.0	0.5	0.3	KVD101L334□32A0T00	2,000
	0.47	X8L	6.5	6.5	4.0	5.0	0.5	0.8	KVD101L474□43A0T00	2,000
	0.68	X8L	6.5	6.5	4.0	5.0	0.5	0.8	KVD101L684□43A0T00	2,000
	1.0	X8L	7.5	9.0	4.5	5.0	0.5	1.0	KVD101L105□55A0T00	2,000
	1.5	X8L	7.5	9.0	4.5	5.0	0.5	1.0	KVD101L155□55A0T00	2,000

※ The square (□) in part numbers is replaced by a capacitance tolerance code: 'K' when ±10%, or 'M' when ±20%
 ※ Please consult with us when you consider the rating other than a standard table.

◆ PART NUMBERING SYSTEM



◆ DIMENSIONS



Please refer to "Part Numbering System" of the beginning of a catalog for the details.



- Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.
- Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.
- The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.
- The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.
- We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.
- We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products
- We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

[Precautions and Guidelines](#) · [Recommended Soldering Conditions](#)

[Part Numbering System](#)

[List of Standardization and Obsolete Products](#)

[TAPING SPECIFICATION](#)

[Characteristics Data](#)

[Minimum Packaging Quantity](#)