ONLY FOR REFERENCE

Standard Spec Sheet

Mitsumi Model Name	STI-055A12AX
Mitsumi Model No.	R 66 8005
Operating Force	1.2N
Pcs/Reel	25,000

This specification is only for reference. If you have any questions for the details, please contact SW engineering division.

Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.

For your adopting the products, the formal supply specification will be provided.


MITSUMI ELECTRIC CO.,LTD.

2-11-2, Tsurumaki, Tama-shi. Tokyo 206-8657 Japan.

SWITCH ENGINEERING SECTION 1049, Tateiwa, Iizuka-shi. Fukuoka 820-8533 Japan.


					(1/ 1 /
	Product specification Tactile	ın	Approved	Checked	Drawn
	Tactile	switches	Mar-23-18		
.on 9Ji4	STI-05	5A12AX		SW Eng. Kawaguchi	
1, _	3 1 1 0 3	<i>51112111</i>	Ogui a	Iva w a yuciii	IIIOUE
Customer's name	Customer's parts no.	General specification	Issued		
_	_	S66-1826	١	1ar-23-18	3

- 1) The items specified in this Product specification are prior to General specification.
- 2) For the items not specified in this Product specification. General specification is applied.



Reference solder stencil dimension

0



. (0)


0

(*1)The switch height shall be measured with applying 5 gf load.

Operating force	1.2+/-0.5 [N]
Return force	0.1 [N] min.
Click ratio	40 [%] min.
Travel	0.11+/-0.05 [mm]
Contact resistance	1 [ohm] max.
Max. rating	20 [mA] 15 [V] DC (Resistive Load)
Operating life	500,000 cycles

Thickness of solder stencil: 100 µm

Reference land dimension



No pattern Circuit diagram No silk (A)RoHS compliant

Environmental classification	G
Parameter sheet result	N
Development class	2

											_
						Third	Scale	Tole	rance	Ass'y dwg.	. по.
Rev						angle projection	10:1	+/-	0.15	66-K292	2 V
						hi.o ler i ioii		·			
	јА рг flow	ocess chart	Product inspection standard	Model	code	Code I	ndent.	ПО.	File	ПО.	
	Q66-		166-8600	150	6 3	R	66		(8005	00

(2011/65/EU)

1826

General specification
Tactile switches

STI series

Approved Checked

Mar-26-18
SW Eng.
Ogura Kawaguchi

Drawn Mar-26-18 SW Eng. Inoue

Released Mar-26-18

1. General

1.1. Application

This specification is applied to Tactile switches named STI series.

1.2. Operating temperature range: -10 to +60 deg-C

1.3. Storage temperature range: -25 to +85 deg-C (Product level)

-20 to +50 deg-C (Taped condition)

ISSUED

03. Apr. '2018

SWITCH ENG
DEPT

1.4. Test conditions

Normal temperature; 5 to 35 deg-C, normal humidity; 45 to 85% RH. If any doubt arises from judgement, tests and measurements shall be conducted under the following conditions.

Temperature 20+/- 2deg-C, humidity 65+/-5% RH, and air pressure 86 to 106 kPa.

2. Appearance and Construction

2.1. Dimensions: Specified on Product specifications.

2.2. Materials: Refer to Table-1.

2.3. Appearance: There shall be no defects that affect the performance of

the products such as crack, scratch, dirt, discoloration, air bubble of

ACTUATOR, and contamination.

2.4. Cross section view:




Fig. 1. Cross section of product

Table-1

Components	Material	Note
(1) ACTUATOR	9T Nylon	
(2) COVER FILM	9T Nylon	
(3) CLICK SPRING	Stainless steel	Ag plated
(4) BASE	9T Nylon	
(5) TERMINAL	Phosphor bronze	Ag plated

3. Rating

Specified on Product specification.

			Code	Division	File No.
ision					
l >			C	66	1826
Re			3	OO	1020

MITSUMI ELECTRIC. CO., LTD.

Item	Test conditions	Criteria
4.1. Contact resistance	Measurements shall be made under the conditions shown in Fig. 3. 1) Load: 2 times of the specified standard operating force.	Specified on Product specifications.
	Measurement conditions: Contact resistance meter at 20 mV Max. and 10uA to 10mA.	
	2.5 mm dia. Push direction 0.5 mm Max. Tilt angle 90+/-2 deg Ro.1 Perimeter (Material: Stainless steel) Fig. 2: Push rod Fig. 3: Measurement conditions	ISSUED 03. Apr. '2018 SWITCH ENG DEPT
4.2. Insulation resistance	Measurements shall be made under the following conditions. 1) Applied voltage: 100 V, DC 2) Duration: 1 min. 3) Applied position: Between terminals.	50 M-ohm Min.
4.3. Withstanding voltage	Measurements shall be made under the following conditions. 1) Applied voltage: 100 V, AC (50/60 Hz) 2) Duration: 1 min. 3) Leak current: 2 mA 4) Applied position: Between terminals.	There shall be no damage and breakdown.
4.4. Bounce	Measurements shall be made under the conditions shown in Fig. 3. Bounce time at "ON" and "OFF" shall be measured under the following conditions. 1) Circuit: Refer to Fig. 4. 2) Load: 1.5 times of the specified standard operating force. 3) Frequency of operation: 3 to 4 times/sec. DC5 V	ON bounce: 10 ms Max. OFF bounce: 10 ms Max.

File number 1826

5. Mechanica	al Characteristics	
Item	Test conditions	Criteria
5.1. Operating force 5.2. Return force	Measurements shall be made under the conditions shown in Fig. 3 just after striking 10 times lightly. 1) Measurement speed: 0.5 mm/sec. 2) Limit load to apply: 1.5 to 2 times of the specified standard operating force. Force (N)	Specified on Product specifications.
	Operating force Return force Stroke (mm) Fig. 6: Force-Stroke curve	ISSUED 03. Apr. '2018 SWITCH ENG DEPT
5.3. Click ratio	Refer to 5.1 and 5.2 for the measurement conditions. Click ratio = (a - b) / a x 100%	Specified on Product
5.4. Travel	Force (N) a b Travel Fig. 7 Force-Stroke curve	specifications.
5.5. Stopper strength	Measurements shall be made under the conditions shown in Fig. 3 and at returned condition. Load: 30 N Duration: 15 sec.	There shall be no electrical and mechanical abnormality.
5.6. Impact resistance	Measurements shall be made after testing under the following conditions. 1) Acieration: 735 m/s2 2) Duration: 6 msec 3) Test direction: 6 directions 4) Number of test: 3 times per direction (18 times in total)	There shall be no electrical and mechanical abnormality.

File number

5. Mechanical Characteristics

Item	Test conditions	Criteria
5.7.	Measurements shall be made after testing under the	There shall be
Vibration	following conditions.	no electrical
resistance		and mechanical
resistance	1) Vibration frequency range: 10 to 55 Hz	
	2) Amplitude: 1.5 mm (peak-to-peak)	abnormality.
	3) Sweep ratio: 10-55-10 Hz in approx. 1 min.	ISSUED
	4) Frequency sweep mode: Logarithmic or Liner sweep	
	5) Direction of vibration: 3 orthogonal directions including	03. Apr. '2018
	the direction of operation.	SWITCH ENG
	6) Duration: 2 hr each (6 hr in total)	DEPT
5.8.	Measurements shall be made under the following conditions.	More than 75%
Solderability	1) Solder temperature: 230 +/- 5 dig-C	of dipped part
	2) Dipping time: 3 +/- 0.5 sec.	shall be covered
	3) Composition of solder: Sn-3.0Ag-0.5Cu	with solder.
	4) Soldering flux: Rosin 25%, Alcohol 75%	
5.9.	Measurements shall be made after reflow soldering under	There shall be
Soldering	the following conditions.	no abnormality
heat	Heating method: Far-infrared radiation heating	such as marked
resistance	Temperature profile: As shown in below.	looseness,
	Allowable soldering process: 2 times Max.	drop-off,
		and assured
	Temp.	4. Electrical
	(deg-C) [↑]	Characteristics.
	5 sec max.	Operating force:
Ī	1 300 max.	
	260 †	Item 5.1.
	260 230 40+/-10 sec	
	260 230 180 150	
	260 230 40+/-10 sec	
	260 230 180 150 90+/-30 sec	
	260 230 180 150 90+/-30 sec	

5.10. Precautions for soldering

- 1) This product is designed for reflow soldering. Please do not solder manually.
- 2) Do not wash the product with solvent or the like.
- 3) The soldering conditions will be different depending on reflow soldering machines. Conditions of soldering shall be confirmed under actual production conditions.
- 4) Reflow soldering shall be performed in shorter time and at lower temperature. Otherwise click ratio may be decreased.
- 5) Please set the proper volume of solder in order to prevent soldering flux ingress and float of the products.
- 6) Please do not apply soldering flux to the terminals and mounting surface of PWB/FPC.
- 7) Note that if the load is applied to the terminals during soldering it might cause deformation and defects in electrical performance.

File number

1826

6. Durability

6. Durability			
Item	Test conditions	Crite	eria
6.1.	Measurements shall be made after testing under the	Contact	Insulation
Operating life	following conditions.	resistance:	resistance:
	 Electrical load: Rated load or no load. Rate of operation: 2 cycles/sec. 	20 ohm Max.	10 M-ohm Min
	 Depression: The maximum value of specified operating force. 	Bounce (ON/OFF):	Withstanding voltage:
	Cycles of operation: Specified on the product specification.	20 msec Max.	Item 4.3.
		Operating force: Within +/-30% of specified initial value.	Travel: Item 5.4.
		03. A	SSUED Apr.'2018 TCH ENG DEPT

7. Environmental

Item	Test conditions	Criteria
7.1.	Following the test set forth below the sample shall be left in	Contact
Humidity	normal temperature and humidity conditions for 1 hr before	resistance:
resistance	measurements are made.	1 ohm Max.
	Water drops shall be removed.	
	1) Temperature: 60+/-2 deg-C, Humidity: 90 to 96% RH	Insulation
	2) Duration: 96+/-5 hr	resistance:
		10 M-ohm Min.
7.2.	Following the test set forth below the sample shall be left in	
Heat	normal temperature and humidity conditions for 1 hr before	Withstanding
resistance	measurements are made.	voltage:
	1) Temperature: 85+/-2 deg-C	Item 4.3.
	2) Duration: 96+/-5 hr	
		Bounce
7.3.	Following the test set forth below the sample shall be left in	(ON/OFF):
Cold resistance	normal temperature and humidity conditions for 1 hr before measurements are made.	20 msec Max.
10010141100	Water drops shall be removed.	Operating force:
	1) Temperature: -40+/-3 deg-C	Within +/-30%
	2) Duration: 96+/-5 hr	of specified
	2) Baladon. 66-7-6111	initial value.
		Travel:
		Item 5.4.

File number

1826

CTRIC. CO., LTD. S-0115

7. Environmental

Item	Test conditions	Criteria			
7.4.	Following continuous 5 cycles of the temperature cycling test	Contact			
Temperature	set forth below, the sample shall be left in normal	resistance: 1 ohm Max.			
cycling					
	-40+/-3 deg- 120 min 10 to 15 min 1 cycle	Insulation resistance: 10 M-ohm Min. Withstanding voltage: Item 4.3. Bounce (ON/OFF): 20 msec Max.			
	Fig. 9: Temperature cycling test conditions	Operating force: Within +/-30% of specified initial value.			
		Travel: Item 5.4.			
7.5. Water resistance IPX7 equivalent	Ingress shall be confirmed after the test under the following conditions based on IPX7. 1) Depth of immersion: 1 m 2) Duration of immersion: 30 min.	There shall be no ingress water inside of the product.			
7.6. Dust protection IP6X equivalent	st protection conditions based on IP6X.				

8. Use Condition

8.1. Operating temperature range: Refer to the item 1.2. (Temperature range which the product is ON and OFF electrically.) There shall be no freezing and condensation.

8.2. Using environment

- 1) Do not expose the products to corrosive gas such as sulfur gas and salty wind.
- 2) Visible dust must be cleared.
- 3) Please do not apply excessive load to the products to avoid deformation and deterioration.

9. Storage Condition

- 9.1. Storage temperature range: Refer to the item 1.3. There shall be no freezing and condensation.
- 9.2. Environment
 - 1) Do not expose the products to corrosive gas such as sulfur gas, and salty wind.
 - 2) Visible dust must be cleared.
 - 3) Please do not apply excessive load to the products to avoid deformation and deterioration.
- 9.3. Storage method
 - 1) Products shall be packed in an airtight plastic bag and stored in cool place avoiding direct sunshine.
 - 2) Do not stack too many switches for strafe. Shall be free from high temperature and high humidity.
 - 3) Do not store the products in the state of applying load on it's operation area.
 - 4) Products should be used within six months after the date of delivery.

File number

ISSUED 03. Apr. '2018 SWITCH ENG

- 10. Precautions in Use
- 10.1. Do not clean the products with a solvent or the like.
- 10.2. Do not use the products with beyond the rated current and voltage.
- 10.3. Do not apply excessive load to the terminals and the operating part.
- 10.4. Larger static load than specified and/or shock shall not be applied to the operating part.
- 10.5. After mounting the products on PWB/FPC, please do not stack too many PWB/FPC in order to avoid excessive load to the switch mounted area.
- 10.6. The dimensions of a pattern on PWB/FPC shall refer to the recommended dimensions in Product specifications.
- 10.7. If you use this product in one of the following environmental conditions, progress of sulfaration and oxidization on the contact part (silver) will be accelerated, which may cause contact failure.

Therefore, be careful about the operation environment.

- 1) Around a sulfarate hot spring where sulfide gas is generated.
- 2) In case this product is always used in a place where exhaust gas from automobiles exist.
- 10.8. Do not push the cover film of products with something sharp.
- 10.9. Please design and assemble your unit not to apply over load to the switch.
- 10.10. Please let us know beforehand if you use other shape of pushing rod than the shape described in Fig. 2.
- 10.11. Please be careful on designing and handling especially when the switch is being built into the unit, not to add side force (static or impact) to the ACTUATOR as shown below (Fig. 10), because the ACTUATOR might deform or come off.




Fig. 10 Load and impact from side direction

- 10.12. Unless provided for otherwise, the products have been designed and manufactured for application in equipment and devices which are sold to end users in the market, including audio-visual equipment, electrical home appliances, office machines, information and communication equipment, and amusement equipment.
 The products are not intended for use in, and must not be used for, any application for nuclear equipment, driving equipment for aerospace or any other unauthorized use. With the exception of the abovementioned prohibited applications, please contact us (MITSUMI) and/or evaluate the total system regarding applicability for applications involving high levels of safety and liability such as medical equipment, burglar alarm equipment, disaster prevention equipment and undersea equipment. Please also incorporate fail-safe design, protection and redundant circuitry, malfunction protection, and/or fire protection into the complete system to ensure safety and reliability of the total system.
- 10.13. If you intend to use the products for automotive, please let us know beforehand.

File number

SSUED


03. Apr. '2018

1826

11. Packing Specification

- 11.1. Dimensions of carrier tape are as shown below.
- 11.2. Taping rule
 - Tape winding direction is in clockwise.
 (When pulling the tape toward, feeding holes should be located on the right side.)
 - 2) Feeding holes shall not be covered with the cover tape.
 - The cover tape shall not be run off the edge of the carrier tape.
 - 3) 160 mm or more from the end of trailer tape part shall be empty.
 - 4) The leader part shall be 400 mm or more and it should include 100 mm of empty part. The leader part shall have 20 to 30 mm of un-sealed cover tape.
 - 5) The top tape of the leader part shall be stuck on the side of the reel by 30 to 50 mm using adhesive tape.
 - 6) Peeling strength of cover tape from carrier tape is 0.1 to 1.3 N at 165 to 180 deg.
 - 7) QR code label and Mitsumi label shall be stuck on the side of the reel.
 - 8) The products shall free drop from the reversed carrier tape without cover tape after pressing at 0.1 to 0.2 N force.
 - 9) Continuous two missing switches shall not be allowed.

 Total number of missing switches shall be 0.1% or less of the packed quantity per reel.
 - 10) The direction of products in the pockets is not specified.
 - 11) 25,000 switches shall be packed in a reel.





Α	В	С	D	Е	F	G
12	1.75	5.5	4+/-0.05	4+/-0.05	2	1.5 dia +0.1/-0

Fig. 11 Carrier tape dimensions





Fig. 12 Taping specification

File number


1826

12. Packing Specification



3) MITSUMI label specification

400



400

File number

1826

PE bag

5 reels max. shall be packed in an inner bag.