

**D64DS5,6,7**  
**D64ES5,6,7**

File Number **15.34**

HARRIS SEMICOND SECTOR

27E D ■ 4302271 0020361 5 ■ HAS

T-33-29


## 20-Ampere N-P-N Darlington Power Transistors

### Features:

- High speed  $t_s < 3.0 \mu\text{sec.}$ ,  $t_r < 1.0 \mu\text{sec.}$
- High voltage: 400-500  $V_{CEO(SUS)}$
- High gain:  $h_{FE}$  40 minimum @  $I_C = 20A$
- High current: 30 amperes,  $I_C$  (Peak)


The D64DS and D64ES series of silicon n-p-n power Darlington transistors are designed for use in high-speed switching applications. These applications include off-line switching power supplies, PWM ac and dc motor controls, UPS systems, ultrasonic equipment, and other high-frequency power conversion equipment.

### TERMINAL DESIGNATIONS



92CS-27516

JEDEC TO-204AA



D64DS

D64ES

### DEVICE CIRCUIT

### MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ ) (unless otherwise specified)

RATING	SYMBOL	D64DS5/ES5	D64DS6/ES6	D64DS7/ES7	UNITS
Collector-Emitter Voltage	$V_{CEV}$	500	600	700	Volts
Collector-Emitter Voltage	$V_{CEO}$	400	450	500	Volts
Emitter Base Voltage	$V_{EBO}$	8 5	8 5	8 5	Volts
Collector Current — Continuous	$I_C$	20	20	20	A
Peak (Repetitive)	$I_{CM}$	30	30	30	
Peak (Non-Repetitive)	$I_{CSM}$	50	50	50	
Base Current — Continuous	$I_B$	5	5	5	A
Peak (Non-Repetitive)	$I_{BM}$	10	10	10	
Total Power Dissipation @ $T_C = 25^\circ\text{C}$	$P_D$	125	125	125	Watts
Operating and Storage Junction Temperature Range	$T_J, T_{STG}$	-65 to +150	-65 to +150	-65 to +150	$^\circ\text{C}$

### THERMAL CHARACTERISTICS

Thermal Resistance, Junction to Case	$R_{\theta JC}$	1	1	1	$^\circ\text{C/W}$
Maximum Lead Temperature for Soldering Purposes: $\frac{1}{16}$ " from Case for 5 Seconds	$T_L$	300	300	300	$^\circ\text{C}$

**D64DS5,6,7**  
**D64ES5,6,7**

T-33-29

ELECTRICAL CHARACTERISTICS ( $T_C = 25^\circ\text{C}$ ) (unless otherwise specified)

CHARACTERISTIC	SYMBOL	MIN	TYP	MAX	UNIT
----------------	--------	-----	-----	-----	------

## OFF CHARACTERISTICS

Collector-Emitter Sustaining Voltage ( $I_C = 0.5\text{A}$ ) ( $V_{\text{clamp}} = V_{\text{CEO Rated}}$ )	D64DS5/ES5 D64DS6/ES6 D64DS7/ES7	$V_{\text{CEO(sus)}}$	400 450 500	— — —	— — —	Volts
Collector Cutoff Current ( $V_{\text{CE}} = \text{Rated Value}$ , $V_{\text{BE}} = -1.5\text{V}$ )	$T_J = 25^\circ\text{C}$ $T_J = 150^\circ\text{C}$	$I_{\text{CEV}}$	— —	— —	1.0 2.5	mA
Emitter Cutoff Current ( $V_{\text{EB}} = 4.5\text{V}$ , $I_C = 0$ ) ( $V_{\text{EB}} = 1.5\text{V}$ , $I_C = 0$ )	D64DS D64ES	$I_{\text{EBO}}$	— —	— —	200 200	mA

## SECOND BREAKDOWN

Second Breakdown with Base Forward Biased	FBSOA	SEE FIGURE 26
---	-------	---------------

## ON CHARACTERISTICS

DC Current Gain ( $I_C = 30\text{A}$ , $V_{\text{CE}} = 5\text{V}$ ) ( $I_C = 20\text{A}$ , $V_{\text{CE}} = 5\text{V}$ ) ( $I_C = 10\text{A}$ , $V_{\text{CE}} = 5\text{V}$ )	$h_{\text{FE}}$	20 40 100	35 85 160	— — —	— — —
Collector-Emitter Saturation Voltage ( $I_C = 30\text{A}$ , $I_B = 3\text{A}$ ) ( $I_C = 20\text{A}$ , $I_B = 2\text{A}$ ) ( $I_C = 10\text{A}$ , $I_B = 1\text{A}$ )	$V_{\text{CE(sat)}}$	— — —	2.1 1.6 1.2	3.5 2.5 1.5	V
Base-Emitter Saturation Voltage ( $I_C = 30\text{A}$ , $I_B = 3\text{A}$ ) ( $I_C = 20\text{A}$ , $I_B = 2\text{A}$ ) ( $I_C = 10\text{A}$ , $I_B = 1\text{A}$ )	$V_{\text{BE(sat)}}$	— — —	2.65 2.3 1.8	4 3 2.5	V

## SWITCHING CHARACTERISTICS

		TYP.		MAX.			
Resistive Load		DS	ES	DS	ES		
Delay Time	$V_{\text{CC}} = 250\text{V}$	$t_d$	—	0.05	0.05	0.5	$\mu\text{sec}$
Rise Time	$I_C = 20\text{A}$	$t_r$	—	0.4	0.4	1	
Storage Time	$I_{B1} = 1\text{A}$ , $I_{B2} = -2\text{A}$	$t_s$	—	2.2	1.8	5	
Fall Time	$t_p = 50 \mu\text{sec}$	$t_f$	—	1.6	.45	3	

## EMITTER-COLLECTOR DIODE CHARACTERISTICS

Power Dissipation	$P_D$	—	—	125	Watts
Forward Voltage ( $I_F = 10\text{A}$ ) ( $I_F = 25\text{A}$ ) ( $I_F = 25\text{A}$ , $T_J = 150^\circ\text{C}$ )	$V_F$ $V_F$ $V_F$	— — —	1.95 2.80 2.75	3.20 4.00 4.00	Volts Volts Volts
Reverse Recovery Time ( $I_F = 25\text{A}$ , $di/dt = 15\text{A}/\mu\text{sec}$ , $R_{B1E} = .25\Omega$ )	$T_{rr}$	—	3.85	10	$\mu\text{sec}$
Forward Turn-On Time ( $I_F = 25\text{A}$ , $di/dt = 50\text{A}/\mu\text{sec}$ )	$T_{\text{ON}}$	—	0.42	1.0	$\mu\text{sec}$
Single Cycle Surge Current (60Hz)	$I_{\text{FSM}}$	—	—	50	Amps
Thermal Resistance	$R_{\theta\text{JC}}$	—	—	1.0	$^\circ\text{C}/\text{Watt}$

D64DS5,6,7  
D64ES5,6,7

T-33-29

TYPICAL CHARACTERISTICS




FIGURE 1. DC CURRENT GAIN ( $V_{CE} = 2V$ )




FIGURE 2. DC CURRENT GAIN ( $V_{CE} = 5V$ )




FIGURE 3. DC CURRENT GAIN ( $V_{CE} = 10V$ )




FIGURE 4. COLLECTOR SATURATION REGION




FIGURE 5.  $V_{CE(SAT)}$  VS.  $I_C$ ,  $T_J = 25^\circ C$




FIGURE 6.  $V_{CE(SAT)}$  VS.  $I_C$ ,  $T_J = 100^\circ C$

D64DS5,6,7  
D64ES5,6,7

TYPICAL CHARACTERISTICS

T-33-29




FIGURE 7.  $V_{CE(SAT)}$  VS.  $I_C$ ,  $T_J = 150^\circ\text{C}$




FIGURE 8.  $V_{BE(SAT)}$  VS.  $I_C$ ,  $T_J = 25^\circ\text{C}$




FIGURE 9.  $V_{BE(SAT)}$  VS.  $I_C$ ,  $T_J = 100^\circ\text{C}$




FIGURE 10.  $V_{BE(SAT)}$  VS.  $I_C$ ,  $T_J = 150^\circ\text{C}$




FIGURE 11. CAPACITANCE ( $C_{CB0}$ )




FIGURE 12. TURN-ON TIME (RESISTIVE LOAD)  
(D64DS ONLY)

T-33-29

D64DS5,6,7  
D64ES5,6,7

TYPICAL CHARACTERISTICS




FIGURE 13. TURN-ON TIME (RESISTIVE) (D64ES ONLY)




FIGURE 14. TURN-OFF TIME (RESISTIVE) (D64DS ONLY)




FIGURE 15. TURN-OFF TIME (RESISTIVE) (D64ES ONLY)




FIGURE 16. NORMALIZED RESISTIVE SWITCHING STORAGE TIME (RBE VARIATIONS) VS. COLLECTOR CURRENT (D64DS ONLY)




FIGURE 17. NORMALIZED RESISTIVE SWITCHING STORAGE TIME (RBE VARIATIONS) VS. COLLECTOR CURRENT (D64ES ONLY)




FIGURE 18. CLAMPED INDUCTIVE TURN-OFF TIME (D64DS ONLY)



D64DS5,6,7  
D64ES5,6,7

TYPICAL CHARACTERISTICS

T-33-29




FIGURE 19. CLAMPED INDUCTIVE TURN-OFF TIME (D64ES ONLY)




FIGURE 20. STORAGE TIME VARIATION WITH  $I_{B2}$  (D64DS ONLY)




FIGURE 21. STORAGE TIME VARIATION WITH  $I_{B2}$  (D64ES ONLY)




FIGURE 22. FALL TIME VARIATION WITH  $I_{B2}$  (D64DS ONLY)




FIGURE 23. FALL TIME VARIATION WITH  $I_{B2}$  (D64ES ONLY)




FIGURE 24. CROSS-OVER TIME VARIATION WITH  $I_{B2}$  (D64DS ONLY)

HARRIS SEMICONDUCTOR SECTOR 27E D 430227J 0020366 4 HAS

T-33-29

D64DS5,6,7  
D64ES5,6,7

TYPICAL CHARACTERISTICS




FIGURE 25. CROSS-OVER TIME VARIATION WITH  $I_{B2}$  (D64ES ONLY)




FIGURE 26. FORWARD BIAS SAFE OPERATING AREA




FIGURE 27. REVERSE BIAS SAFE OPERATING AREA




FIGURE 28. TRANSIENT THERMAL RESPONSE




FIGURE 29. POWER DERATING

D64DS5,6,7  
D64ES5,6,7

T-33-29

TYPICAL CHARACTERISTICS

HARRIS SEMICOND SECTOR

27E D ■ 430227J 0020368 & ■ HAS




FIGURE 30. DIODE CHARACTERISTICS




FIGURE 31. SWITCHING TIME TEST CIRCUIT