

		REVISIONS			
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE NEW DRAWING	04/JAN/22	IAN	TOMMY





2X RECOMMENDED TORQUE: 1.5-2.0 NM-

NOTES: UNLESS OTHERWISE SPECIFIED

1. RECEPTACLE MATERIAL:

SHELL: ALUMINUM ALLOY, ANODIZE

INSERT AND RETAINING RING: THERMOPLASTIC

SEAL: SILICONE RUBBER

2. BACKSHELL MATERIAL:

SHELL: ALUMINIUM ALLOY, NICKEL PLATED; LATCH SEGMENT: ALUMINIUM ALLOY, NICKEL PLATED; SCREW AND LOCK WASHER: STAINLESS STEEL;


BUSHING: EPDM.

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION):

IP69K(MATED CONDITION).

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. APPLY TO CABLE OD SIZE: Ø11.20-Ø24.08 . CAN BE USED:
- 4.1. WITH LARGE AND SMALL BUSHINGS IN PLACE.
- 4.2. WITH ONLY LARGE BUSHING IN PLACE.
- 4.3. WITH BOTH BUSHINGS REMOVED.
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6. SEE SPECIFIC RECEPTACLE DRAWING FOR:
 - 6.1 CONTACT SIZE AND WIRE RANGE.
 - 6.2 RETAINING RING COLOR.
 - 6.3 MATING PART(S).
 - 6.4 CONTACT LAYOUT AND ALL OTHER SPECIFICATIONS.







- Ø18.8 LARGE BUSHING

	AHDBM04-	24-91P	N-059	-059		REF:HD34-24-91PN-059				
QUANTITY	PART N	NUMBE	R	DESCRIPTION		П	TEM			
			MAT	ERI	ALS	S LI	ST			
UNLESS OTHER	WISE SPECIFIED	SIG	NATURES	DATE		Λ	:00 :0 b c			
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		DRAWN:	IAN.XIAO	04/JAN/22		H	mphe	SUO		
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	SULLEN.ZHANG	04/JAN/22	04/JAN/22 Sine Systems - www.amphenol-sine.com				-	
3) Note reference = X		ENGINEER:			44724 Morley Drive Clinton Township, MI 48036					
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY.XIE	05/JAN/22			Clinton Township, MI 460	030		-
		CUSTOMER	:	'	DURA	MATE	AHDBM RECEPT,	SIZE 24,	WD TH	HD,
			ING IS SUPPLIED F			KIT V	// CABLE CLAMP E	BACKSHE	LL	
PROCESS SPECIFICATIONS:		SPECIFICAT SHOWN HER THE AMPHE OF REPROD	TIONS AND PERFOIREON ARE THE PRENOL CORPORATION ARE IMPLES ARE SUBJECT TO	RMANCE DATA ROPERTY OF DN. NO RIGHTS JED. ALL	B	C-	AHDBM04-24-	91PN-05	9 A	sion 1
NEXT ASS'Y:			URING VARIATION:	S.	SCALE: NONE DURAMATE SHEET 1		OF 1	1		

TITLE: DURAMATE AHDBM RECEPT, SIZE 24, WD THD,KIT,RECPT AND BACKSHELL,SZ 24 DWG NO: AHDBM 04-24-91PN-059

SH:

A Series™ - Contact Size 8 Options (Works with: ATHD and DuraMate Series)

Machined Contacts, Pins and Sockets							
Part Number	Description	Size	AWG	Туре	Amps		
AT60-204-08141	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A		
AT62-203-08141	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A		
AT60-204-08141-16	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	6	Machined	60A		
AT62-203-08141-16	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	6	Machined	60A		

Tooling - Machined Contacts				
Part Number	Description			
WA23	Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961			
WA23-2	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 8			
WA23-3	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 6			
WA23-10	Contact Locator, Size 6 and Size 8			
96-978-22	Crimper and Dies -for Size 10mm²-185mm² Wires			
AT114008	Contact Removal Tool, Plastic, Size 8, 8-10AWG			

A Series™ - Contact Size 12 Options (Works with: AHD-6, ATP, ATHD, DuraMate and PanelMate Series)

Machined Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Туре			
*AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined			
*AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined			
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined			
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined			
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined			
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined			

^{*}Works with ATP Series only

	DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective								
	Part Number	Description	Size	AWG	Туре				
Γ	65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined				
	AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined				

Tooling - Machined Contacts						
Part Number	Description					
AUTK-12	Hand Crimp Tool, Size 12					
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20					
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20					
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20					
M300-25A	Hand Crimp Tool used with Crimp Locator MFX-3966, Size 12, 10AWG					
MFX-3966	Contact Locator used with Hand Crimp Tool M300-25A, Size 12, 10AWG					

Contact Removal Tools (For both Machined or Stamped & Formed Contacts)						
Part Number Description						
ATRT-100	Contact and Wedgelock Extraction Tool					
AT11-337-1205 Contact Removal Tool, Plastic, Size 12						

Sealing Plugs (For both Machined or Stamped & Formed Contacts)						
Part Number	Description					
A114017	Sealing Plug, Size 12, White					

Stamped & Formed Contacts, Sockets & Pins								
Part Number	Description	Size	AWG	Туре				
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed				
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed				
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed				
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed				
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed				
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed				
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed				
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed				

Tooling - Stamped & Formed Contacts					
Part Number	Description				
MFX-3973	Crimp Die - Size 12				
MFX-3985	Crimp Die - Svize 12, 10-12AWG -02XX Series				
ATT-12-00	Hand Crimp Tool - Size 12, 12AWG				
ATT-12-01	Hand Crimp Tool - Size 12, 10AWG				

A Series™ - Contact Size 16 Options (Works with: AT, ATV, AHD-9, ARC, DuraMate and PanelMate Series)

	Machined Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Туре				
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined				
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined				
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined				
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined				
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined				
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined				
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined				
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined				
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined				
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined				
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined				
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined				

Tooling - Machined Contacts			
Part Number	Description		
AUTK-16	Hand Crimp Tool, Size 16		
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20		
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20		
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20		

Contact Removal Tools (For both Machined or Stamped & Formed Contacts)				
Part Number	Description			
ATRT-100	Contact and Wedgelock Extraction Tool			
AT11-310-1605	Contact Removal Tool, Plastic, Size 16			

Sealing Plugs (For both Machined or Stamped & Formed Contacts)				
Part Number	Description			
A114017	Sealing Plug, Size 16, White			
A114017-SR	Sealing Plug, Size 16, SR01 Series, Black			
AT13-217-1605	Locking Sealing Plug, Size 16, Grey			
AT13-217-1605-SR	Locking Sealing Plug, Size 16, SR01 Series, Red			

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-18	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-18	Stamped & Formed		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-18	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	16-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	16-20	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	16-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	16-20	Stamped & Formed		
AT60-16-0677	Male Contact - Pin, Tin-plated	16	16-20	Stamped & Formed		
AT62-16-0677	Female Contact - Socket, Tin-plated	16	16-20	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		

Tooling - Stamped & Formed Contacts		
MFX-3950	Crimp Die - Size 16, 18-20AWG	
MFX-3953	Crimp Die - Size 16, 16-18AWG	
MFX-3975	Crimp Die - Size 16, 14-16AWG	
MFX-3990	Crimp Die - Size 16, 20-22AWG	
ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG	
ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG	
ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG	