

RN73C2A8R25BTDF ✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 8-1879160-1

8.25 Ω , Thin Film, Precision Resistor, .1 %, 2 Termination, 0805, Taped & Reeled, .1 W, ± 10 ppm/ $^{\circ}\text{C}$, Solder, Height .022 in [.55 mm], Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0805**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0805
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	100 V
Passive Component Tolerance	.1 %
Resistance Class	Up to 1k Ω
Resistance Value	8.25 Ω
Power Rating	.1 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]



Product Width	1.25 mm[.049 in]
---------------	------------------

Usage Conditions

Temperature Coefficient	± 10 ppm/ $^{\circ}\text{C}$
-------------------------	----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





















EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 <p>TE Part # 1676153-2 RN 0805 10K 0.1% 10PPM 1KRL</p>	 <p>TE Part # 1614349-9 RN 0603 10K 0.1% 10PPM CUT LENGTH</p>	 <p>TE Part # 1676153-3 RN 0805 10K 0.1% 10PPM 5KRL</p>	 <p>TE Part # 1-1676142-3 RN 0805 100K 0.01% 10PPM 5K RL</p>
 <p>TE Part # 8-1879130-4 RN 0402 5K11 0.1% 10PPM 5K RL</p>	 <p>TE Part # 4-1879160-1 RN 0805 5R11 0.1% 10PPM 5K RL</p>	 <p>TE Part # 4-1879160-3 RN 0805 5R23 0.1% 10PPM 5K RL</p>	 <p>TE Part # 4-1879160-5 RN 0805 5R36 0.1% 10PPM 5K RL</p>
 <p>TE Part # 4-1879160-7 RN 0805 5R49 0.1% 10PPM 5K RL</p>	 <p>TE Part # 4-1879160-9 RN 0805 5R62 0.1% 10PPM 5K RL</p>	 <p>TE Part # 5-1879160-1 RN 0805 5R76 0.1% 10PPM 5K RL</p>	 <p>TE Part # 5-1879160-3 RN 0805 5R9 0.1% 10PPM 5K RL</p>
 <p>TE Part # 5-1879160-5 RN 0805 6R04 0.1% 10PPM 5K RL</p>	 <p>TE Part # 5-1879160-7 RN 0805 6R19 0.1% 10PPM 5K RL</p>	 <p>TE Part # 5-1879160-9 RN 0805 6R34 0.1% 10PPM 5K RL</p>	 <p>TE Part # 6-1879160-1 RN 0805 6R49 0.1% 10PPM 5K RL</p>
 <p>TE Part # 6-1879160-3 RN 0805 6R65 0.1% 10PPM 5K RL</p>	 <p>TE Part # 6-1879160-5 RN 0805 6R81 0.1% 10PPM 5K RL</p>	 <p>TE Part # 6-1879160-7 RN 0805 6R98 0.1% 10PPM 5K RL</p>	 <p>TE Part # 6-1879160-9 RN 0805 7R15 0.1% 10PPM 5K RL</p>

Also in the Series | [Holsworthy RN73](#)



Customers Also Bought



Documents

Product Drawings

[RN 0805 8R25 0.1% 10PPM 1K RL](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_8-1879160-1_BA.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_8-1879160-1_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1879160-1_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[High Precision Resistors \(SMD\) - Type RN73 Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English