

1-794407-1 ✓ ACTIVE

MATE-N-LOK | Mini-Universal MATE-N-LOK

TE Internal #: 1-794407-1

Socket Contact, Gold, 600 VAC, 600 VDC, 20 – 16 AWG Wire Size, .  
5 – 1.4 mm<sup>2</sup> Wire Size, Crimp, Phosphor Bronze, Power, Mini-  
Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **600 VDC**

## Features

### Product Type Features

Discrete Wire Type Stranded

### Electrical Characteristics

Operating Voltage 600 VDC

### Contact Features

Mating Pin Diameter 1 mm[.039 in]

Contact Underplating Material Thickness 1.27 µm[50 µin]

Wire Contact Termination Area Plating Thickness 2.54 – 6.35 µm[100 – 250 µin]

Wire Contact Termination Area Plating Material Finish Bright

Contact Mating Area Plating Material Thickness .76 µm[30 µin]

Contact Orientation Straight

Contact Underplating Material Nickel

Contact Type Socket

Contact Mating Area Plating Material Gold

Wire Contact Termination Area Plating Material Tin

Contact Retention Within Housing With



Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11.2 A

### Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

### Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

### Dimensions

Compatible Insulation Diameter Range	2 – 3.2 mm [.079 – .126 in]
Wire Size	.5 – 1.4 mm <sup>2</sup>

### Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Industry Standards

Compatible With Agency/Standards Products	CSA, UL
-------------------------------------------	---------

### Packaging Features

Packaging Quantity	4500
Packaging Method	Reel

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer







This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts


 <p>TE Part # 770586-1 22P MINI UMNL PLUG HSG</p>	 <p>TE Part # 770587-1 24P MINI UMNL PLUG HSG</p>	 <p>TE Part # 770582-1 14P MINI UMNL PLUG HSG</p>	 <p>TE Part # 770585-1 20P MINI UMNL PLUG HSG</p>
 <p>TE Part # 172333-1 MINI UNIVERSAL M-N-L HOUSING</p>	 <p>TE Part # 770581-1 12P MINI UMNL PLUG HSG</p>	 <p>TE Part # 770580-1 10P MINI UMNL PLUG HSG</p>	 <p>TE Part # 770584-1 18P MINI UMNL PLUG HSG</p>
 <p>TE Part # 172328-1 MINI UNIVERSAL MATE-N-LOK CAP HOUSING 2P</p>	 <p>TE Part # 172330-1 MINI UNIVERSAL MATE-N-LOK CAP HOUSING 4P</p>	 <p>TE Part # 172344-1 MINI UNIVERSAL MATE-N-LOK CAP HOUSING 3P</p>	 <p>TE Part # 172170-1 12 CIR UNIV M-N-L PLUG</p>



## Also in the Series | Mini-Universal MATE-N-LOK



## Customers Also Bought





TE Part #2150041-2  
[OCEAN\\_2.0\\_Applicator-E-110F180F](#)



TE Part #2151168-1  
[OCEAN\\_2.0\\_Applicator-S-090F102F](#)



TE Part #2151314-1  
[OCEAN\\_2.0\\_Applicator-S-110F155F](#)



TE Part #2837605-1  
[OCEAN-2.0-APPLICATOR-S-112O160F](#)



TE Part #466178-1  
[HDM EMPO062F140FT](#)

## Documents

### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_1-794407-1\\_F.2d\\_dxf.zip](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_1-794407-1\\_F.3d\\_igs.zip](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_1-794407-1\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_AND\\_SOCKET\\_CONNECTORS\\_CATALOG](#)

English

### Product Specifications

[Application Specification](#)

English