




**RAST**

TE Internal #: 2825197-1

Socket Contact, Tin, 20 – 17 AWG Wire Size, .5 – 1 mm<sup>2</sup> Wire Size, Power, -40 – 266 °F [-40 – 130 °C]

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin**

Wire Size: **.5 – 1 mm<sup>2</sup>**

Product Terminates To: **Wire & Cable**

**Features**

**Contact Features**

Mating Tab Width	6.3 mm[.248 in]
Mating Tab Thickness	.8 mm[.031 in]
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	16 A

**Termination Features**

Product Terminates To	Wire & Cable
-----------------------	--------------

**Dimensions**

Wire Size	.5 – 1 mm <sup>2</sup>
-----------	------------------------

**Usage Conditions**

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
-----------------------------	----------------------------

**Operation/Application**

Circuit Application	Power
---------------------	-------

**Packaging Features**

Packaging Method	Reel & Carton
------------------	---------------



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 1241959-4 STD-TIM HSG MKII 4P</p>	 <p>TE Part # 2836290-1 OCEAN_2.0_APPLICATOR-S-081F110OV</p>	 <p>TE Part # 2836290-2 OCEAN_2.0_APPLICATOR-S-081F110OV</p>	 <p>TE Part # 7-2151176-1 OCEAN_2.0_APPLICATOR-S-080F110OV</p>
----------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------



## Customers Also Bought



## Documents

### Product Drawings

[STD PW TIMER CONTACT](#)

English

### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_2825197-1\\_A.2d\\_dxf.zip](#)

2825197-1

Socket Contact, Tin, 20 – 17 AWG Wire Size, .5 – 1 mm<sup>2</sup> Wire Size, Power, -40 – 266 °F  
[-40 – 130 °C]



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2825197-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2825197-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.