## SIEMENS

## Data sheet

## US2:17CUD92BA10



Non-reversing motor starter, Size 0, Three phase full voltage, Solid-state overload relay, OLR amp range 5.5-22A, Combination type, 30A fusible disconnect, 30A/250V fuse clip, Enclosure NEMA type 1, Indoor general purpose use, Standard width enclosure

| Figuresimilar | Fi | gu | ire | si | m | ilar |
|---------------|----|----|-----|----|---|------|
|---------------|----|----|-----|----|---|------|

| product brand name   | Class 17  |  |  |
|--|---|--|--|
| design of the product  | Non-reversing motor starter with fusible disconnect |  |  |
| special product feature  | ESP200 overload relay; Dual voltage coil            |  |  |
| General technical data   |   |  |  |
| weight [lb]  | 34 lb   |  |  |
| Height x Width x Depth [in]  | 24 × 11 × 8 in                                      |  |  |
| touch protection against electrical shock                                  | NA for enclosed products                            |  |  |
| installation altitude [ft] at height above sea level maximum               | 6560 ft   |  |  |
| ambient temperature [°F]   |   |  |  |
| <ul> <li>during storage</li> </ul>   | -22 +149 °F   |  |  |
| during operation   | -4 +104 °F  |  |  |
| ambient temperature  |   |  |  |
| <ul> <li>during storage</li> </ul>   | -30 +65 °C  |  |  |
| during operation   | -20 +40 °C  |  |  |
| country of origin  | USA   |  |  |
| Horsepower ratings   |   |  |  |
| yielded mechanical performance [hp] for 3-phase AC motor                   |   |  |  |
| • at 200/208 V rated value   | 3 hp  |  |  |
| • at 220/230 V rated value   | 3 hp  |  |  |
| • at 460/480 V rated value   | 0 hp  |  |  |
| <ul> <li>at 575/600 V rated value</li> </ul>                               | 0 hp  |  |  |
| Contactor  |   |  |  |
| size of contactor  | NEMA controller size 0                              |  |  |
| number of NO contacts for main contacts                                    | 3   |  |  |
| operating voltage for main current circuit at AC at 60 Hz maximum          | 600 V   |  |  |
| operational current at AC at 600 V rated value                             | 18 A  |  |  |
| mechanical service life (switching cycles) of the main<br>contacts typical | 1000000   |  |  |
| Auxiliary contact  |   |  |  |
| number of NC contacts at contactor for auxiliary contacts                  | 0   |  |  |
| number of NO contacts at contactor for auxiliary contacts                  | 1   |  |  |
| number of total auxiliary contacts maximum                                 | 8   |  |  |
| contact rating of auxiliary contacts of contactor according to UL          | 10A@600VAC (A600), 5A@600VDC (P600)                 |  |  |
| Coil   |   |  |  |
| type of voltage of the control supply voltage                              | AC  |  |  |
| control supply voltage   |   |  |  |

| a at AC at CO Lie rated value   | 440 94037  |
|---|--|
| at AC at 60 Hz rated value  | 110 240 V  |
| holding power at AC minimum   | 8.6 W  |
| apparent pick-up power of magnet coil at AC   | 218 VA   |
| apparent holding power of magnet coil at AC   | 25 VA  |
| operating range factor control supply voltage rated value<br>of magnet coil   | 0.85 1.1   |
| percental drop-out voltage of magnet coil related to the input voltage  | 50 %   |
| ON-delay time   | 19 29 ms   |
| OFF-delay time  | 10 24 ms   |
| Overload relay  |  |
| product function  |  |
| overload protection   | Yes  |
| phase failure detection   | Yes  |
| asymmetry detection   | Yes  |
| ground fault detection  | Yes  |
| test function   | Yes  |
| external reset  | Yes  |
| reset function  | Manual, automatic and remote                     |
| trip class  | CLASS 5 / 10 / 20 (factory set) / 30             |
| adjustable current response value current of the current-<br>dependent overload release   | 5.5 22 A   |
| tripping time at phase-loss maximum   | 3 s  |
| relative repeat accuracy  | 1 %  |
| product feature protective coating on printed-circuit board   | Yes  |
| number of NC contacts of auxiliary contacts of overload relay   | 1  |
| number of NO contacts of auxiliary contacts of overload relay   | 1  |
| operational current of auxiliary contacts of overload relay   |  |
| • at AC at 600 V  | 5 A  |
| ● at DC at 250 V  | 1 A  |
| contact rating of auxiliary contacts of overload relay according to UL  | 5A@600VAC (B600), 1A@250VDC (R300)               |
| insulation voltage (Ui)   |  |
| <ul> <li>with single-phase operation at AC rated value</li> </ul>   | 600 V  |
| <ul> <li>with multi-phase operation at AC rated value</li> </ul>  | 300 V  |
| Disconnect Switch   |  |
| response value of switch disconnector   | 30A / 250V                                       |
| design of fuse holder   | Class R fuse clips                               |
| operating class of the fuse link  | Class R  |
| Enclosure   |  |
| degree of protection NEMA rating  | 1  |
| design of the housing   | indoors, usable on a general basis               |
| Mounting/wiring   |  |
|   | vertical   |
| mounting position   | vertical   |
| fastening method  | Surface mounting and installation                |
| type of electrical connection for supply voltage line-side  | Box lug  |
| tightening torque [lbf·in] for supply   | 35 35 lbf in                                     |
| type of connectable conductor cross-sections at line-side<br>at AWG cables single or multi-stranded   | 1x (14 2 AWG)                                    |
| temperature of the conductor for supply maximum   | 75.00  |
| permissible   | 75 °C  |
| permissible<br>material of the conductor for supply   | AL or CU   |
| permissible<br>material of the conductor for supply<br>type of electrical connection for load-side outgoing feeder  | AL or CU<br>Screw-type terminals                 |
| permissible<br>material of the conductor for supply<br>type of electrical connection for load-side outgoing feeder<br>tightening torque [lbf-in] for load-side outgoing feeder  | AL or CU<br>Screw-type terminals<br>20 20 lbf·in |
| permissible<br>material of the conductor for supply<br>type of electrical connection for load-side outgoing feeder  | AL or CU<br>Screw-type terminals                 |
| permissible         material of the conductor for supply         type of electrical connection for load-side outgoing feeder         tightening torque [lbf-in] for load-side outgoing feeder         type of connectable conductor cross-sections at AWG         cables for load-side outgoing feeder single or multi- | AL or CU<br>Screw-type terminals<br>20 20 lbf·in |

| type of electrical connection of magnet coil   | Screw-type terminals                                |  |  |  |  |
|--|---|--|--|--|--|
| tightening torque [lbf·in] at magnet coil  | 5 12 lbf·in   |  |  |  |  |
| type of connectable conductor cross-sections of magnet<br>coil at AWG cables single or multi-stranded  | 2x (16 12 AWG)                                      |  |  |  |  |
| temperature of the conductor at magnet coil maximum permissible  | 75 °C   |  |  |  |  |
| material of the conductor at magnet coil   | CU  |  |  |  |  |
| type of electrical connection for auxiliary contacts   | Screw-type terminals                                |  |  |  |  |
| tightening torque [lbf·in] at contactor for auxiliary contacts   | 10 15 lbf·in  |  |  |  |  |
| type of connectable conductor cross-sections at contactor<br>at AWG cables for auxiliary contacts single or multi-<br>stranded   | 1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)         |  |  |  |  |
| temperature of the conductor at contactor for auxiliary<br>contacts maximum permissible  | 75 °C   |  |  |  |  |
| material of the conductor at contactor for auxiliary contacts  | CU  |  |  |  |  |
| type of electrical connection at overload relay for auxiliary<br>contacts  | Screw-type terminals                                |  |  |  |  |
| tightening torque [lbf·in] at overload relay for auxiliary contacts  | 7 10 lbf·in   |  |  |  |  |
| type of connectable conductor cross-sections at overload<br>relay at AWG cables for auxiliary contacts single or multi-<br>stranded  | 2x (20 14 AWG)                                      |  |  |  |  |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible  | 75 °C   |  |  |  |  |
| material of the conductor at overload relay for auxiliary contacts   | CU  |  |  |  |  |
| Short-circuit current rating   |   |  |  |  |  |
| design of the fuse link for short-circuit protection of the<br>main circuit required   | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |  |  |  |  |
| certificate of suitability   | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |  |  |  |  |
| Further information  |   |  |  |  |  |
| Industrial Controls - Product Overview (Catalogs, Brochures,)<br>www.usa.siemens.com/iccatalog   |   |  |  |  |  |
| · · · · · · · · · · · · · · · · · · ·  |   |  |  |  |  |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,)<br>https://support.industry.siemens.com/cs/US/en/ps/US2:17CUD92BA10  |   |  |  |  |  |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,)<br>http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17CUD92BA10⟨=en |   |  |  |  |  |
| Certificates/approvals   |   |  |  |  |  |

Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17CUD92BA10/certificate

last modified:

1/25/2022 🖸