## SIEMENS

## Data sheet

## US2:14LPU32AE



Non-reversing motor starter Size 5 Three phase full voltage Solid-state overload relay OLRelay amp range 55-250A 575-600V 50-60HZ/DC coil Combination type No enclosure

Fig	ure	sin	nilar

product brand name	Class 14			
design of the product	Full-voltage non-reversing motor starter			
General technical data				
weight [lb]	21 lb			
Height x Width x Depth [in]	12.92 × 6.5 × 8.94 in			
touch protection against electrical shock	Main circuit (not finger-safe); Control circuit (finger-safe)			
installation altitude [ft] at height above sea level maximum	6560 ft			
ambient temperature [°F]				
<ul> <li>during storage</li> </ul>	-22 +149 °F			
during operation	-4 +104 °F			
ambient temperature				
<ul> <li>during storage</li> </ul>	-30 +65 °C			
during operation	-20 +40 °C			
Horsepower ratings				
yielded mechanical performance [hp] for 3-phase AC				
motor	75 hr			
at 200/208 V rated value	75 hp			
<ul> <li>at 220/230 V rated value</li> <li>at 460/480 V rated value</li> </ul>	100 hp			
<ul> <li>at 450/480 V rated value</li> <li>at 575/600 V rated value</li> </ul>	200 hp			
	200 hp			
Contactor				
size of contactor	NEMA controller size 5			
number of NO contacts for main contacts	3 600 V			
operating voltage for main current circuit at AC at 60 Hz maximum	600 V			
operational current at AC at 600 V rated value	270 A			
mechanical service life (switching cycles) of the main contacts typical	1000000			
Auxiliary contact				
number of NC contacts at contactor for auxiliary contacts	2			
number of NO contacts at contactor for auxiliary contacts	2			
number of total auxiliary contacts maximum	8			
contact rating of auxiliary contacts of contactor according to UL	10A@240VAC (A300), 2.5A@250VDC (Q300)			
Coil				
type of voltage of the control supply voltage	AC/DC			
control supply voltage				
<ul> <li>at DC rated value</li> </ul>	575 600 V			
<ul> <li>at AC at 50 Hz rated value</li> </ul>	575 600 V			

• at AC at 60 Hz rated value	575 600 V
holding power at AC minimum	7.4 W
apparent pick-up power of magnet coil at AC	590 VA
apparent holding power of magnet coil at AC	6.7 VA
operating range factor control supply voltage rated value	0.85 1.1
of magnet coil	
percental drop-out voltage of magnet coil related to the input voltage	60 %
ON-delay time	30 95 ms
OFF-delay time	40 80 ms
Overload relay	
product function	
<ul> <li>overload protection</li> </ul>	Yes
<ul> <li>phase failure detection</li> </ul>	Yes
<ul> <li>asymmetry detection</li> </ul>	Yes
<ul> <li>ground fault detection</li> </ul>	No
test function	Yes
external reset	No
reset function	Manual and automatic
trip class	CLASS 20
adjustable current response value current of the current- dependent overload release	55 250 A
product feature protective coating on printed-circuit board	No
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay	5A@600VAC (B600), 1A@250VDC (R300)
according to UL	
insulation voltage (Ui)	
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V
<ul> <li>with multi-phase operation at AC rated value</li> </ul>	300 V
Enclosure	
degree of protection NEMA rating	Open device (no enclosure)
design of the housing	NA
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf·in] for supply	180 195 lbf·in
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	3/0 AWG - 600 MCM (front only) or 250 - 500 MCM (back only) or 2 x 2/0 AWG - 2 x 500 MCM (both front & back)
temperature of the conductor for supply maximum permissible	75 °C
type of electrical connection for load-side outgoing feeder	Box lug
tightening torque [lbf·in] for load-side outgoing feeder	180 220 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	2 x 2/0 AWG - 500 MCM
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
material of the conductor for load-side outgoing feeder	CU
type of electrical connection of magnet coil	screw-type terminals
tightening torque [lbf·in] at magnet coil	7 10 lbf·in
type of connectable conductor cross-sections of magnet	2 x (18 - 14 AWG)
coil at AWG cables single or multi-stranded temperature of the conductor at magnet coil maximum	75 °C
permissible	
material of the conductor at magnet coil type of electrical connection for auxiliary contacts	CU

tightening torque [lbf·in] at contactor for auxiliary contacts	7 10 lbf·in
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	2x (20 - 16), 2x (18 - 14)
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C
material of the conductor at contactor for auxiliary contacts	CU
type of electrical connection at overload relay for auxiliary contacts	screw-type terminals
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2 x (20 - 14 AWG)
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C
material of the conductor at overload relay for auxiliary contacts	CU
Short-circuit current rating	
design of the fuse link for short-circuit protection of the main circuit required	14kA@600V (Class H or K); 100kA@600V (Class R or J)
design of the short-circuit trip	Thermal magnetic circuit breaker
breaking capacity maximum short-circuit current (lcu)	
• at 240 V	14 kA
• at 480 V	14 kA
• at 600 V	14 kA
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14
Further information	
Industrial Controls - Product Overview (Catalogs, Broch www.usa.siemens.com/iccatalog Industry Mall (Online ordering system)	Jres,)


Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14LPU32AE

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:14LPU32AE

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:14LPU32AE&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:14LPU32AE/certificate



last modified:

11/29/2021 🖸