## **SIEMENS**

Data sheet US2:17DUA92BH11



Non-reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 0.25-1A, Combination type, 30A fusible disconnect, 30A/600V fuse clip, Enclosure NEMA type 1, Indoor general purpose use, Standard width enclosure

Figure similar

product brand name	Class 17	
design of the product	Non-reversing motor starter with fusible disconnect	
special product feature	ESP200 overload relay	
General technical data		
weight [lb]	34 lb	
Height x Width x Depth [in]	24 × 11 × 8 in	
touch protection against electrical shock	NA for enclosed products	
installation altitude [ft] at height above sea level maximum	6560 ft	
ambient temperature [°F]		
<ul> <li>during storage</li> </ul>	-22 +149 °F	
during operation	-4 +104 °F	
ambient temperature		
<ul> <li>during storage</li> </ul>	-30 +65 °C	
during operation	-20 +40 °C	
country of origin	USA	
Horsepower ratings		
yielded mechanical performance [hp] for 3-phase AC motor		
• at 200/208 V rated value	0 hp	
• at 220/230 V rated value	0 hp	
• at 460/480 V rated value	0.33 hp	
• at 575/600 V rated value	0.5 hp	
Contactor		
size of contactor	NEMA controller size 1	
number of NO contacts for main contacts	3	
operating voltage for main current circuit at AC at 60 Hz maximum	600 V	
operational current at AC at 600 V rated value	27 A	
mechanical service life (switching cycles) of the main contacts typical	10000000	
Auxiliary contact		
number of NC contacts at contactor for auxiliary contacts	0	
number of NO contacts at contactor for auxiliary contacts	1	
number of total auxiliary contacts maximum	8	
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)	
Coil		
type of voltage of the control supply voltage	AC	
control supply voltage		

at AC at 50 Hz == t-1 := t-2	200 440 V
at AC at 50 Hz rated value	380 440 V
at AC at 60 Hz rated value  holding power at AC minimum	440 480 V
holding power at AC minimum	8.6 W
apparent holding power of magnet coil at AC	218 VA 25 VA
apparent holding power of magnet coil at AC	
operating range factor control supply voltage rated value of magnet coil	0.85 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	19 29 ms
OFF-delay time	10 24 ms
Overload relay	
product function	
<ul> <li>overload protection</li> </ul>	Yes
<ul> <li>phase failure detection</li> </ul>	Yes
<ul> <li>asymmetry detection</li> </ul>	Yes
<ul> <li>ground fault detection</li> </ul>	Yes
• test function	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	0.25 1 A
tripping time at phase-loss maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
	5A@600VAC (B600), 1A@250VDC (R300)
contact rating of auxiliary contacts of overload relay according to UL	3A@000VAC (B000), IA@230VDC (K300)
insulation voltage (Ui)	000.1/
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V
with multi-phase operation at AC rated value	300 V
Disconnect Switch	
response value of switch disconnector	30A / 600V
design of fuse holder	Class R fuse clips
operating class of the fuse link	Class R
Enclosure	
degree of protection NEMA rating	1
design of the housing	indoors, usable on a general basis
Mounting/wiring	
mounting position	vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf-in] for supply	35 35 lbf·in
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Screw-type terminals
tightening torque [lbf·in] for load-side outgoing feeder	20 24 lbf·in
type of connectable conductor cross-sections at AWG	
cables for load-side outgoing feeder single or multi- stranded	2x (14 10 AWG)
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
- p <del>-</del>	

of the conductor for load-side outgoing feeder CU		
ectrical connection of magnet coil Screw-type terminals		
torque [lbf·in] at magnet coil 5 12 lbf·in		
onnectable conductor cross-sections of magnet 2x (16 12 AWG) //G cables single or multi-stranded	2x (16 12 AWG)	
ure of the conductor at magnet coil maximum 75 °C		
of the conductor at magnet coil CU		
ectrical connection for auxiliary contacts Screw-type terminals		
torque [lbf·in] at contactor for auxiliary contacts 10 15 lbf·in		
nnectable conductor cross-sections at contactor ables for auxiliary contacts single or multi-	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)	
ure of the conductor at contactor for auxiliary 75 °C maximum permissible		
of the conductor at contactor for auxiliary contacts CU		
ectrical connection at overload relay for auxiliary  Screw-type terminals	Screw-type terminals	
torque [lbf·in] at overload relay for auxiliary 7 10 lbf·in		
onnectable conductor cross-sections at overload 2x (20 14 AWG) WG cables for auxiliary contacts single or multi-		
ure of the conductor at overload relay for auxiliary 75 °C maximum permissible		
of the conductor at overload relay for auxiliary		
uit current rating		
the fuse link for short-circuit protection of the uit required 10kA@600V (Class H or K); 100kA@600V	600V (Class R or J)	
of suitability NEMA ICS 2; UL 508; CSA 22.2, No.1	14	
ormation		
uit required	,	
ormation		

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUA92BH11

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:17DUA92BH11

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:17DUA92BH11&lang=en">http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:17DUA92BH11&lang=en</a>

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:17DUA92BH11/certificate

last modified: 1/25/2022 🖸