

# H3-TCM2-672X+

1700-6700MHz 50Ω 1:2 Balun


## APPLICATIONS

Ideally suited for high volume cellular and wireless applications.

## FEATURES

- Surface mount
- Impedance ratio: 1:2
- Available on tape and reel
- RoHS compliant and Pb free
- 260°C reflow compatible

## DIMENSIONS




A	B	C
3.81	3.81	2.80
D		
1.27		

Unless otherwise stated dimensions are in mm


Tolerance: .xx ± 0.25, .xxx ± 0.05

## Land Pattern



E	F	G
4.83	3.30	1.40
H	J	
0.76	1.27	

## FUNCTIONAL SCHEMATIC






## PIN CONFIGURATION

Pin No.	Function
1	Not Used
2	Primary
3	Primary Dot
4	Secondary Dot
5	Secondary
6	Not Used


## ELECTRICAL SPECIFICATIONS@25°C:

Parameters (P#: ENA PORT)	frequency band	Min.	Typ.	Max.	Unit
Port Impedance, Z0 (P1 / P2 / P3)			50/ 25/ 25		Ohm
Insertion Loss	1700-6700MHz		1.6	2.5	dB
Amplitude Balance	1700-6700MHz		0.8		dB
Phase Unbalance	1700-6700MHz		6		°

## TEST CURVE



## APPLICATION & TEST CIRCUIT



## ABSOLUTE MAXIMUM RATINGS

Parameter	Value
Input Power	250mW MAX
DC Current	30mA MAX
Operating Temperature Range	-40 to 85°C

Tel: +86-28-85589664

E-mail: mr\_li@henglitaitech.com

Web: www.hltchips.com

Adress:No.198 Tianqin East Street, Gaoxin West District, Chengdu City