



Neohm | Neohm CRGP

TE Internal #: 2176325-5

22 Ω, Thick Film, General Purpose Resistor, 1 %, 2 Termination, 0402, Taped & Reeled, .125 W, ±200 ppm/°C, Solder, Height .014 in [.35 mm], Neohm CRGP

[View on TE.com >](#)

Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**

Number of Terminations: **2**

Package Size Code: **0402**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Package Size Code	0402
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	22 Ω
Power Rating	.125 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	.35 mm[.014 in]
Product Length	1.1 mm[.043 in]



Product Width	.5 mm[.02 in]
---------------	---------------

Usage Conditions

Temperature Coefficient	± 200 ppm/ $^{\circ}\text{C}$
-------------------------	-----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2176326-2
CRGP 0603 12R 1%



TE Part # 5-2176327-4
CRGP 0805 270K 1%



TE Part # 2-2176328-3
CRGP 1206 680R 1%



TE Part # 6-2176330-1
CRGP 2010 1M0 1%



TE Part # 4-2176331-9
CRGP 2512 100K 1%

Also in the Series | **Neohm CRGP**



Surface Mount Resistors(432)

Customers Also Bought



TE Part #1-2213766-7
AV19 SPM 5A POWER LED BLUE 12V



TE Part #8-1879494-9
CRGH0603 5% 4K7 0.2W



TE Part #3-2176325-7
CRGP 0402 10K 1%



TE Part #2-2176325-5
CRGP 0402 1K0 1%



TE Part #2176325-7
CRGP 0402 33R 1%



TE Part #1-2007394-8
SFP+ assy 2x4 EMI Sprng No Lp Sn Enhanced



TE Part #2214565-1
zQSFP+ STACKED RECEPTACLE ASSEMBLY 2X3



TE Part #2302794-1
RAPLUGASSY,CENTERRP0,RTM,VPX, MGRT3



TE Part #2302796-1
RAPLUGASSY,LEFTEND,HALF,RTM,
VPX,MGRT3



TE Part #L9000246-01
MCX Jack 50 Ohm .062 PCB Edge
Mount

Documents

Product Drawings

[CRGP 0402 22R 1%](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2176325-5_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176325-5_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176325-5_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CRGP Data Sheet](#)

English