

# APBA3010SEKCGKC-GX

3.0 mm x 1.0 mm Right Angle SMD Chip LED Lamp

## **DESCRIPTIONS**

- The Super Bright Orange device is made with AlGaInP (on GaAs substrate) light emitting diode chip
- The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- . It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

## **FEATURES**

- 3.0 x 2.0 x 1.0 mm right angle SMD LED, 1.0 mm thickness
- Low power consumption
- · Wide viewing angle
- · Ideal for backlight and indicator
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- · Tinned pads for improved solderability
- RoHS compliant

## **APPLICATIONS**


- Backlight
- · Status indicator
- Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

## **ATTENTION**

Observe precautions for handling electrostatic discharge sensitive devices




## **PACKAGE DIMENSIONS**



## RECOMMENDED SOLDERING PATTERN

(units: mm; tolerance: ± 0.1)



- 1 All dimensions are in millimeters (inches)
- Tolerance is ±0.15(0.006") unless otherwise noted.
  The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- The device has a single mounting surface. The device must be mounted according to the specifications. For right angle SMD LEDs, the solder stencil should be at least 5mil in thickness, to prevent poor solder due to insufficient solder paste.

#### **SELECTION GUIDE**

Part Number	Emitting Color (Material)	Lens Type	Iv (mcd) @ 20mA [2]		Viewing Angle [1]	
			Min.	Тур.	201/2	
APBA3010SEKCGKC-GX	Super Bright Orange (AlGaInP)	- Water Clear	120	320		
			*80	*150	140°	
	Green (AlGaInP)		40	70		
			*40	*70		

Notes.

1. 61/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity / luminous flux: +/-15%.

\* Luminous intensity value is traceable to CIE127-2007 standards.





# ELECTRICAL / OPTICAL CHARACTERISTICS at T<sub>A</sub>=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Farameter			Тур.	Max.	Uill
Wavelength at Peak Emission I <sub>F</sub> = 20mA	$\lambda_{peak}$	Super Bright Orange Green	610 574	-	nm
Dominant Wavelength I <sub>F</sub> = 20mA	λ <sub>dom</sub> <sup>[1]</sup>	Super Bright Orange Green	605 570	-	nm
Spectral Bandwidth at 50% $\Phi$ REL MAX I <sub>F</sub> = 20mA	Δλ	Super Bright Orange Green	29 20	-	nm
Capacitance	С	Super Bright Orange Green	15 15	-	pF
Forward Voltage I <sub>F</sub> = 20mA	V <sub>F</sub> <sup>[2]</sup>	Super Bright Orange Green	2.1 2.1	2.5 2.5	V
Reverse Current (V <sub>R</sub> = 5V)	I <sub>R</sub>	Super Bright Orange Green	-	10 10	μА
Temperature Coefficient of $\lambda_{peak}$ $I_F=20mA, -10^{\circ}C \leq T \leq 85^{\circ}C$	$TC_{\lambda peak}$	Super Bright Orange Green	0.13 0.12	-	nm/°C
Temperature Coefficient of $\lambda_{dom}$ $I_F = 20mA, -10^{\circ}C \leq T \leq 85^{\circ}C$	$TC_{\lambdadom}$	Super Bright Orange Green	0.06 0.08	-	nm/°C
Temperature Coefficient of $V_F$ $I_F$ = 20mA, -10°C $\leq$ T $\leq$ 85°C	TC <sub>V</sub>	Super Bright Orange Green	-1.9 -1.9	-	mV/°C

# ABSOLUTE MAXIMUM RATINGS at T<sub>A</sub>=25°C

Parameter	Symbol	Va	Unit	
Farameter	Symbol	Super Bright Orange	Green	Ullit
Power Dissipation	P <sub>D</sub>	75	75	mW
Reverse Voltage	V <sub>R</sub>	5	5	V
Junction Temperature	TJ	115	115	°C
Operating Temperature	T <sub>op</sub>	-40 To +85		°C
Storage Temperature	T <sub>stg</sub>	-40 To +85		°C
DC Forward Current	I <sub>F</sub>	30	30	mA
Peak Forward Current	I <sub>FM</sub> <sup>[1]</sup>	195	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	3000	V
Thermal Resistance (Junction / Ambient)	R <sub>th JA</sub> <sup>[2]</sup>	670	620	°C/W
Thermal Resistance (Junction / Solder point)	R <sub>th JS</sub> <sup>[2]</sup>	580	510	°C/W

Notes:
1. 1/10 Duty Cycle, 0.1ms Pulse Width.
2.  $R_{\text{Ib.Ja}}$ ,  $R_{\text{Rb.Ja}}$ ,  $R_{\text{Bulls}}$  from mounting on PC board FR4 (pad size  $\geq$  16 mm<sup>2</sup> per pad).
3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.




<sup>1.</sup> The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd:±1nm.)
2. Forward voltage: ±0.1V.
3. Wavelength value is traceable to CIE127-2007 standards.
4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.




## **TECHNICAL DATA**


#### **RELATIVE INTENSITY vs. WAVELENGTH**





#### **SPATIAL DISTRIBUTION**




## **SUPER BRIGHT ORANGE**













## **GREEN**












#### **REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS**


#### 300 above 255°C (°C) 260°C max. 30s max. 10s max. 250 3°C/s max. 6°C/s max. 200 150 pre-heating 100 150~200°C above 217°C 60~120s 60~150s 50 -25°C 0 0 50 100 150 200 250 300 (sec) Time

- 1. Don't cause stress to the LEDs while it is exposed to high temperature.
  2. The maximum number of reflow soldering passes is 2 times.
  3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.


#### TAPE SPECIFICATIONS (units:mm)



#### **REEL DIMENSION** (units: mm)



## **PACKING & LABEL SPECIFICATIONS**



#### **PRECAUTIONARY NOTES**

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.

  The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening
- liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.

  The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- All design applications should refer to Kingbright application notes available at <a href="https://www.https://www.ntmag.new.new.ntmag.ntmag.n

