

GPS+GSM Active Antenna Module-Screw mount plus adhesive tape.

APAMS-106

RoHS/RoHS II compliant

Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-1)



Ø75 x 14.1mm

MSL level: Not Applicable

FEATURES:

- Dual Band
- High Reliability/Sensitivity
- Compact Size, Easy to install
- ROHS Compliant

TYPICAL APPLICATIONS:

- GPS navigation
- Vehicle tracking
- Telemetry Applications
- Asset tracking
- Emergency call systems

STANDARD SPECIFICATIONS:

Antenna

Parameters	Min.	Typ.	Max.	Units	Note
Center Frequency	1574.40	1575.42	1576.44	MHz	
Bandwidth	10.0			MHz	
VSWR			1.5:1		
Polarization Model	RHCP				(Right Hand Circular Polarization)
Impedance		50		Ω	
Gain		5		dBic	(Based on 70× 70mm ground plane)
Operating Temperature	-40		+80	°C	
Storage Temperature	-45		+85	°C	

Low Noise Amplifier (LNA)

Parameters	Min.	Typ.	Max.	Units	Note
Center Frequency	1574.40	1575.42	1576.44	MHz	
DC Voltage	2.5	3.0	3.5	V	
Gain	25	26	28	dB	(Without cable +25°C± 10°C)
Output VSWR			2.0		
Noise Figure			1.5		(+25°C ± 10°C)
DC current		10.5	12.5	mA	

Electrical Characteristics (GSM)

Parameters	Min.	Typ.	Max.	Units	Note
Working Frequency	806		960	MHz	
	1710		1880		
Peak Gain			-1	dBi	(@900MHZ)
			1		(@1800MHZ)
VSWR			2:1		
Impedance		50		Ω	
Azimuth	Omni-Directional				
Polarization	Linear Polarization				


GPS+GSM Active Antenna Module-Screw mount plus adhesive tape.

APAMS-106


RoHS/RoHS II compliant
Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-1)



ANTENNA'S IMPEDANCE AND RETURN-LOSS CHARACTERISTICS



LNA REFLECTION PROFILE



OUTLINE DRAWING:

14,10
75,00
0,80
18,00
L1
L2
25
25

Golden SMA Connected to GSM Antenna
Silver SMA Connected to GPS Antenna

Parameters	Description
L1(Cable1 Length)	200±10cm
L2(Cable2 Length)	200±10cm
Antenna	Dielectric Ceramics
PCB	FR4
GPS RF Connector	Silver SMA-J3
GSM RF Connector	Golden SMA-J3
Shielding	Tinplate
Thickness	15mm
Mounting Type	Screw Mount plus Adhesive Tape

Bottom View
Top View

Unit:mm

ABRACON IS
ISO9001:2008
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 10.23.14**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

GPS+GSM Active Antenna Module-Screw mount plus adhesive tape.

APAMS-106

RoHS/RoHS II compliant
Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-1)



PRODUCT IMAGE:



PACKAGING:

Each 450 x 400 x 300mm size carton includes 60 pieces of antenna



CAUTION:

- (1) Do not apply excess mechanical stress to the component body or terminations. Do not attempt to re-form or bend the components as this will cause damage to the component.
- (2) Do not expose the component to open flame.
- (3) This specification applies to the functionality of the component as a single unit. Please insure the component is thoroughly evaluated in the application circuit.

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 10.23.14**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com