CTMPC080605F Series From 0.24 µH to 2.2 µH



CHARACTERISTICS

Description: SMD Shielded Molded Power Inductor Applications: Smartphone, Tablet PC, Hard Disk for Ultrabook, LTE Module, Portable Devices, etc. Operating Temperature: -40°C to 125°C (including selftemperature rise) Inductance Tolerance: ±20% Testing: Inductance is tested on an E4991A/HP4287A+16197A, 2MHz, 0.2V. Packaging: Tape and Reel. Miscellaneous: RoHS Compliant. Additional Information: Additional electrical & physical information available upon request.


Samples available. See website for ordering information.

SPECIFICATIONS

Isat: DC current (A) that will cause L to drop approximately 30%. Irms: DC current (A) that will cause an approximate ΔT of 40°C.

Part Number	Inductance (µH)	L Test Freq. (MHz)	DCR Max. (mΩ)	Isat Max. (A)	Irms Max. (A)
CTMPC080605F-R24M	0.24	2.0	35	5.5	4.2
CTMPC080605F-R47M	0.47	2.0	52	3.8	3.2
CTMPC080605F-R68M	0.68	2.0	70	3.3	2.6
CTMPC080605F-1R0M	1.0	2.0	82	3.1	2.3
CTMPC080605F-1R5M	1.5	2.0	120	2.6	2.2
CTMPC080605F-2R2M	2.2	2.0	195	2.0	1.3

PHYSICAL DIMENSIONS						
Size	Α	В	С	D		
			Max.			
mm	2.0 ± 0.2	1.6 ± 0.2	1.2	0.5 ± 0.3		
inches	0.078 ± 0.008	0.063 ± 0.008	0.047	0.020 ± 0.012		



PAD LAYOUT

