

| IPSS SERIES

SEMI-FLUSH MOUNT PRESSURE TRANSMITTER



SPECIFICATIONS

Performance

The semi-flush mount pressure transmitter, IPSS, has a piezo-resistive silicon or ceramic pressure sensor. The sensor is semi-flush to the housing making this product ideal for viscous or paste like media. The sensor and housing are made from stainless steel with a choice of internal 'O' ring seals to ensure the product is suitable for a wide range of applications.

The electronics incorporate a microprocessor-based amplifier, requiring no adjusting and giving stable electronics - especially in high vibration or shock applications.

Every device is temperature compensated, calibrated and supplied with a traceable serial number and calibration data.*

*Calibration data is supplied as a sticker affixed to the product packaging - do not discard.

Features

- Piezo-resistive sensor, Ceramic
- Accuracy <±0.25% FS BFSL
- mA output available
- Pressure ranges from -1 Bar to +19Bars
- Pressure reference, Gauge or Absolute
- 3/4" BSP Pressure port connection

Suitable Applications

- Environmental engineering
- Static tank level
- Viscous and paste-like media
- Composite manufacturing
- Process control
- Automotive testing
- Process pumping
- Sewage or grey water
- Injection moulding or infusion
- Aggressive media

Accuracy (Non-linearity & Hysteresis)	<±0.25% / FS (BFSL)		
Setting Errors (Offsets)	2-wire Zero & Full Scale, <±0.5% / FS		
Permissible Load	2-wire $R_{max} = [(VS-VSmin)/0.02] \Omega$		
Influence Effects	Supply	<0.005% FS / 1V	
	Load	0.05% FSO / kΩ	

Material

Housing	303 Stainless Steel		
"O" Ring Seals	Viton		
Diaphragm	316L Stainless Steel or Ceramic		
Media Wetted Parts	Housing & process connection, 'O' ring seal, diaphragm		

Miscellaneous

Current Consumption	2-wire Limits at 28mA	
Weight	Approx 100g	
Installation Position	Any, small zero shift when tilted through 90° for silicon	
Operation Life	> 100 x 10 ⁶ cycles	
Insulation Resistance	> 50MOhms at 50Vdc	

Electrical Protection

Supply Reverse Polarity	No damage/no function	
Electromagnetic Compatibility	CE EMC directive · EN 61326-1:2013	

Environmental Conditions

Shock	100g / 11s
Vibration	10g RMS (20 - 2000Hz)
Media Temperature	-40°C to +125°C
Ambient Temperature	-20°C to +80°C
Storage Temperature	-40°C to +125°C
Humidity	5% to 95% RH non-condensing

Temperature & Thermal Effects

Compensated Temperature	+20°C to +80°C
Thermal Zero Shift (TZS)	<±0.04% /FS/°C
Thermal Span Shift (TSS)	<-0.015% /°C

• PRESSURE RANGES


Input Pressure Ranges

Nominal Pressure, Gauge	Bar	2	5	
Nominal Pressure Absolute	Bar	2		
Nominal Pressure Compound	Bar		-1 to +5	-1 to +19
Permissible Overpressure	Bar	4	10	35

Output Signal & Supply Voltage

Wiring Designation

Wire System	Output	Supply Volts	Connection	Pin No. (M12 4-pin connector)
2-wire 4 -	4 - 20mA	9 – 32V dc	+ve Supply	Pin 1
			-ve Supply	Pin 2
			Ground	Pin 3




	_		_
Part No	Sensor type	Pressure Range	Output
IPSS-G2000-5C	Ceramic	0-2 Bar G (0-29psi)	4-20mA
IPSS-G5000-5C	Ceramic	0-5 Bar G (0-73psi)	4-20mA
IPSS-GM1P5-5C	Ceramic	-1 to +5 Bar G (-14.5 to +73psi)	4-20mA
IPSS-C0072-5C	Ceramic	-1 to +19 Bar G (-14.5 to +276psi)	4-20mA
IPSS-A2000-5C	Ceramic	0-2 Bar Abs (0-29psiA)	4-20mA



DIMENSIONS

All dimensions are in millimeters.



Page 3

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEROF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

+44 (0)1202 897969 c3w_sales@sensata.com Cynergy3 Components Ltd. 7 Cobham Road, Ferndown Industrial Estate, Wimborne, Dorset, BH21 7PE, United Kingdom