LOW VOLTAGE C-MOS OPERATIONAL AMPLIFIER

GENERAL DESCRIPTION

The NJU7021,22 and 24 are single, dual and quad C-MOS Operational Amplifiers operated on a single-power-supply, low voltage and low operating current.

The minimum operating voltage is 3V and the output stage permits output signals to swing between both of the supply rails.

The input bias current is as low as less than 1pA,consequently the very small signal around the ground level can be amplified.

Furthermore, the operating current is also as low as $150\mu A$ (typ) per circuit, therefore it can be applied especially to battery operated items.

(V_{DD}=3~16V)

(150µA/circuit)

(I_{IB}=1pA typ.)

FEATURES


- Single-Power-Supply
- Wide Operating Voltage
- Wide Output Swing Range
- Low Operating Current
- Low Bias Current
- Internal Compensation Capacitor
- External Offset Null Adjustment (Only NJU7021)
- Package Outline

DMP/SSOP8 (NJU7021) DIP/DMP8 (NJU7022) DIP/DMP/SSOP14 (NJU7024)


(V_{OM}=9.98V typ. @V_{DD}=10V)

C-MOS Technology

■ PIN CONFIGURATION








NJU7021V

NJU7024V

NJU7021/22/24

EQUIVALENT CIRCUIT



* IN1,IN2 are only for NJU7021 (NJU7022/24 don't have these terminals).

■ ABSOLUTE MAXIMUM RATINGS


			(Ta=25°C)
PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V _{DD}	18	V
Differential Input Voltage	VID	±18 (note1)	V
Common Mode Input Voltage	V _{IC}	-0.3~18	V
Power Dissipation	P _D	(DIP14)700 (DIP8)500 (DMP8,14)300 (SSOP14)300 (SSOP8)250	mW
Operating Temperature Range	T _{opr}	-20~+75	°C
Storage Temperature Range	T _{stg}	-40~+125	D°

(note1) For supply voltage less than 18V, the absolute maximum input voltage is equal to the supply voltage.


■ ELECTRICAL CHARACTERISTICS


				(Ta=25°C,V _{DD} =10V,R _L =∞)		
PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Input Offset Voltage	V _{IO}	R _s =50Ω	-	-	10	mV
Input Offset Current	lio		-	1	-	pА
Input Bias Current	I _{IB}		-	1	-	pА
Input Impedance	R _{IN}		-	1	-	ΤΩ
Large Signal Voltage Gain	Av		80	95	-	dB
Input Common Mode Voltage Range	VICM		0~9	-	-	V
Maximum Output Swing Voltage	Vom	R _L =1MΩ	9.80	9.98	-	V
Common Mode Rejection Ratio	CMR		60	75	-	dB
Supply Voltage Rejection Ratio	SVR		60	75	-	dB
Operating Current/Circuit	I _{DD}		-	150	300	μA
Slew Rate	SR		-	0.40	-	V/µs
Unity Gain Bandwidth	Ft	A _V =40dB,C _L =10pF	-	0.4	-	MHz


■ OFFSET ADJUSTMENT CIRCUIT (Only For NJU7021)




■ TYPICAL CHARACTERISTICS











Output Voltage vs. Output Current













NJU7021/22/24

TYPICAL CHARACTERISTICS



Equivalent Input Noise Voltage vs. Frequency



[CAUTION] The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.