

Wideband, Fast Settling, Unity Gain Stable, Video Operational Amplifier

July 1994

Features

- This Circuit Is Processed in Accordance to MIL-STD-883 and Is Fully Conformant Under the Provisions of Paragraph 1.2.1
- Low AC Variability Over Process and Temperature
- Low Supply Current..... 11mA (Max)
- Unity Gain Bandwidth 50MHz (Typ)
- High Slew Rate..... 290V/ μ s (Typ)
- Low Offset Voltage..... 1mV (Typ)
- Full Power Bandwidth 4.6MHz (Typ)
- Low Differential Gain/Phase 0.03%/0.03° (Typ)

Applications

- Pulse and Video Amplifiers
- Wideband Amplifiers
- Fast Sample and Hold Circuits
- Fast, Precise D/A Converters
- High Speed A/D Input Buffer

Description

The HA-2841/883 is a wideband, unity gain stable, operational amplifier featuring a 50MHz unity gain bandwidth, and excellent DC specifications. This amplifier's performance is further enhanced through stable operation down to closed loop gains of +1, the inclusion of offset null controls, and by its excellent video performance.

The capabilities of the HA-2841/883 are ideally suited for high speed pulse and video amplifier circuits, where high slew rates and wide bandwidth are required. Gain flatness of 0.05dB, combined with differential gain and phase specifications of 0.03%, and 0.03 degrees, respectively, make the HA-2841/883 ideal for component and composite video applications.

A zener/nichrome based reference circuit, coupled with advanced laser trimming techniques, yields a supply current with a low temperature coefficient and low lot-to-lot variability. Tighter I_{cc} control translates to more consistent AC parameters ensuring that units from each lot perform the same way, and easing the task of designing systems for wide temperature ranges.



3

 OPERATIONAL
AMPLIFIERS

Ordering Information

PART NUMBER	TEMPERATURE RANGE	PACKAGE
HA1-2841/883	-55°C to +125°C	14 Lead CerDIP
HA7-2841/883	-55°C to +125°C	8 Lead CerDIP

Pinouts

 HA-2841/883
 (CERDIP)
 TOP VIEW

 HA-2841/883
 (CERDIP)
 TOP VIEW


NOTE: (NC) No Connection pins may be tied to a ground plane for better isolation and heat dissipation.

Absolute Maximum Ratings

Voltage between V+ and V- Terminals.....	+35V
Differential Input Voltage	6V
Voltage at Either Input Terminal.....	V+ to V-
Peak Output Current (<10% Duty Cycle).....	50mA
Junction Temperature (T _J).....	+175°C
Storage Temperature Range.....	-65°C to +150°C
ESD Rating.....	<2000V
Lead Temperature (Soldering 10s).....	+300°C

Thermal Information

	θ _{JA}	θ _{JC}
14 Pin CerDIP Package.....	73°C/W	18°C/W
8 Pin CerDIP Package.....	110°C/W	27°C/W
Package Power Dissipation Limit at +75°C for T _J ≤ +175°C		
14 Pin CerDIP Package.....	1.05W	
8 Pin CerDIP Package.....	0.9W	
Package Power Dissipation Derating Factor Above +75°C		
14 Pin CerDIP Package.....	10.5mW/°C	
8 Pin CerDIP Package.....	9mW/°C	

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Operating Conditions

Operating Temperature Range.....	-55°C to +125°C	V _{INCM} ≤ 1/2(V+ - V-)
Operating Supply Voltage.....	±12V to ±15V	R _L ≥ 1kΩ

TABLE 1. DC ELECTRICAL PERFORMANCE CHARACTERISTICS

Device Tested at: V_{SUPPLY} = ±15V, R_{SOURCE} = 100Ω, R_{LOAD} = 100kΩ, V_{OUT} = 0V, Unless Otherwise Specified.

PARAMETERS	SYMBOL	CONDITIONS	GROUP A SUBGROUP	TEMPERATURE	LIMITS		UNITS
					MIN	MAX	
Input Offset Voltage	V _{IO}	V _{CM} = 0V	1	+25°C	-4	4	mV
			2, 3	+125°C, -55°C	-8	8	mV
Input Bias Current	+I _B	V _{CM} = 0V, +R _S = 1.1kΩ -R _S = 100Ω	1	+25°C	-10	10	μA
	+I _B	V _{CM} = 0V, +R _S = 100Ω -R _S = 1.1kΩ	2, 3	+125°C, -55°C	-20	20	μA
	-I _B	V _{CM} = 0V, +R _S = 100Ω -R _S = 1.1kΩ	1	+25°C	-10	10	μA
	-I _B	V _{CM} = 0V, +R _S = 1.1kΩ -R _S = 1.1kΩ	2, 3	+125°C, -55°C	-20	20	μA
Input Offset Current	I _{IO}	V _{CM} = 0V, +R _S = 1.1kΩ -R _S = 1.1kΩ	1	+25°C	-1	1	μA
	I _{IO}		2, 3	+125°C, -55°C	-2	2	μA
Common Mode Range	+CMR	V+ = 5V V- = -25V	1	+25°C	10	-	V
	+CMR		2, 3	+125°C, -55°C	10	-	V
	-CMR	V+ = 25V V- = -5V	1	+25°C	-	-10	V
	-CMR		2, 3	+125°C, -55°C	-	-10	V
Large Signal Voltage Gain	+A _{VOL}	V _{OUT} = 0V and +10V R _L = 1kΩ	4	+25°C	10	-	kV/V
	+A _{VOL}		5, 6	+125°C, -55°C	5	-	kV/V
	-A _{VOL}	V _{OUT} = 0V and -10V R _L = 1kΩ	4	+25°C	10	-	kV/V
	-A _{VOL}		5, 6	+125°C, -55°C	5	-	kV/V
Common Mode Rejection Ratio	+CMRR	ΔV _{CM} = 10V, V _{OUT} = -10V V+ = 5V, V- = -25V	1	+25°C	86	-	dB
	+CMRR		2, 3	+125°C, -55°C	80	-	dB
	-CMRR	ΔV _{CM} = -10V, V _{OUT} = 10V V+ = 25V, V- = -5V	1	+25°C	86	-	dB
	-CMRR		2, 3	+125°C, -55°C	80	-	dB

Specifications HA-2841/883

TABLE 1. DC ELECTRICAL PERFORMANCE CHARACTERISTICS (Continued)

Device Tested at: $V_{SUPPLY} = \pm 15V$, $R_{SOURCE} = 100\Omega$, $R_{LOAD} = 100k\Omega$, $V_{OUT} = 0V$, Unless Otherwise Specified.

PARAMETERS	SYMBOL	CONDITIONS	GROUP A SUBGROUP	TEMPERATURE	LIMITS		UNITS
					MIN	MAX	
Output Voltage Swing	$+V_{OUT}$	$R_L = 1k\Omega$	1	+25°C	10	-	V
			2, 3	+125°C, -55°C	10	-	V
	$-V_{OUT}$	$R_L = 1k\Omega$	1	+25°C	-	-10	V
			2, 3	+125°C, -55°C	-	-10	V
Output Current	$+I_{OUT}$	$V_{OUT} = -5V$, (Note 1)	1	+25°C	25	-	mA
			2, 3	+125°C, -55°C	15	-	mA
	$-I_{OUT}$	$V_{OUT} = 5V$, (Note 1)	1	+25°C	-	-25	mA
			2, 3	+125°C, -55°C	-	-15	mA
Quiescent Power Supply Current	$+I_{CC}$	$V_{OUT} = 0V$ $I_{OUT} = 0mA$	1	+25°C	-	11	mA
			2, 3	+125°C, -55°C	-	11	mA
	$-I_{CC}$	$V_{OUT} = 0V$ $I_{OUT} = 0mA$	1	+25°C	-11	-	mA
			2, 3	+125°C, -55°C	-11	-	mA
Power Supply Rejection Ratio	$+PSRR$	$\Delta V_{SUPPLY} = 10V$ $V_+ = 10V$, $V_- = -15V$ $V_+ = 20V$, $V_- = -15V$	1	+25°C	70	-	dB
			2, 3	+125°C, -55°C	70	-	dB
	$-PSRR$	$\Delta V_{SUPPLY} = 10V$ $V_+ = 15V$, $V_- = -10V$ $V_+ = 15V$, $V_- = -20V$	1	+25°C	70	-	dB
			2, 3	+125°C, -55°C	70	-	dB
Offset Voltage Adjustment	$+V_{IOAdj}$	(Note 2)	1	+25°C	$V_{IO^{-1}}$	-	mV
	$-V_{IOAdj}$	(Note 2)	1	+25°C	$V_{IO^{+1}}$	-	mV

NOTES:

1. The output metal is sized to handle $I_{OUT} = 10mA$ at a 50% duty cycle, for $T_J = +175^{\circ}C$. For $I_{OUT} = 15mA$ and $T_J = +175^{\circ}C$, a duty cycle $\leq 33\%$ is required.
2. Offset Adjustment range is $|V_{IO} \text{ (measured)} \pm 1mV|$ minimum referred to output. This test is for functionality only, to assure adjustment through 0V.

TABLE 2. AC ELECTRICAL PERFORMANCE CHARACTERISTICS

Table 2 Intentionally Left Blank. See A.C. Specifications in Table 3

Specifications HA-2841/883

TABLE 3. ELECTRICAL PERFORMANCE CHARACTERISTICS

Device Characterized at: $V_{SUPPLY} = \pm 15V$, $R_{SOURCE} = 50\Omega$, $R_{LOAD} = 1k\Omega$, $V_{OUT} = 0V$, $A_V = +1V/V$, Unless Otherwise Specified.

PARAMETERS	SYMBOL	CONDITIONS	NOTES	TEMPERATURE	LIMITS		UNITS
					MIN	MAX	
Gain Bandwidth Product	GBWP	$V_O = 200mV$, $f_O = 0.1MHz$	1	+25°C	42	-	MHz
		$V_O = 200mV$, $f_O = 10MHz$	1	+25°C	44	-	MHz
Slew Rate	SR	$V_O = -3V$ to $+3V$	1, 3	+25°C	200	-	V/ μ s
	SR	$V_O = -3V$ to $+3V$	1, 3	-55°C to +125°C	187	-	V/ μ s
Rise Time	T_R	$V_O = 0V$ to $+200mV$ $C_L < 10pF$	1, 3	+25°C	-	6	ns
			1, 3	-55°C to +125°C	-	6	ns
Fall Time	T_F	$V_O = 0V$ to $-200mV$ $C_L < 10pF$	1, 3	+25°C	-	5	ns
			1, 3	-55°C to +125°C	-	6	ns
Full Power Bandwidth	FPBW	$V_{PEAK} = +10V$	1, 2	+25°C	3.1	-	MHz
			1, 2	-55°C to +125°C	3.0	-	MHz
Overshoot	+OS	$V_O = 0V$ to $+200mV$	1	+25°C	-	60	%
			1	-55°C to +125°C	-	65	%
	-OS	$V_O = 0V$ to $-200mV$	1	+25°C	-	60	%
			1	-55°C to +125°C	-	70	%
Closed Loop Output Resistance	R_{OUT}	$A_V > +1$ $V_M = 10V$, $\Delta I = 9mA$	1	+25°C	-	1	Ω

NOTES:

1. Parameters listed in Table 3 are controlled via design or process parameters and are not directly tested at final production. These parameters are lab characterized upon initial design release, or upon design changes. These parameters are guaranteed by characterization based upon data from multiple production runs which reflect lot to lot and within lot variations.
2. Full Power Bandwidth guarantee based on Slew Rate measurement using $FPBW = \text{Slew Rate}/(2\pi V_{PEAK})$.
3. Measured between 10% and 90% points.

TABLE 4. ELECTRICAL TEST REQUIREMENTS

MIL-STD-883 TEST REQUIREMENTS	SUBGROUPS (SEE TABLE 1)
Interim Electrical Parameters (Pre Burn-In)	1
Final Electrical Test Parameters	1 (Note 1), 2, 3, 4, 5, 6
Group A Test Requirements	1, 2, 3, 4, 5, 6
Groups C & D Endpoints	1

NOTE:

1. PDA applies to Subgroup 1 only.

Die Characteristics**DIE DIMENSIONS:**

77 x 81 x 19 mils \pm 1 mils
 1960 x 2060 x 483 μ m \pm 25.4 μ m

METALLIZATION:

Type: Al, 1% Cu
 Thickness: 16k \AA \pm 2k \AA

GLASSIVATION:

Type: Nitride over Silox
 Silox Thickness: 12k \AA \pm 2k \AA
 Nitride thickness: 3.5k \AA \pm 1k \AA

WORST CASE CURRENT DENSITY:

1.2 x 10⁵ A/cm² at 9.7mA


SUBSTRATE POTENTIAL (Powered Up): V-

TRANSISTOR COUNT: 43

PROCESS: Bipolar Dielectric Isolation

Metalization Mask Layout

HA-2841/883



3

OPERATIONAL AMPLIFIERS