SINGLE-SUPPLY QUAD OPERATIONAL AMPLIFIER

GENERAL DESCRIPTION

The NJM3403A is high performance ground sensing quad operational amplifier featuring the high slew rate and no crossover distortion.

(+4V~+36V)

(1.2V/µs typ.)

DIP14,DMP14,SSOP14


(3mA typ.)

The NJM3403A is improved version of the NJM2902.


FEATURES

- Single Supply
- Operating Voltage
- Low Operating Current
- Slew Rate
- Package Outline
- Bipolar Technology

■ PIN CONFIGURATION



■ EQUIVALENT CIRCUIT (1/4 Shown)



PACKAGE OUTLINE





NJM3403AD

NJM3403AM



NJM3403AV

■ ABSOLUTE MAXIMUM RATINGS

			(Ta=25°C)
PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	$V^{+}(V^{+}/V^{-})$	36 (or ±18)	V
Differential Input Voltage	VID	36	V
Input Voltage	VIC	-0.3~+36	V
Power Dissipation	PD	(DIP14) 500 (DMP14) 300	mW
Operating Temperature Range	T _{opr}	(SSOP14) 300 -40~+85	°C
Storage Temperature Range	T _{stg}	-40~+125	°C


■ ELECTRICAL CHARACTERISTICS

				$(1a=25 \text{ C}, \text{V} / \text{V} = \pm 15 \text{V})$		
PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Input Offset Voltage	V _{IO}	R _s =0Ω	-	2	5	mV
Input Offset Current	lio		-	5	50	nA
Input Bias Current	I _B		-	70	200	nA
Large Signal Voltage Gain	Av	R _L >2kΩ	88	100	-	dB
Maximum Output Voltage Swing	Vom	R _L =2kΩ	± 13	± 14	-	V
Input Common Mode Voltage Range	VICM		-15~+13	-	-	V
Common Mode Rejection Ratio	CMR	DC	70	90	-	dB
Supply Voltage Rejection Ratio	SVR		80	94	-	dB
Output Source Current	ISOURCE	V _{IN} ⁺ =1V,V _{IN} ⁻ =0V	20	30	-	mA
Output Sink Current	Isink	V _{IN} ⁺ =0V,V _{IN} ⁻ =1V	10	20	-	mA
Channel Separation	CS	f=1k~20kHz Input Referred	-	120	-	dB
Operating Current	lcc	R _L =∞	-	3	5	mA
Slew Rate	SR		-	1.2	-	V/µs
Unity Gain Bandwidth	f _T		-	1.2	-	MHz
Total Harmonic Distortion	THD	f=20kHz,V ₀ =10V _{PP}	-	1	-	%


(Ta=25°C,V⁺/V⁻=±15V)


Maximum Output


■ TYPICAL CHARACTERISTICS





Equivalent Input Noise Voltage vs. Frequency


















New Japan Radio Co., Ltd.


TYPICAL CHARACTERISTICS













Slew Rate vs. Temperatute $(V^{+}/V^{-} = \pm 15V, R_{L} = 2 k\Omega)$ 1.8 1.6 Rate 1.4 1.2 Slew J 1.0 0.8 SR 0.6 $(V/\mu S)0.4$ 0.2 0 - 25 - Š0 25 0 50 75 100 125 Ambient Temperature Ta (°C)

■ TYPICAL CHARACTERISTICS



Crossover Distortion

Photos (1) and (2) show the output waveforms of NJM3403A and operational amplifier having crossover distortion. The NJM3403A eliminates the crossover distortion through the A,B class output stage as shown in the photo. NJM3403A IC has realized a wide band and a high slew rate in addition to the low distortion.



(1) NJM3403A Output Waveform

(2) Crossover Distortion Example

 $f\!=\!1kHz,~R_L\!=\!2k\Omega,~Vertical~Axis:~2V/div$

[CAUTION]

The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right induding the industrial rights.

New Japan Radio Co., Ltd.