

#### **DATASHEET**

# Chip Infrared LED With Right Angle Lens IR12-21C/TR8



#### **Features**

- Small double-end package
- Low forward voltage
- Good spectral matching to Si photo detector
- Pb free
- The product itself will remain within RoHS compliant version
- Compliance with EU REACH

## **Descriptions**

- IR12-21C/TR8 is an infrared emitting diode in miniature SMD package which is molded in a water clear plastic with right angle lens
- The device is spectrally matched with silicon photodiode and phototransistor

## **Applications**

- PCB mounted infrared sensor
- Infrared emitting for miniature light barrier
- Floppy disk drive
- · Optoelectronic switch
- Smoke detector

#### **Device Selection Guide**


Part Category	Chip Material	Lens Color
IR	GaAlAs	Water Clear


ч

**Expired Period: Forever** 

LifecyclePhase: Approved


## **Package Dimensions**







**Polarity** 

- Anode
- Calthode



For reflow soldering(propose)





Notes: 1.All dimensions are in millimeters

- 2. Tolerances unless dimensions ±0.1mm
- 3. Suggested pad dimension is just for reference only Please modify the pad dimension based on individual need

Absolute Maximum Ratings (Ta=25)

Parameter	Symbol	Rating	Units	
Continuous Forward Current	l <sub>F</sub>	65	mA	
Reverse Voltage	$V_{R}$	5	V	
Operating Temperature	$T_{opr}$	-25 ~ +85		
Storage Temperature	$T_{stg}$	-40 ~ +85		
Soldering Temperature*1	T <sub>sol</sub>	260		
Power Dissipation at (or below) 25 Free Air Temperature	$P_d$	130	mW	

Notes: \*1: Soldering time 5 seconds

Electro-Optical Characteristics (Ta=25)

Electro-Optical Characteristics (Ta=25)								
Parameter	Symbol	Condition	Min.	Тур.	Max.	Units		
Radiant Intensity	le		0.5	0.8	1	mW/sr		
Peak Wavelength	λр			940		nm		
Spectral Bandwidth	Δλ	I <sub>F</sub> =20mA	-	45		nm		
Forward Voltage	V <sub>F</sub>			1.2	1.5	V		
View Angle	201/2			150		deg		
Reverse Current	I <sub>R</sub>	V <sub>R</sub> =5V			10	μA		

**Expired Period: Forever** 

LifecyclePhase: Approved

# **EVERLIGHT**

## **Typical Electro-Optical Characteristics Curves**

Fig.1 Forward Current vs.

Ambient Temperature




Fig.2 Spectral Distribution





Fig.3 Forward Current vs. Forward Voltage

10<sup>4</sup> tp=100μs tp/T=0.01 10<sup>2</sup> 10<sup>1</sup> 0 1 2 3 4 Forward Voltage (V)

Fig.4 Radiant Intensity vs.
Forward Current




LifecyclePhase: Approved



## **Typical Electro-Optical Characteristics Curves**

Fig.5 Relative Radiant Intensity vs. Angular Displacement



LifecyclePhase:



#### **Precautions For Use**

#### 1. Over-current-proof


Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

#### 2. Storage

- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package, the LEDs should be kept at 10 ~30 and 90%RH or less.
- 2.3 The LEDs suggested be used within one year.
- 2.4 After opening the package, the devices must be stored at 10 ~30 and ≤ 60%RH, and used within 168 hours (floor life). If unused LEDs remain, it should be stored in moisture proof packages.
- 2.5 If the moisture absorbent material (desiccant material) has faded or unopened bag has exceeded the shelf life or devices (out of bag) have exceeded the floor life, baking treatment is required.
- 2.6 If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure or recommend the following conditions:
  - 96 hours at 60  $\pm$  5 and < 5 % RH (reeled/tubed/loose units).

#### 3. Soldering Condition

3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times
- 3.3 When soldering, do not put stress on the LEDs during heating
- 3.4 After soldering, do not warp the circuit board

Approved


# **EVERLIGHT**

#### 4. Soldering Iron


Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

#### 5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.




## **Package Dimensions**



Note: The tolerances unless mentioned are ±0.1mm, unit: mm


# Carrier Taping Dimensions: (Quantity: 2000PCS/Reel)



Note: The tolerances unless mentioned are ±0.1mm, unit: mm

## **EVERLIGHT**

### **Label Form Specification**



CPN: Customer's Production Number

P/N: Production Number LOT No: Lot Number

QTY: Packing Quantity **HUE: Peak Wavelength** 

CAT: Ranks

**REF: Reference** MSL-X: MSL Level

Made In: Manufacture place

#### **Notes**

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 3. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 4. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.
- 5. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No. 6-8, Zhonghua Rd., Shulin Dist.,

New Taipei City 23860, Taiwan

Tel: 886-2-2685-6688 Fax: 886-2685-2699, 6897 http://www.everlight.com