



## Multilayer Balun

For 1920-2170MHz

## HHM1506

2.0×1.25mm [EIA 0805]\*

\* Dimensions Code JIS[EIA]



# The products in this catalog will be or have been stopped production

Discontinue Issue Date	Jun. 3, 2022
Last Purchase Order Date	Mar. 31, 2023
Last Shipment Date	Mar. 31, 2024

Please refer to our Web site about replacement information.




## **Multilayer Balun**


For 1920-2170MHz

## HHM1506


#### **Conformity to RoHS Directive**

#### SHAPES AND DIMENSIONS





#### ■ RECOMMENDED LAND PATTERN



RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/

<sup>•</sup> All specifications are subject to change without notice.

<sup>•</sup> Before using these products, be sure to request the delivery specifications.



## HHM1506

#### **ELECTRICAL CHARACTERISTICS**

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Unbalanced Port Characteristic Impedance (Ω)			50 (Nominal	
Balanced Port Characteristic Impedance (Ω)			100 (Nomina	al)
Return Loss at Unbalanced Port (dB)	1920 to 1980	10	_ (7	
Tietuiii Loss at Olibalanceu i Ort (ub)	2110 to 2170	10		<del>-</del>
Phase Balance (deg.)	1920 to 1980	170		190
Thase balance (deg.)	2110 to 2170	170		190
Amplitude Balance (dB)	1920 to 1980	-2.0		2.0
Amplitude Balance (db)	2110 to 2170	-2.0	2.0	2.0
Insertion Loss (dP)	1920 to 1980			1.0
Insertion Loss (dB)	2110 to 2170	<u> </u>		1.0

#### ■TEMPERATURE RANGE

Operating temperature	Storage temperature
(°C)	(°C)
-40 to ±85	_40 to ±85




All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.




### HHM1506

#### FREQUENCY CHARACTERISTICS


#### □INSERTION LOSS 0.0 0.5 1.0 1.5 2.0 2.5 3.0 3.5 4.0 4.5 5.0 L 1700 1800 2100 2200 2000 Frequency(MHz)



#### □RETURN LOSS




#### **□PHASE BALANCE**



<sup>•</sup> All specifications are subject to change without notice.

<sup>•</sup> Before using these products, be sure to request the delivery specifications.

#### ■ RECOMMENDED REFLOW PROFILE



Preheating		Soldering				
		Critical zone (T3 to T4)		Peak		
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	Т3	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120s	sec 240 to 260°C	30sec max.

\*t3: Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

- All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

#### REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

#### SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

#### **⚠** REMINDERS

The products listed on this catalog are intended for use in general electronic equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.