

1241380-2 ✓ ACTIVE

AMP | AMP MCP Connector System

TE Internal #: 1241380-2

Automotive Terminals, Receptacle, Mating Tab Width 1.5 mm [.059 in], Tab Thickness .6 mm [.024 in], 20 – 17 AWG Wire Size, AMP MCP Connector System

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > AMP MCP, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: 1.5 mm [.059 in]

Mating Tab Thickness: .6 mm [.024 in]

Terminal Transmits: 0 – 24 A (Low Power)

Wire Size: 20 – 17 AWG

[All AMP MCP, RECEPTACLE AND TAB \(124\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	Yes
Primary Locking Feature	Locking Lance

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Contact Size	1.5K
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	12 A
Crimp Type	F-Crimp
Terminal Type	Receptacle



Mating Tab Width	1.5 mm[.059 in]
Mating Tab Thickness	.6 mm[.024 in]
Interface Plating	Gold (Au)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.4 – 2.1 mm[.055 – .083 in]
Wire Size	.5 – 1 mm ²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F][302 °F]
Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]

Operation/Application

Conforms to KOMAX Automatic Component Insertion Guideline	Yes, per Version 5.0 (March 2018)
Compatible With Wire Base Material	Copper

Industry Standards

Compatible With Agency/Standards Products	LV214
---	-------

Packaging Features

Packaging Quantity	4500
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-H3399-CH8172 Heavy Duty Sealed Connector Series Housings</p>	 <p>TE Part # CAT-L489-CH8172 LEAVYSEAL Housings</p>	 <p>TE Part # 1-1579007-1 EXTRACTION TOOL</p>	 <p>TE Part # 964972-1 EINZELLEITERDICHTNG</p>
 <p>TE Part # 963530-1 EINZELLEITERDICHTNG</p>	 <p>TE Part # 2306960-1 3POS,AMP MCP 1.5K,REC HSG ASSY, SLD,COD A</p>	 <p>TE Part # CAT-AM705-CH8172 AMP MCP, SEALED CONNECTOR HOUSING</p>	 <p>TE Part # 1-2293551-1 62POS,MIXED,REC HSG,ASSY,SLD</p>




TE Part # 1579008-9
INSERTION TOOL



TE Part # 2-2293551-1
62POS, MIXED, REC HSG, ASSY, SLD



TE Part # 2063524-1
SDE MCP1.5 0.2-1.0mm2 ASSY



TE Part # 2063524-2
SDE MCP1.5 0.2-1.0mm2 DIE SET



TE Part # 2151064-1
OCEAN_2.0 APPLICATOR-S-070F125O



TE Part # 2151064-2
OCEAN_2.0 APPLICATOR-S-070F125O



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 3-2293551-1
62POS, MIXED, REC HSG, ASSY, SLD



TE Part # 5-2151064-1
OCEAN_2.0 APPLICATOR-S-070F125O



TE Part # 5-2151064-2
OCEAN_2.0 APPLICATOR-S-070F125O




TE Part # 7-2151064-1
OCEAN_2.0 APPLICATOR-S-070F125O




TE Part # 7-2151064-2
OCEAN_2.0 APPLICATOR-S-070F125O


Also in the Series | AMP MCP Connector System




Automotive Connector Caps & Covers (22)




Automotive Connector Locks & Position Assurance (6)




Automotive Housings (332)




Automotive Terminals (130)



Connector Seals & Cavity Plugs (7)



Insertion & Extraction Tools (13)





Other Automotive Connector Accessories (2)



PCB Headers & Receptacles (28)

Customers Also Bought



Documents

Product Drawings

AMP MCP 1.5K, CONTACT, SWS

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1241380-2_B_c-1241380-2-b.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1241380-2_B_c-1241380-2-b.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1241380-2_B_c-1241380-2-b.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[HDSCS CAN Bus Y-Connector and 120 Resistor Brochure](#)

English

[HDSCS Catalog](#)

English

[CONNECTOR SELECTOR](#)

English

[Product Specifications](#)

[Application Specification](#)

German

[Application Specification](#)

English