

HCSA1V1008

Automotive grade dual winding high current inductor



Product features

- AEC-Q200 qualified
- Magnetically shielded, low EMI
- Robust molded construction
- Dual winding, ideal for SEPIC converters
- Inductance range from 10 μ H to 22 μ H
- Current range from 3.3 A to 11.2 A
- 11.35 mm x 10.3 mm footprint surface mount package in a 8.2 mm height
- Moisture sensitivity level (MSL): 1
- Alloy powder core material

Applications

- Body electronics
 - Heating ventilation and air conditioning controllers (HVAC)
 - Headlamps, tail lamps and interior lighting and LED lighting
 - Doors, window lift and seat control
- Advanced driver assistance systems
 - Basic and smart surround, and rear and front-view camera
 - Adaptive cruise control (ACC)
 - Collision avoidance system
 - Car black box system
- Infotainment and cluster electronics
 - Audio subsystem: head unit and trunk amp
 - Digital instrument cluster
 - In-vehicle infotainment (IVI) and navigation
- Engine and powertrain systems
 - Diesel/gasoline engine management
 - Powertrain control module (PCM)/ engine control unit (ECU)
 - Transmission control unit (TCU)

Environmental compliance and general specifications

- Storage temperature range (Component): -55 °C to +155 °C
- Operating temperature range: -55 °C to +155 °C (ambient plus self-temperature rise)




Product specifications

Part number ⁷	OCL ¹ (μH) $\pm 20\%$	FLL ² (μH) minimum	I_{rms}^3 (A) maximum	I_{sat}^4 (A) maximum	DCR ⁸ (m Ω) typical @ +20 °C	DCR ⁸ (m Ω) maximum @ +20 °C	Coupling coefficient (K)	SCL (μH) typical ⁵	SRF (MHz) typical	K-factor ⁶
HCSA1V1008-100-R	10	5.6	5.0	11.2	35.80	40.45	0.95	0.30	8.4	39
HCSA1V1008-150-R	15	8.4	3.8	9.1	58.37	65.96	0.95	0.35	7.0	29
HCSA1V1008-220-R	22	12.3	3.32	7.5	74.40	84.07	0.96	0.35	5.0	25


- Open Circuit Inductance (OCL) Test Parameters: 100 kHz, 0.25 V_{rms}, 0.0 Adc, +25 °C, pins (1 - 3), (2 - 4)
- Full Load Inductance (FLL) Test Parameters: 100 kHz, 0.25 V_{rms}, I_{rms}, +25 °C, pins (1 - 3), (2 - 4)
- I_{rms}: DC current for an approximate temperature rise of 30 °C without core loss. Derating is necessary for AC currents. PCB layout, trace thickness and width, air-flow, and proximity of other heat generating components will affect the temperature rise. It is recommended that the temperature of the part not exceed +155 °C under worst case operating conditions verified in the end application.
- I_{sat}: Peak current for approximately 30% rolloff @ +25 °C, pins: (1 - 3), (2 - 4)

- Short circuit inductance (SCL) test parameters: 100 kHz, 0.25 V_{rms}, 0.0 Adc, pins: (1 - 3) short pins (2 - 4)
- K-factor: Used to determine B_{pp} for core loss (see graph). B_{pp} = K * L * ΔI . B_{pp}: (Gauss), K: (K-factor from table), L: (Inductance in μH), ΔI (Peak to peak ripple current in Amps).
- Part Number Definition: HCSA1V1008-xxx-R
HCSA1V1008 = Product code and size
xxx= inductance value in μH , R= decimal point,
If no R is present then last character equals number of zeros
-R suffix = RoHS compliant
- DCR: +20 °C (pins (1-3), (2-4))


Dimensions- mm



Recommended pad layout



Schematic




Part number	A	B	C	D	E	F	G	H	I	J
HCSA1V1008-xxx-R	11 ± 0.35	10 ± 0.3	8.2 maximum	3.1 ± 0.3	2.4 ± 0.5	6.4 typical	1.6 ± 0.2	0.05-0.25	4.2 reference	4.2 reference

Part marking: xxx= inductance value in μH , R= decimal point, If no R is present then last character equals number of zeros
 yyyy= lot code
 All soldering surfaces to be coplanar within 0.1 millimeters
 Tolerances are ± 0.3 millimeters unless stated otherwise
 Pad layout tolerances are ± 0.1 millimeters unless stated otherwise
 DCR is measured from point "a" to point "b"
 Traces or vias underneath the inductor is not recommended

Packaging information- mm




Drawing not to scale

Supplied in tape and reel packaging, 400 parts per 13" diameter reel (EIA-481 compliant)






Dimension	Value
W	24 ± 0.3
F	11.50 ± 0.1
E1	1.75 ± 0.1
E2	22.25 min
P0	4.0 ± 0.1
P1	16.0 ± 0.1
P2	2.0 ± 0.05
D0	1.5 +0.1 -0
D1	1.5 +0.1 -0
A0	10.7 ± 0.1
B0	11.65 ± 0.1
K0	8.50 ± 0.1
T	0.5 ± 0.05




Core loss vs B_{p-p} (per winding)



Inductance and impedance vs. frequency (per winding)



Inductance and temperature rise vs. current (per winding)



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T _{smin})	100 °C	150 °C
• Temperature max. (T _{smax})	150 °C	200 °C
• Time (T _{smin} to T _{smax}) (t _s)	60-120 seconds	60-120 seconds
Ramp up rate T _L to T _p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T _L)	183 °C	217 °C
Time (t _L) maintained above T _L	60-150 seconds	60-150 seconds
Peak package body temperature (T _p)*	Table 1	Table 2
Time (t _p)* within 5 °C of the specified classification temperature (T _C)	20 seconds*	30 seconds*
Ramp-down rate (T _p to T _L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2023 Eaton
All Rights Reserved
Printed in USA
Publication No. ELX1085
September 2023

Eaton is a registered trademark.
All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

