

1326133-1 ✓ ACTIVE

AMP 0.64 Connector System


TE Internal #: 1326133-1

Housing for Female Terminals, Wire-to-Wire, 18 Position, .1 in [2.54 mm] Centerline, Black, Cable Mount (Free-Hanging), AMP 0.64 Connector System

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Wire**

Number of Positions: **18**

Connector & Housing Type: **Housing for Female Terminals**

Centerline (Pitch): **2.54 mm [.1 in]**

Sealable: **No**

### Features

#### Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	No

#### Configuration Features

Number of Positions	18
Number of Rows	2

#### Body Features

Primary Product Color	Black
-----------------------	-------

#### Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

#### Housing Features

Housing Material	Glass Filled Nylon
------------------	--------------------



Centerline (Pitch) 2.54 mm[.1 in]

**Dimensions**

Connector Height	20.4 mm[.803 in]
Product Width	7.9 mm[.311 in]
Product Length	23.7 mm[.933 in]
Row-to-Row Spacing	5.9 mm[.232 in]

**Industry Standards**

UL Flammability Rating	UL 94HB
------------------------	---------

**Packaging Features**

Packaging Quantity	50
Packaging Method	Package

**Other**

Serviceable	No
Connector Position Assurance Capable	No

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # 1326132-1  
18WAY LAC SHIELD ASSEMBLY 70 D

TE Part # 638551-3  
CONTACT,FEMALE,0.64MM,SN,18-20

TE Part # 1326028-3  
0.64MM FEMALE CONTACT,AU,18-20

TE Part # 1326028-5  
.64MM FEM CONT,AU,18-20,FORMED

TE Part # 638551-1  
CONTACT,FEMALE,0.64MM,SN,18-20

TE Part # 1326028-2  
0.64MM FEMALE CONTACT,AU,22AWG

TE Part # 638551-4  
CONTACT,FEMALE,0.64MM,SN,22

TE Part # 1326028-1  
0.64MM FEMALE CONTACT,AU,18-20

TE Part # 638551-2  
CONTACT,FEMALE,0.64MM,SN,22

TE Part # 1326028-4  
0.64MM FEMALE CONTACT,AU,22AWG

TE Part # 1326028-6  
0.64MM FEMALE CONTACT,AU,22AWG

TE Part # 1326132-4  
18WAY LAC SHIELD ASSEMBLY 70 D

## Also in the Series | AMP 0.64 Connector System

Automotive Connector Caps & Covers (17)


Automotive Housings(25)

Automotive Terminals(14)

Insertion & Extraction Tools(1)



Other Automotive Connector Accessories(2)



PCB Headers & Receptacles(30)

## Customers Also Bought



TE Part #1326362-1  
26WAY LAC "COMMON" SHIELD ASMB



TE Part #1719957-1  
GET 0.64 TERMINAL WIRE SIZE 0.



TE Part #2035363-5  
1X6 GENERATION Y ASSY KEY D



TE Part #1924900-1  
Assy, Plug, 30p Hybrid Key A



TE Part #2098216-1  
32P Carrier, GY



TE Part #2035360-1  
1X4 GENERATION Y ASSY KEY A



TE Part #2035363-7  
1X6 GENERATION Y ASSY KEY E



TE Part #2288274-2  
24P HYBRID 0.64/2.8 PLUG ASSY, B KEY



TE Part #9-2177796-1  
O-RING,4x1.5



TE Part #9-2208798-5  
6POS,0.64 GENER. Y,REC HSG,ASSY

## Documents

### Product Drawings

[RECEPTACLE HOUSING, 18 POSITIO](#)

English

### CAD Files

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_1326133-1\\_B.2d\\_dxf.zip](#)

English

[3D PDF](#)



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1326133-1\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1326133-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English