

MDR-131-1 ✓ ACTIVE

CII | CII MDR Series

TE Internal #: 1393139-2

Power Relays, Rotary, Non-Latching, .06 VA Coil Power Rating AC, 115 VAC Coil Voltage, 4 Form C, 4PDT, 4 C/O, CII MDR Series

[View on TE.com >](#)



Relays & Contactors > Relays > Power Relays



Power Relay Type: **Rotary**

Coil Magnetic System: **Non-Latching**

Coil Power Rating AC: **.06 VA**

Coil Voltage Rating: **115 VAC**

Contact Arrangement: **4 Form C, 4PDT, 4 C/O**

Features

Product Type Features

Power Relay Type	Rotary
------------------	--------

Electrical Characteristics

Coil Power Rating	6.5 W
Coil Current	.215 A
Insulation Initial Dielectric Between Contacts & Coil	1230 V
Actuating System	AC
Input Voltage	115 VAC
Coil Magnetic System	Non-Latching
Coil Power Rating AC	.06 VA
Coil Voltage Rating	115 VAC
Contact Voltage Rating	115 VAC

Contact Features

Contact Arrangement	4 Form C, 4PDT, 4 C/O
Contact Current Rating (Max)	10 A
Contact Material	Silver Cadmium Oxide
Contact Number of Poles	4
Relay Terminal Type	Screw Terminals

Mechanical Attachment

Relay Mounting Type	Screw
---------------------	-------



Dimensions

Product Height	79.5 mm[3.13 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	0 – 65 °C
-----------------------------	-----------

Packaging Features

Packaging Method	Carton & Box
------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 1393139-4
MDR-134-1=MDR



TE Part # 1755066-1
MDR-7025=RLY,LTH,MED,28VDC,16PDT



TE Part # 1755088-1
MDR-142-1=MED,NL,125VDC,24PDT



TE Part # 9-1393139-9
MDR-7035=MDR

Also in the Series | CII MDR Series



Power Relays(31)

Customers Also Bought



TE Part #5413879-1
JACK ASSY,RTANG,BNC



TE Part #324159
TERM, RING, PIDG, 16-14, #4




TE Part #1616050-7
DHL31=RELAY




TE Part #1218124-4
37 POS,ASSY,PLUG,LOW PROF,109




TE Part #2560-220-2031
CONT PIN




TE Part #148510-1
2MMRS,ASY,072,R/A,HDR,PKG




TE Part #1616116-3
B4652=RELAY



TE Part #9-1616920-6
BH494C=CONTACTOR



TE Part #148376-1
2MM RS,072,RECEPTACLE ASSY



TE Part #1616004-1
B301EA=RELAY



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1393139-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393139-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393139-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec12_MDR](#)

English