SIEMENS

Data sheet

US2:17EUE92WS



Non-reversing motor starter, Size 1 3/4, Three phase full voltage, Solidstate overload relay, OLR amp range 10-40A, 24VDC coil, Combination type, 60A non-fusible disconnect, Encl NEMA type 4X 304 S-Steel, Water/dust tight noncorrosive, Standard width enclosure

Fi	gu	re	si	mi	ar
	-				

product brand name	Class 17 & 25		
design of the product	Full-voltage non-reversing motor starter with non-fusible disconnect		
special product feature	ESP200 overload relay; Half-size controller		
General technical data			
Height x Width x Depth [in]	24 × 11 × 8 in		
touch protection against electrical shock	(NA for enclosed products)		
installation altitude [ft] at height above sea level maximum	6560 ft		
ambient temperature [°F]			
 during storage 	-22 +149 °F		
during operation	-4 +104 °F		
ambient temperature			
 during storage 	-30 +65 °C		
 during operation 	-20 +40 °C		
Horsepower ratings			
yielded mechanical performance [hp] for 3-phase AC			
motor			
at 200/208 V rated value	10 hp		
at 220/230 V rated value	10 hp		
• at 460/480 V rated value	15 hp		
at 575/600 V rated value	15 hp		
Contactor			
size of contactor	Controller half size 1 3/4		
number of NO contacts for main contacts	3		
operational current at AC at 600 V rated value	40 A		
mechanical service life (switching cycles) of the main contacts typical	1000000		
Auxiliary contact			
number of NC contacts at contactor for auxiliary contacts	0		
number of NO contacts at contactor for auxiliary contacts	1		
number of total auxiliary contacts maximum	8		
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)		
Coil			
type of voltage of the control supply voltage	DC		
control supply voltage			
at DC rated value	24 V		
holding power at AC minimum	0 W		
apparent pick-up power of magnet coil at AC	163 VA		
apparent holding power of magnet coil at AC	5.5 VA		

operating range factor control supply voltage rated value of magnet coil	0.85 1.1			
percental drop-out voltage of magnet coil related to the input voltage	25 %			
ON-delay time	21 21 ms			
OFF-delay time	11 11 ms			
Overload relay				
product function				
 overload protection 	Yes			
phase failure detection	Yes			
 asymmetry detection 	Yes			
ground fault detection	Yes			
• test function	Yes			
external reset	Yes			
reset function	Manual, automatic and remote			
trip class	CLASS 5 / 10 / 20 (factory set) / 30			
adjustable current response value current of the current-	10 40 A			
dependent overload release make time with automatic start after power failure	3 s			
maximum				
relative repeat accuracy	1 %			
product feature protective coating on printed-circuit board number of NC contacts of auxiliary contacts of overload	Yes 1			
relay				
number of NO contacts of auxiliary contacts of overload relay	1			
operational current of auxiliary contacts of overload relay				
• at AC at 600 V	5 A			
• at DC at 250 V	1 A			
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)			
insulation voltage (Ui)				
 with single-phase operation at AC rated value 	600 V			
 with multi-phase operation at AC rated value 	300 V			
Disconnect Switch				
response value of switch disconnector	60A / 600V			
design of fuse holder	non-fusible			
operating class of the fuse link	non-fusible			
Enclosure				
degree of protection NEMA rating	4X, 304 stainless steel			
design of the housing	dustproof, waterproof & resistant to corrosion			
Mounting/wiring				
mounting position	vertical			
fastening method	Surface mounting and installation			
type of electrical connection for supply voltage line-side	Box lug			
tightening torque [lbf·in] for supply	35 35 lbf·in			
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)			
temperature of the conductor for supply maximum permissible	75 °C			
material of the conductor for supply	AL or CU			
type of electrical connection for load-side outgoing feeder	Screw-type terminals			
tightening torque [lbf-in] for load-side outgoing feeder	45 45 lbf-in			
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2 AWG)			
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C			
material of the conductor for load-side outgoing feeder	AL or CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
con at AWO cables single of matt-stranded				

r-type terminals 15 lbf-in 2 AWG), 2x (16 14 AWG), 2x (18 16 AWG)
15 lbf·in 2 AWG), 2x (16 14 AWG), 2x (18 16 AWG)
15 lbf·in 2 AWG), 2x (16 14 AWG), 2x (18 16 AWG)
2 AWG), 2x (16 14 AWG), 2x (18 16 AWG)
-type terminals
-type terminals
-type terminals
0 lbf·in
9 14 AWG)
2600V (Class H or K); 100kA@600V (Class R or J)
A ICS 2; UL 508; CSA 22.2, No.14
<u>JS2:17EUE92WS</u> .) odels, device circuit diagrams, EPLAN macros,)

last modified:

1/25/2022 🖸