



VAL-U-LOK

TE Internal #: 1586316-4

Pin Contact, Gold, 600 VAC, 26 – 22 AWG Wire Size, .13 – .33 mm<sup>2</sup> Wire Size, Crimp, Phosphor Bronze, Power, -40 – 221 °F [-40 – 105 °C]

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Gold**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **600 VAC**

Contact Retention Within Housing: **With**

**Features**

**Electrical Characteristics**

Operating Voltage	600 VAC
-------------------	---------

**Contact Features**

Mating Square Post Dimension	1.14 mm[.045 in]
Contact Fabrication	Stamped & Formed
Contact Underplating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Type	Pin
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	With



Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	9 A

### Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

### Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

### Dimensions

Compatible Insulation Diameter Range	1.19 – 1.75 mm [.047 – .069 in]
Wire Size	.13 – .33 mm <sup>2</sup>

### Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Flammability Rating	UL 94V-0, UL 94V-2

### Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 91387-1  
PRO-CRIMPER TOOL & DIE




REPRESENTATION ONLY. DIE SET MAY VARY. TE

TE Part # 2394312-1  
SDE F PIN 22-26 ASSY



TE Part # 2394312-2  
SDE F PIN 22-26 DIE SET



TE Part # 91387-2  
PRO-CRIMPER DIE(ONLY)


### Customers Also Bought



TE Part #33476  
PIDG RECT 22-16COMM 22-18MIL 6



TE Part #204519-2  
AMPLIMITE,ASY,PLUG,STD,90,4



TE Part #1586106-3  
3P RCPT VAL-U-LOK SR V0



TE Part #1-1546670-2  
12P.437" DR BARRIER,W/BND SCRWB"




TE Part #1-1546670-4  
14P.437" DR BARRIER,W/BND SCRWB"





TE Part #1-1546670-8  
18P.437" DR BARRIER,W/BND SCRWB"



TE Part #204518-2  
RECEIPT ASSY,62 POSN,AMPLIMITE



TE Part #1586104-3  
3P PLUG VAL-U-LOK SR FH V0



## Documents

### Product Drawings

[VAL-U-LOK PIN PHBZ AU 26-22 LP](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_1586316-4\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1586316-4\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1586316-4\\_A.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_AND\\_SOCKET\\_CONNECTORS\\_CATALOG](#)

English

### Product Specifications

[Application Specification](#)

English