

15ACM 3 series

15W- Single Output AC-DC Converter - Universal Input - Isolated & Regulated



AC-DC Converter

15 Watt

- Universal Input:
 85 305VAC/100 430VDC
- Operating temperature range: -40°C to +85°C
- (Isolation voltage up to 3kVAC
- Low power consumption, green power
- Short circuit protection (SCP)
- Over voltage protection
- Over current protectionHigh power density,
- high reliability
- Designed to meet IEC/EN/ UL60335 safety standards
- Designed to meet IEC/EN/
 UL62368 safety standards

The 15ACM_S3 series s one of GAPTEC's highly efficient green power AC-DC Converter series. They feature ultra-wide input range accepting either AC or DC voltage, high efficiency, low power consumption and reinforced isolation. All models are particularly suitable for industrial control, electric power, instrumentation and smart home applications which have high requirement for dimension and don't have high requirement on EMC. For extremely harsh EMC environment, we recommend using the application circuit show in Design Reference of this datasheet.







| Approval | Model | Power [W] | Output voltage [V] | Output current [mA, max] | Efficiency [%, typ] | Capacitive load [μF, max] |
|----------|------------|--------------|-----------------------|--------------------------|------------------------|------------------------------|
| UL | 15ACM_03S3 | 9.9 | 3.3 | 3000 | 75 | 2000 |
| UL | 15ACM_05S3 | 14 | 5 | 2800 | 77 | 1500 |
| UL | 15ACM_09S3 | 15 | 9 | 1670 | 82 | 1000 |
| UL | 15ACM_12S3 | 15 | 12 | 1250 | 82 | 680 |
| UL | 15ACM_15S3 | 15 | 15 | 1000 | 84 | 470 |
| UL | 15ACM_24S3 | 15 | 24 | 625 | 85 | 330 |

Please add suffix /L for bent pins (15ACM 24S3/L).

| Input specifications | | | |
|---------------------------------|------------------------|-------------------------|--|
| Input voltage range | 85~305VAC, 100~430VDC | | |
| Input frequency | 47~63Hz | | |
| Input current | 115VAC • 0.4A (max) | 230VAC • 0.25A (max) | |
| Inrush current | 115VAC • 18A (typ) | 230VAC • 35A (typ) | |
| Hot plug | Unavailable | | |
| Recommended external input fuse | 1A/300V | slow blow, required | |

Example:

15ACM_05S3

15 = 15Watt; AC = AC-DC; M = Micro size; 5Vout; S = Single Output; 3 = 3kVAC isolation

| Output specifications | |
|---|--|
| Voltage accuracy | 3.3V output: ±3% (typ) Others: ±2% (typ) |
| Minimum load | 0% |
| Line regulation (full load) | ±0.5% (typ) |
| Load regulation (0% to 100%) | 3.3VDC: ±2% (typ); Others: ±1% (typ) |
| Ripple & Noise* 20MHz bandwidth (peak-peak value) | 80mV (typ) 150mV (max) |
| Short circuit protection | Hiccup, continuous, self-recovery |
| Over current protection | ≥110%Io self-recovery |
| Over voltage protection (Output voltage clamp or hiccup) | • 3.3VDC/5VDC: ≤9VDC • 9VDC: ≤15VDC • 12VDC/15VDC: ≤25VDC • 24VDC: ≤35VDC |

^{*} Ripple and noise are measured by "parallel cable" method.

Note:


- 1. External electrolytic capacitors are required to modules, more details refer to typical applications.
- This part is open frame, at least 6.4mm safety distance between the primary and secondary external components of the module is needed to meet the safety requirement.
- 3. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta = 25°C, humidity <75%, nominal input voltage (115V and 230V) and rated output load.
- 4. In order to improve the efficiency at light load, there will be audible noise generated, but it does not affect product performance and reliability.
- 5. Module required dispensing fixed after assembled.
- All index testing methods in this datasheet are based on our company corporate standards.
- We can provide product customization service, please contact our technicians directly for specific information.
- 8. Products are related to laws and regulations: see "Features" and "EMC".
- Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.


15ACM 3 series

10W- Single Output AC-DC Converter - Universal Input - Isolated & Regulated

| Common specifications | | | | |
|--|--|---|--|--|
| Operating temperature range | -40°C ~ +85°C | | | |
| Storage temperature range | -40°C ~ +105°C | | | |
| Case temperature range | +95°C MAX | | | |
| Storage humidity | 95%RH MAX | | | |
| Welding temperature | | 60 ± 5°C; time: 5 - 10s 60 ± 10°C; time: 3 - 5s | | |
| Temperature coefficient | 0.02%/°C | | | |
| Switching frequency | 65kHz TYP | | | |
| Power derating | • -40°C to -25°C: 4% • +55°C to +70°C: 3.3 • +70°C to +85°C: 2.6 • 85VAC-100VAC: 1,6 • 277VAC-305VAC: 0. | 94%/°C MIN 57%/°C MIN 57%/VAC MIN | | |
| I/O-isolation voltage | 3000VAC/1Min | | | |
| EMC / EMI / CE | CISPR32/EN55032 CISPR32/EN55032 | CLASS A (recommended circuit 1, 4) CLASS B (recommended circuit 2, 3) | | |
| EMC / EMI / RE | CISPR32/EN55032 CISPR32/EN55032 | CLASS A (recommended circuit 1, 4) CLASS B (recommended circuit 2, 3) | | |
| EMC / EMS / ESD | IEC/EN 61000-4-2 | Contact ±6KV | perf. Criteria B | |
| EMC / EMS / RS | IEC/EN 61000-4-3 | 10V/m | perf. Criteria A | |
| EMC / EMS / EFT | • IEC/EN 61000-4-4 • IEC/EN 61000-4-4 | ± 2kV (recommended circuit 1, 4) ± 4kV (recommended circuit 2, 3) | perf. Criteria B perf. Criteria B | |
| EMC / EMS / Surge | • IEC/EN 61000-4-5 • IEC/EN 61000-4-5 • IEC/EN 61000-4-5 | line to line ±1KV (recommended circuit 1, 2) line to line ±2KV (recommended circuit 3, 4) line to line ±4KV (recommended circuit 4) | perf. Criteria B perf. Criteria B perf. Criteria B | |
| EMC / EMS / CS | IEC/EN61000-4-6 | 10 Vr.m.s | perf. Criteria A | |
| EMC / EMS / Voltage dips, short and interruptions immunity | IEC/EN61000-4-11 | 0%-70% | perf. Criteria B | |
| Safety standards | IEC/EN/UL62368, IEC/EN/UL60335 | | | |
| Safety certification | IEC/EN/UL62368 | | | |
| Safety class | CLASS II | | | |
| MTBF | >1,00,000h @25°C (MIL-HDBK-217F) | | | |
| Cooling method | Free air convection | | | |
| Weight | 11g | | | |
| Dimensions | 44.50 x 24.00 x 15.00 | mm | | |

Typical characteristics







Note

- With an AC input between 85 -100VAC/277-305VAC and a DC input between 100 120VDC/390 430VDC, the output power must be derated as per temperature derating curves;
- ② This product is suitable for applications using natural air cooling; for applications in closed environment please consult factory or one of our FAE.

Additional circuits design reference





Additional components selection guide

| | | o. / \ | | | / · · · · · · · · · · · · · · · · · | | 5) # / I I) | |
|------------|-----------------|---------------|---|------------------|-------------------------------------|-----------|----------------|------------------|
| Model | FUSE (required) | C1 (required) | C2 (required) | L1 (required) | C3 (required) | C4 | CY1 (required) | |
| 15ACM_03S3 | | | | 470μF/16V | | 220μF/35V | | |
| 15ACM_05S3 | | | (solid-state capacitor) | | 220μF/35V | | | |
| 15ACM_09S3 | 1A/300V | 33μF/450V | 470μF/16V 33μF/450V (solid-state capacitor) | 2.2 | 220μF/35V | 0.1µF/50V | 2.2nF/400VAC | |
| 15ACM_12S3 | 1A/300V | | | ' / (Solid-State | 2.2μΗ | 220μF/35V | υ.ιμε/ 50 ν | 2.2111 / 400 VAC |
| 15ACM_15S3 | | | 680μF/35V | 680μF/35V | 220μF/35V | | | |
| 15ACM_24S3 | | | 470μF/35V | | 220μF/35V | | | |

Note:

1. C1: input capacitors, C2: output storage capacitors, they must be connected externally.

^{2.} We recommend using an electrolytic capacitor with high frequency and low ESR rating for C3 (refer to manufacture's datasheet). Combined with C2, L1, they form a pi-type filter circuit. Choose a capacitor voltage rating with at least 20% margin, in other words not exceeding 80%. C4 is a ceramic capacitor, used for filtering high frequency noise. A suppressor diode (TVS) is a recommended to protect the application in case of a converter failure and specification should be 1.2 times of the output voltage.


Environmental application EMC solution

Environmental application EMC solution selection table

| Recommen- ded circuit | Application environmental | Typical industry | Input voltage range | Environment temperature | Emissions | Immunity |
|--------------------------|--------------------------------|--|---------------------|----------------------------|-----------|--|
| 1 | Basic application | None | | -40°C~+85°C | CLASS A | CLASS III |
| | Indoor civil environment | Smart home/Home appliances (2Y) | | -25°C~+55°C | CLASS B | CLASS III |
| 2 | Indoor general environment | Intelligent building/Intel- ligent agriculture | 85~305VAC | | | |
| 3 | Indoor industrial environment | Manufacturing workshop | | -25°C~+55°C | CLASS B | CLASS IV |
| | Outdoor general environment | ITS/Video monitoring/ Charging point/ Communication/Security and protection | | -40°C~+85°C | CLASS A | CLASS IV |
| 4 | Outdoor harsh environment | On-line power meter Communication base station | | -40°C~+85°C | CLASS A | > CLASS IV Surge: line to ground ±4KV EFT: CLASS IV |

Electromagnetic compatibility solution-recommended circuit

Recommended circuit 1 - basis application




| Application environmental Ambient temperature range | | Immunity class | Emissions Class |
|---|--|----------------|-----------------|
| Basic application -40°C~+85°C | | CLASS III | CLASS A |

| Component | Recommended value | |
|-----------------|----------------------------|--|
| NTC | 10D-10 | |
| LDM | 1.2mH (MIN: 0.4A, MAX: 4Ω) | |
| CX | 0.1μF/310VAC | |
| FUSE (required) | 1A/300V, slow-blow | |

Electromagnetic compatibility solution-recommended circuit

Recommended circuit 2 - Indoor civil /Universal system recommended circuits for general environment




| Application environmental | Ambient temperature range | Immunity class | Emissions Class |
|---------------------------|---------------------------|----------------|-----------------|
| Indoor civil/general | -25°C~+55°C | CLASS III | CLASS B |

| Component | Recommended value | |
|-----------------|------------------------------|--|
| NTC | 10D-10 | |
| CY1 (CY2) | 2.2nF/400VAC | |
| LCM | 10mH (MIN: 0.4A, MAX: 600mΩ) | |
| LDM | 0.33mH (MIN: 0.4A, MAX: 1Ω) | |
| CX | 0.22μF/310VAC | |
| FUSE (required) | 1A/300V, slow-blow | |
| | | |

Note:

In the home appliance application environment, the two Y capacitors of the primary and secondary need to be externally connected (CY1/CY2, value at 2.2nF/400VAC), which can meet the EN60335 certification. In other industries, only one Y capacitor is needed.

Recommended circuit 3 - Universal system recommended circuits for indoor industrial environment




| Application environmental | Ambient temperature range | Immunity class | Emissions Class |
|---------------------------|---------------------------|----------------|-----------------|
| Indoor industrial | -25°C~+55°C | CLASS IV | CLASS B |

| Component | Recommended value | |
|-----------------|------------------------------|--|
| MOV | S14K350 | |
| C1 | - | |
| CY1 | 2.2nF/400VAC | |
| CX | 0.22μF/310VAC | |
| LCM | 10mH (MIN: 0.4A, MAX: 600mΩ) | |
| LDM | 0.33mH (MIN: 0.4A, MAX: 1Ω) | |
| R1 | 12Ω/3W | |
| FUSE (required) | 2A/300V, slow-blow | |

Electromagnetic compatibility solution-recommended circuit

Recommended circuit 4 - Universal system recommended circuits for outdoor general/harsh environment




| Application environmental | Ambient temperature range | Immunity class | Emissions Class |
|---------------------------|---------------------------|----------------|-----------------|
| Outdoor general | -40°C~+85°C | CLASS IV | CLASS A |


| Component | Recommended value |
|-----------------|----------------------------|
| MOV | S14K350 |
| CX | 0.1μF/310VAC |
| LDM | 1.2mH (MIN: 0.4A, MAX: 4Ω) |
| R1 | 12Ω/3W |
| FUSE (required) | 2A/300V, slow-blow |

| Application environmental | Ambient temperature range | Immunity class | Emissions Class |
|---------------------------|---------------------------|---|-----------------|
| Outdoor harsh | -40°C~+85°C | >CLASS IV Surge: line to ground ±4KV | CLASS A |
| | | EFT: CLASS IV | |

| Component | Recommended value |
|-----------------|---------------------------------------|
| MOV | S20K350 |
| C1 | 450V/33uF (surge protection priority) |
| LDM | 4.7mH |
| R1 | 33Ω/5W |
| FUSE (required) | 6.3A/300V, slow-blow |

Mechanical dimensions






Note:

Unit: mm[inch]

Pin section tolerances: $\pm 0.10[\pm 0.004]$ General tolerances: $\pm 0.50[\pm 0.020]$

The layout of the device is for reference only, please refer to the actual product

THIRD ANGLE PROJECTION





Note:Grid 2.54*2.54mm


| Р | in-Out |
|-----|----------|
| Pin | Function |
| 1 | AC(N) |
| 3 | AC(L) |
| 5 | +V(cap) |
| 7 | -V(cap) |
| 14 | -Vo |
| 16 | +Vo |

1.It is necessary to add C1 between pin5 and pin7. 2.It is necessary to add circuit to the output, such as the recommended circuit 1.

THIRD ANGLE PROJECTION








Note:Grid 2.54*2.54mm

| Pin-Out | | |
|---------|----------|--|
| Pin | Function | |
| 1 | AC(N) | |
| 3 | AC(L) | |
| 5 | +V(cap) | |
| 7 | -V(cap) | |
| 14 | -Vo | |
| 16 | +Vo | |



Note: Unit: mm[inch]

Pin section tolerances: ±0.10[±0.004]

General tolerances: ±0.50[±0.020]

The layout of the device is for reference only,

please refer to the actual product