## SIEMENS

## Data sheet

## 3RW5243-6TC15



SIRIUS soft starter 200-600 V 210 A, 110-250 V AC Screw terminals Thermistor input

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
<ul> <li>of standard HMI module usable</li> </ul>	<u>3RW5980-0HS00</u>
<ul> <li>of high feature HMI module usable</li> </ul>	<u>3RW5980-0HF00</u>
<ul> <li>of communication module PROFINET standard usable</li> </ul>	<u>3RW5980-0CS00</u>
<ul> <li>of communication module PROFIBUS usable</li> </ul>	<u>3RW5980-0CP00</u>
<ul> <li>of communication module Modbus TCP usable</li> </ul>	<u>3RW5980-0CT00</u>
<ul> <li>of communication module Modbus RTU usable</li> </ul>	<u>3RW5980-0CR00</u>
<ul> <li>of communication module Ethernet/IP</li> </ul>	<u>3RW5980-0CE00</u>
<ul> <li>of circuit breaker usable at 400 V</li> </ul>	3VA2325-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 500 V</li> </ul>	3VA2325-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 400 V at inside-delta circuit</li> </ul>	3VA2440-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 500 V at inside-delta circuit</li> </ul>	3VA2440-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of the gG fuse usable up to 690 V</li> </ul>	2x3NA3354-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of the gG fuse usable at inside-delta circuit up to 500 V</li> </ul>	2x3NA3354-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of full range R fuse link for semiconductor protection usable up to 690 V</li> </ul>	<u>3NE1230-2: Type of coordination 2. Iq = 65 kA</u>
<ul> <li>of back-up R fuse link for semiconductor protection usable up to 690 V</li> </ul>	<u>3NE3333; Type of coordination 2, Iq = 65 kA</u>
General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
• CE marking	Yes
• UL approval	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
• is supported HMI-Standard	Yes
• is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes



trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2			
buffering time in the event of power failure				
<ul> <li>for main current circuit</li> </ul>	100 ms			
for control circuit	100 ms			
insulation voltage rated value	600 V			
degree of pollution	3, acc. to IEC 60947-4-2			
impulse voltage rated value	6 kV			
blocking voltage of the thyristor maximum	1 600 V			
service factor	1			
surge voltage resistance rated value	6 kV			
maximum permissible voltage for safe isolation				
<ul> <li>between main and auxiliary circuit</li> </ul>	600 V			
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting			
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz			
utilization category according to IEC 60947-4-2	AC 53a			
reference code according to IEC 81346-2	Q			
Substance Prohibitance (Date)	02/15/2018			
product function				
<ul> <li>ramp-up (soft starting)</li> </ul>	Yes			
• ramp-down (soft stop)	Yes			
Soft Torque	Yes			
<ul> <li>adjustable current limitation</li> </ul>	Yes			
• pump ramp down	Yes			
intrinsic device protection	Yes			
<ul> <li>motor overload protection</li> </ul>	Yes; Full motor protection (thermistor motor protection and electronic motor overload protection)			
<ul> <li>evaluation of thermistor motor protection</li> </ul>	Yes; Type A PTC or Klixon / Thermoclick			
• inside-delta circuit	Yes			
• auto-RESET	Yes			
manual RESET	Yes			
remote reset	Yes; By turning off the control supply voltage			
communication function	Yes			
<ul> <li>operating measured value display</li> </ul>	Yes; Only in conjunction with special accessories			
• error logbook	Yes; Only in conjunction with special accessories			
via software parameterizable	No			
<ul> <li>via software configurable</li> </ul>	Yes			
PROFlenergy	Yes; in connection with the PROFINET Standard communication module			
<ul> <li>firmware update</li> </ul>	Yes			
<ul> <li>removable terminal for control circuit</li> </ul>	Yes			
torque control	No			
analog output	No			
Power Electronics				
operational current				
at 40 °C rated value	210 A			
at 50 °C rated value	186 A			
at 60 °C rated value	170 A			
operational current at inside-delta circuit				
at 40 °C rated value	364 A			
• at 50 °C rated value	322 A			
at 60 °C rated value	294 A			
operating voltage				
rated value	200 600 V			
at inside-delta circuit rated value	200 600 V			
relative negative tolerance of the operating voltage	-15 %			
relative positive tolerance of the operating voltage	10 %			
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %			
relative positive tolerance of the operating voltage at inside-delta circuit	10 %			
operating power for 3-phase motors				
· VI · P·····				

• at 230 V at 40 °C rated value	55 kW
<ul> <li>at 230 V at 40° C rated value</li> <li>at 230 V at inside-delta circuit at 40 °C rated value</li> </ul>	110 kW
<ul> <li>at 230 V at inside-defia circuit at 40°C rated value</li> <li>at 400 V at 40 °C rated value</li> </ul>	110 kW
<ul> <li>at 400 V at 40° C rated value</li> <li>at 400 V at inside-delta circuit at 40 °C rated value</li> </ul>	200 kW
<ul> <li>at 400 V at mindedena circuit at 40 C rated value</li> <li>at 500 V at 40 °C rated value</li> </ul>	132 kW
<ul> <li>at 500 V at 40° C rated value</li> <li>at 500 V at inside-delta circuit at 40 °C rated value</li> </ul>	250 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
<ul> <li>at rotary coding switch on switch position 1</li> </ul>	90 A
<ul> <li>at rotary coding switch on switch position 2</li> </ul>	98 A
at rotary coding switch on switch position 3	106 A
<ul> <li>at rotary coding switch on switch position 4</li> </ul>	114 A
<ul> <li>at rotary coding switch on switch position 5</li> </ul>	122 A
• at rotary coding switch on switch position 6	130 A
<ul> <li>at rotary coding switch on switch position 7</li> </ul>	138 A
at rotary coding switch on switch position 8	146 A
<ul> <li>at rotary coding switch on switch position 9</li> </ul>	154 A
<ul> <li>at rotary coding switch on switch position 10</li> </ul>	162 A
<ul> <li>at rotary coding switch on switch position 11</li> </ul>	170 A
<ul> <li>at rotary coding switch on switch position 12</li> </ul>	178 A
<ul> <li>at rotary coding switch on switch position 13</li> </ul>	186 A
<ul> <li>at rotary coding switch on switch position 14</li> </ul>	194 A
<ul> <li>at rotary coding switch on switch position 15</li> </ul>	202 A
<ul> <li>at rotary coding switch on switch position 16</li> </ul>	210 A
• minimum	90 A
adjustable motor current	
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 1</li> </ul>	156 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 2</li> </ul>	170 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 3</li> </ul>	184 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 4</li> </ul>	197 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 5</li> </ul>	211 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 6</li> </ul>	225 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 7</li> </ul>	239 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 8</li> </ul>	253 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 9</li> </ul>	267 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 10</li> </ul>	281 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 11</li> </ul>	294 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 12</li> </ul>	308 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 13</li> </ul>	322 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 14</li> </ul>	336 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 15</li> <li>for inside delta circuit at rotary coding switch on</li> </ul>	350 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 16</li> <li>a stimula data sizuit minimum</li> </ul>	364 A
at inside-delta circuit minimum	156 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	

• at 40 °C after startup	75 W			
• at 50 °C after startup	68 W			
• at 60 °C after startup	63 W			
power loss [W] at AC at current limitation 350 %	0.500 M			
• at 40 °C during startup	3 562 W			
<ul> <li>at 50 °C during startup</li> <li>at 60 °C during startup</li> </ul>	2 979 W 2 617 W			
Control circuit/ Control	2017 W			
	AC			
type of voltage of the control supply voltage control supply voltage at AC	AC			
• at 50 Hz	110 250 V			
• at 60 Hz	110 250 V 110 250 V -15 %			
relative negative tolerance of the control supply				
voltage at AC at 50 Hz				
relative positive tolerance of the control supply voltage at AC at 50 Hz	10 % -15 %			
relative negative tolerance of the control supply voltage at AC at 60 Hz				
relative positive tolerance of the control supply voltage at AC at 60 Hz	10 %			
control supply voltage frequency	50 60 Hz			
relative negative tolerance of the control supply voltage frequency	-10 %			
relative positive tolerance of the control supply voltage frequency	10 %			
control supply current in standby mode rated value	30 mA			
holding current in bypass operation rated value	100 mA			
locked-rotor current at close of bypass contact maximum	2.2 A			
inrush current peak at application of control supply voltage maximum	12.2 A			
duration of inrush current peak at application of control supply voltage	2.2 ms			
design of the overvoltage protection	Varistor			
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply			
Inputs/ Outputs				
number of digital inputs	1			
number of digital outputs	3			
not parameterizable	2			
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)			
number of analog outputs	0			
switching capacity current of the relay outputs				
• at AC-15 at 250 V rated value	3 A			
• at DC-13 at 24 V rated value	1 A			
Installation/ mounting/ dimensions				
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back			
fastening method	screw fixing			
height	393 mm			
width	210 mm			
depth	203 mm			
required spacing with side-by-side mounting	10 mm			
forwards     backwards	10 mm 0 mm			
<ul> <li>backwards</li> <li>upwards</li> </ul>				
downwards	100 mm 75 mm			
at the side	75 mm 5 mm			
weight without packaging	9.9 kg			
Connections/ Terminals				
type of electrical connection				
GPS OF OFOCHION CONTECTION				

• for main current circuit	husbar connection
for main current circuit	busbar connection
• for control circuit	screw-type terminals
width of connection bar maximum	45 mm
wire length for thermistor connection	50
• with conductor cross-section = 0.5 mm <sup>2</sup> maximum	50 m
• with conductor cross-section = 1.5 mm <sup>2</sup> maximum	150 m
• with conductor cross-section = 2.5 mm <sup>2</sup> maximum	250 m
type of connectable conductor cross-sections	
<ul> <li>for DIN cable lug for main contacts stranded</li> </ul>	2x (50 240 mm²)
for DIN cable lug for main contacts finely stranded	2x (70 240 mm²)
type of connectable conductor cross-sections	
<ul> <li>for control circuit solid</li> </ul>	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)
<ul> <li>for control circuit finely stranded with core end processing</li> </ul>	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
<ul> <li>at AWG cables for control circuit solid</li> </ul>	1x (20 12), 2x (20 14)
wire length	
<ul> <li>between soft starter and motor maximum</li> </ul>	800 m
<ul> <li>at the digital inputs at AC maximum</li> </ul>	100 m
tightening torque	
<ul> <li>for main contacts with screw-type terminals</li> </ul>	14 24 N·m
<ul> <li>for auxiliary and control contacts with screw-type</li> </ul>	0.8 1.2 N·m
terminals	0.0 1.2 Will
tightening torque [lbf·in]	
<ul> <li>for main contacts with screw-type terminals</li> </ul>	124 210 lbf·in
<ul> <li>for auxiliary and control contacts with screw-type</li> </ul>	7 10.3 lbf·in
terminals	
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +60 °C; Please observe derating at temperatures of 40 °C or
	above
<ul> <li>during storage and transport</li> </ul>	-40 +80 °C
environmental category	
<ul> <li>during operation according to IEC 60721</li> </ul>	3K6 (no ice formation, only occasional condensation), 3C3 (no salt
e during storage according to IEC 60721	mist), 3S2 (sand must not get into the devices), 3M6
<ul> <li>during storage according to IEC 60721</li> </ul>	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
<ul> <li>during transport according to IEC 60721</li> </ul>	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
• EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of circuit breaker	
	Signars type: $31/453$ may 400 Å or $31/454$ may 600 Å; $a = 40 \text{ k}$ Å
<ul> <li>— usable for Standard Faults at 460/480 V according to UL</li> </ul>	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq = 10 kA
— usable for High Faults at 460/480 V according	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; lq max = 65
to UL — usable for Standard Faults at 460/480 V at	kA Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; lq = 10 kA
inside-delta circuit according to UL — usable for High Faults at 460/480 V at inside-	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq max = 65
delta circuit according to UL — usable for Standard Faults at 575/600 V	kA
according to UL	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq = 10 kA
<ul> <li>— usable for Standard Faults at 575/600 V at inside-delta circuit according to UL</li> </ul>	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq = 10 kA
• of the fuse	
— usable for Standard Faults up to 575/600 V	Type: Class J / L. max. 700 A: Ig = 10 kA

according to UL					
— usable for High Faults up to 57	75/600 V	Type: Cla	ass J / L, max. 700 .	A; lq = 100 kA	
according to UL — usable for Standard Faults at inside-delta					
circuit up to 575/600 V according to UL		Type: Class J / L, max. 700 A; lq = 10 kA			
— usable for High Faults at inside-delta circuit up to 575/600 V according to UL		Type: Class J / L, max. 700 A; lq = 100 kA			
operating power [hp] for 3-phase moto	rs				
• at 200/208 V at 50 °C rated value		60 hp			
<ul> <li>at 220/230 V at 50 °C rated value</li> </ul>		60 hp			
• at 460/480 V at 50 °C rated value		150 hp			
<ul> <li>at 460/480 V at 50 °C rated value</li> <li>at 575/600 V at 50 °C rated value</li> </ul>		150 hp			
<ul> <li>at 200/208 V at inside-delta circuit a</li> </ul>	at 50 °C rated	100 hp			
value		1001.0			
<ul> <li>at 220/230 V at inside-delta circuit a value</li> </ul>	at 50 °C rated	125 hp			
<ul> <li>at 460/480 V at inside-delta circuit a value</li> </ul>	at 50 °C rated	250 hp			
<ul> <li>at 575/600 V at inside-delta circuit a value</li> </ul>	at 50 °C rated	300 hp			
contact rating of auxiliary contacts acc	ording to UL	R300-B3	00		
Safety related data					
protection class IP on the front accord	ing to IEC	IP00; IP2	0 with cover		
touch protection on the front according	g to IEC 60529	finger-sa	fe, for vertical conta	ict from the front with a	over
electromagnetic compatibility	<u> </u>	-	ance with IEC 6094		
Certificates/ approvals					
Centricates/ autorovais					
		_			EMC
General Product Approval					EMC
	(ccc		(UL) UL	EAC	
General Product Approval Confirmation Confirmation	ccc Test Certifica	tes M	UL UL	EAC	EMC ECM
General Product Approval		tes M	UL UL	EAC	EMC ECM
General Product Approval Confirmation Confirmation		tific-	arine / Shipping	EAC EAC	EMC RCM
General Product Approval         Confirmation         Confirmation         Declaration of Conformity	Test Certifica	tific-	arine / Shipping	EAC BUREAU VERITAS	RCM
General Product Approval         Confirmation         Confirmation         Declaration of Conformity         UKK         EGG         EGG         EGG         EGG	Test Certifica <u>Type Test Certificates/Test Rep</u>	tific- port	arine / Shipping	EAC BUREAU VERITAS	RCM
General Product ApprovalConfirmationConfirmationDeclaration of ConformityUKSCCCConfirmationUKSCCCMarine / ShippingVision <td>Test Certificat Type Test Cert ates/Test Rep</td> <td>tific- port</td> <td>arine / Shipping</td> <td>EAC UNCEAU UNCEAU VERITAS</td> <td>RCM</td>	Test Certificat Type Test Cert ates/Test Rep	tific- port	arine / Shipping	EAC UNCEAU UNCEAU VERITAS	RCM
General Product Approval         Confirmation         Confirmation         Declaration of Conformity         UKS         EGE         EGE         Marine / Shipping         Image: Shipping	Test Certifica <u>Type Test Cer</u> <u>ates/Test Rep</u> other <u>Confirmatio</u>	<u>tific-</u> <u>port</u>	arine / Shipping	EAC BUREAU VERITAS	RCM

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5243-6TC15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5243-6TC15

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5243-6TC15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW5243-6TC15&lang=en

Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5243-6TC15/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5243-6TC15&objecttype=14&gridview=view1 Simulation Tool for Soft Starters (STS) https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified:

4/10/2022 🖸