

## H3-TCM3-452X+

20-4500MHz 50Ω 1:3 Balun


### APPLICATIONS

Ideally suitable for PCS, wideband push-pull amplifiers and cellular applications.

### FEATURES

- Surface mount
- Impedance ratio: 1:3
- Balanced transmission line
- RoHS compliant and Pb free
- 260°C reflow compatible

### DIMENSIONS




A	B	C
4.30	4.30	3.00
D		
1.27		

Unless otherwise stated dimensions are in mm


Tolerance: .xx ± 0.25, .xxx ± 0.05

### Land Pattern



E	F	G
1.40	0.76	1.27
H		
4.83		


### FUNCTIONAL SCHEMATIC



### PIN CONFIGURATION

Pin No.	Function
1	Not used(ground)
2	Primary(Ground)
3	Primary Dot
4	Secondary Dot
5	Ground
6	Secondary





### APPLICATION & TEST CIRCUIT



### ELECTRICAL SPECIFICATIONS@25°C:

Parameters (P#: ENA PORT)	frequency band	Min.	Typ.	Max.	Unit
Port Impedance, Z0 (P1 / P2 / P3)			50/75/75		Ohm
Insertion Loss	20-4500MHz		1.6	3.0	dB
Phase Balance	20-4500MHz		4.0		Deg
Amplitude Balance	20-4500MHz		0.5		dB

### TEST CURVE



### ABSOLUTE MAXIMUM RATINGS

Parameter	Value
RF Power	0.4W
DC Current	30mA
Operating Temperature Range	-40 to 85°C
Storage Temperature Range	-55 to 100°C

Tel: +86-28-85589664

E-mail: mr\_li@henglitaitech.com

Web: www.hltchips.com

Adress: No.198 Tianqin East Street, Gaoxin West District, Chengdu City