SIEMENS

Data sheet

US2:87JUH6FA



Pump control panel, Size 4, Three phase full voltage, Solid-state overload relay, OLR amp range 50-200A, 110-120/220-240VAC 60Hz coil, Standard type contactor, 200A fusible disconnect, 200A/600V fuse clip, HOA Sel Sw. <(>&<)> Start P.B., Enclosure NEMA type 3/3R, Weather proof outdoor use

	simi	

product brand name	Class 87
design of the product	Pump control panel with fused disconnect switch
special product feature	ESP200 overload relay; Dual voltage coil
General technical data	
weight [lb]	87 lb
Height x Width x Depth [in]	41 × 24 × 8 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
 during storage 	-22 +149 °F
 during operation 	-4 +104 °F
ambient temperature	
 during storage 	-30 +65 °C
 during operation 	-20 +40 °C
country of origin	USA
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	0 hp
• at 220/230 V rated value	0 hp
• at 460/480 V rated value	100 hp
• at 575/600 V rated value	100 hp
Contactor	
size of contactor	NEMA controller size 4
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operational current at AC at 600 V rated value	135 A
mechanical service life (switching cycles) of the main contacts typical	500000
Auxiliary contact	
number of NC contacts at contactor for auxiliary contacts	0
number of NO contacts at contactor for auxiliary contacts	1
number of total auxiliary contacts maximum	7
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)
Coil	
type of voltage of the control supply voltage	AC
control supply voltage	

 at DC rated value 	0 0 V
 at AC at 50 Hz rated value 	0 0 V
at AC at 60 Hz rated value	110 240 V
holding power at AC minimum	22 W
apparent pick-up power of magnet coil at AC	510 VA
operating range factor control supply voltage rated value of magnet coil	0.85 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	18 34 ms
OFF-delay time	10 12 ms
Overload relay	
product function	
 overload protection 	Yes
 phase failure detection 	Yes
 asymmetry detection 	Yes
ground fault detection	Yes
• test function	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 (factory set) / 20 / 30
adjustable current response value current of the current-	50 200 A
dependent overload release	
tripping time at phase-loss maximum	3s
relative repeat accuracy	<u>1 %</u>
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay _according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
 with single-phase operation at AC rated value 	600 V
 with multi-phase operation at AC rated value 	300 V
Disconnect Switch	
response value of switch disconnector	200A / 600V
design of fuse holder	Class H fuse clips
operating class of the fuse link	Class H, J (retrofittable), K and R
Enclosure	
degree of protection NEMA rating of the enclosure	NEMA Type 3R
design of the housing	Weather proof for outdoor use
Standard Control Devices	
product component Hand-Off-Auto selector switch	Yes
type of Hand-Off-Auto selector switch	
	30mm metal housing with matte finish Yes
product component start push button	
type of start push button	30mm metal housing with matte finish
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (6 AWG 300 Kcmil)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Box lug
tightening torque [lbf-in] for load-side outgoing feeder	200 200 lbf in

type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-stranded	1x (6 AWG 250 MCM)			
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C			
material of the conductor for load-side outgoing feeder	CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection at contactor for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:87JUH6FA Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:87JUH6FA Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:87JUH6FA⟨=en Certificates/approvals				
https://support.industry.siemens.com/cs/US/en/ps/US2:87JUH6FA/certificate				

last modified:

1/25/2022 🖸