


Data sheet for SINAMICS G120X

6SL3220-3YC34-0UP0 Article No.:

Client order no. : Order no.: Offer no. : Remarks :



110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications	
Power factor λ	0.90 0.95
Offset factor $\cos\phi$	0.99
Efficiency η	0.96
Sound pressure level (1m)	70 dB
Power loss 3)	1.310 kW
Filter class (integrated)	Unfiltered
EMC category (with accessories)	without
Safety function "Safe Torque Off"	without

Communication

PROFIBUS DP Communication



Item no.: Consignment no. : Project :

Inputs / outputs	
Standard digital inputs	
Number	6
Switching level: $0 \rightarrow 1$	11 V
Switching level: $1 \rightarrow 0$	5 V
Max. inrush current	15 mA
Fail-safe digital inputs	
Number	1
Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Analog / digital inputs Number	2 (Differential input)
3 3 .	2 (Differential input) 10 bit
Number	
Number Resolution	
Number Resolution Switching threshold as digital input	10 bit
Number Resolution Switching threshold as digital input 0 → 1	10 bit 4 V
Number Resolution Switching threshold as digital input $0 \rightarrow 1$ $1 \rightarrow 0$	10 bit 4 V

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No




Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YC34-0UP0

Ambient conditions	
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.083 m ³ /s (2.931 ft ³ /s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Conne	ections
Signal cable	
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	25.00 70.00 mm ² (AWG 6 AWG 3/0)
Motor end	
Version	Screw-type terminals
Conductor cross-section	25.00 70.00 mm ² (AWG 6 AWG 3/0)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)

Mechanical data	
Degree of protection	IP20 / UL open type
Frame size	FSE
Net weight	16.6 kg (36.60 lb)
Dimensions	
Width	275 mm (10.83 in)
Height	551 mm (21.69 in)
Depth	248 mm (9.76 in)
Standards	
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	63.3 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}\}mbox{The}$ output current and HP ratings are valid for the voltage range 220V-240V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YC34-0UP0

	Operator panel: I	ntelligent Operator Panel (IOP-2
	Screen	
Display design	LCD color	Ambient temperature
Screen resolution	320 x 240 Pixel	Operation
	Mechanical data	Storage
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.134 kg (0.30 lb)	Relative humidity at 25
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	maxi operation
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	Certificate of suitability

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
	55 $^{\circ}\text{C}$ only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C duri	ng	
Max. operation	95 %	
	Approvals	
	Approvais	
Certificate of suitability	CE, cULus, EAC, KCC, RCM	